



SPECIFICATIONS

PANEL SIZE	27"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	144Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GtG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	250 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CURVATURE	Flat
CONTRAST RATIO	1500:1
DCR	100000000:1
Signal Frequency	53.88-143.27 KHz(H) / 48-144 Hz(V)
sRGB	102% (CIE 1976)
ACTIVE DISPLAY AREA (MM)	597.888(H) x 336.312(V)
PIXEL PITCH (H X V)	0.3114(H) x 0.3114(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M, 8 bits (6 bits + FRC)
HDR SUPPORT	HDR Ready
VIDEO PORTS	1x HDMI™ 2.0 (FHD@144Hz) 1x DisplayPort 1.2a 1x D-Sub (VGA)
USB Ports	N/A
Audio Interface	1x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	3W x2
Webcam	N/A
VESA MOUNTING	100 x 100 mm
POWER TYPE	External Adaptor 12V 3A
POWER INPUT	100~240V, 50/60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
Activated Range	48~144Hz
ADJUSTMENT (TILT)	-5° ~ 20°
ADJUSTMENT (SWIVEL)	N/A
ADJUSTMENT (PIVOT)	N/A
ADJUSTMENT (HEIGHT)	N/A
Dimension with Stand (W x D x H)	613.49 x 201.01 x 470.61 mm (24.15 x 7.91 x 18.53 inch)

FEATURES



IPS Grade Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



144Hz Game Ready

Thanks to the high refresh rate and adaptive-sync support, our gaming experience becomes completely smooth and free from interruptions.



EyesErgo

An eye care solution designed with ergonomics in mind.



Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



MSI Power Link

A desktop PC can be powered by an MSI-selected monitor through MSI Power Link technology, enabling the most convenient user experience.



Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.



VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.



Accessory Slot Design

Enjoy a clean table with the accessory slot design where you can put MSI Pen or Smartphone, and you will not miss important messages anymore.



PRO MP273W E14A

SLIM, SLEEK, SMOOTH

Dimension without Stand (W x D x H)	613.49 x 59.56 x 364.46 mm (24.15 x 2.34 x 14.35 inch)
CARTON DIMENSION (W X D X H)	688 x 128 x 451 mm (27.09 x 5.04 x 17.76 inch)
WEIGHT (NW / GW)	4.1 kg (9.04 lbs) / 6.3 kg (13.89 lbs)
CERTIFICATES	CB/CE Energy Star
VIDEO INPUT COMPATIBILITY	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
ACCESSORIES	1x HDMI™ Cable (2.0b), 1x Quick Guide, 1x Power Cord (C13/Optional), 1x Power Adaptor
Note	HDMI™: 1920 x 1080 (Up to 144Hz) DisplayPort: 1920 x 1080 (Up to 144Hz) D-Sub (VGA): 1920 x 1080 (Up to 60Hz) Support: HDMI™ CEC (MSI Power Link), FW Update ; Non Support: PIP/PBP, KVM

CONNECTIONS



- 1. 5-Way Navi Key
- 2. 1x DisplayPort 1.2a
- 3. 1x HDMI™ 2.0 (FHD@144Hz)
- 4. 1x D-Sub (VGA)
- 5. 1x Headphone-out
- 6. DC-in
- 7. Kensington Lock