



ACCESS PRO



ADL 8/128GB

Fanless, plug-and-play mini PC stick for business and power users. Intel Alder Lake N-Series with 8GB/128GB, plus Wi-Fi 6, Bluetooth 5.2, USB-C, and HDMI 4K@60FPS. OS and software can be customized for your deployment.

PORTS AND FEATURES



MOST POPULAR CASES

- ① Kiosks
- ② MSPs
- ③ Digital Signage
- ④ IoT
- ⑤ Remote Work

PRODUCT SPECIFICATIONS

RAM INSTALLED	Embedded 8GB LPDDR5
STORAGE	128GB eMMC
OPERATING SYSTEM	Windows 11 Pro®, Windows IoT®, Linux® Ubuntu®
WI-FI	AX201, Wi-Fi® 6 Dual Band (2.4Ghz/5.0Ghz)
GPU MODEL & MANUFACTURER	Intel® UHD Graphics
PROCESSOR, MODEL & MANUFACTURER	Intel® Alder Lake (N100)
PROCESSOR CORE COUNT	4
PROCESSOR CACHE	6 MB Intel® Smart Cache
ETHERNET	1 Gbps (x1)
BLUETOOTH	Intel® AX201, supports Bluetooth® 5.2.
WIRELESS LAN (TYPE)	Wi-Fi® 6
HDMI (NUMBER)	HDMI® 2.0 (x1)
HDMI OUTPUT	4K@60FPS
USB PORTS	USB 3.0 (x1)
TYPE-C PORT	USB 3.0 (x1)
MICRO SD CARD SLOT	(x1)
AUDIO OUTPUT	3.5 mm Audio Jack with L/R/MIC combo (x1)
POWER SUPPLY	12V/2A
WEIGHT	0.28 lbs
DIMENSIONS	5.1 x 2.0 x 0.8 in
WARRANTY	3 year manufacturer's warranty
KENSINGTON LOCK	K-Slot (x1)