

PORTÉGÉ® X40L-M

PZA31U-0FP01E

POWER AND ELEGANCE UNLEASHED

The lightest 14-inch laptop in Dynabook's history, the Intel® EVO™ platform Portégé® X40L-M redefines high-performance mobile computing.



UNCOMPROMISING PERFORMANCE & EFFICIENCY

The Portégé® X40L-M boasts an Intel® Core™ Ultra processor (Series 1) with hybrid architecture, Intel® Arc graphics, ensuring accelerated performance, extended battery life, and enhanced graphics.



SUPERCHARGE YOUR PRODUCTIVITY WITH AI

Microsoft Copilot, accessible via a dedicated key, streamlines tasks, like launching apps and adjusting system settings, through voice or text commands, enhancing efficiency and device navigation.



FEATHERLIGHT MAGNESIUM ALLOY CHASSIS

With a Tech Blue magnesium alloy chassis meeting MIL-STD-810H standards, the 2.31-pound Portégé® X40L-M, at 15.9mm thin, features a 14-inch ultra-thin bezel display, backlit keyboard, and large ClickPad.



AI-ENHANCED CAMERA FEATURES

Embedded AI enhances collaboration by personalizing appearances and environments to ensure clear faces in various lighting. It enables background blurring and eye contact adjustments for direct engagement.



A MORE COMFORTABLE VIEWING EXPERIENCE

The 14-inch Portégé® X40L-M offers an Eyesafe® 16:10 IPS 1920x1200 display, filtering HEV blue light while maintaining vivid color performance for reduced eye strain during long screen hours.



SECURITY TAKEN SERIOUSLY

Featuring a secure mix of hardware, firmware, software and identity protection technologies, the Portégé® X40L-M is suitable for mission critical users in even the most data-sensitive industries.



Laptops That Defend Against Cyber Threats



Dynabook's Windows 11 Secured-core PC laptops offer advanced security by integrating robust hardware and software defenses into their core components. These laptops provide a fortified shield against sophisticated cyber threats, employing specialized hardware protections and firmware safeguards. They ensure unparalleled security from boot-up, defending against malware and firmware attacks to safeguard critical data and uphold the integrity of business operations.



PLATFORM SPECIFICATIONS AND CONFIGURABLE OPTIONS

Operating System*

- Windows 11 Pro

Processor*

- Intel® Core™ Ultra 7 (Series 1) 155H

Memory*

- 32 GB On-Board LPDDR5x

Graphics

- Intel® Arc™ Graphics

Display*

- 14.0" WUXGA (1920x1200) EyeSafe IPS

Storage*

- 512 GB PCIe NVMe SSD

Communications

- Intel® Ethernet Connection i219
- Intel® Wi-Fi 6E AX211, 6 GHz, 802.11ax
- Bluetooth™

Camera w/ Privacy Shutter*

- Webcam with Dual-Microphones

Audio

- 360° Dual-Array Microphones
- Four-Speaker Audio System with Dolby Atmos®

Ports

- HDMI®
- Two (2) USB-C ports supporting Thunderbolt 4
- Two (2) USB 3.2 Gen 1 Type-A ports • One supporting USB Sleep & Charge
- RJ-45 Ethernet LAN port
- Headset jack (Microphone / Headphone combo port)
- microSD card slot

Security*

- Microsoft Secured-core PC
- Trusted Platform Module 2.0
- Fingerprint Reader
- Security Lock Slot

Input Devices

- Premium Raised-tile, Spill-resistant, Backlit Keyboard
- ClickPad Pointing Device

Battery

- 65 Wh Battery

Physical Description

- Tech Blue Metallic
- Magnesium Alloy Chassis
- Designed to pass MIL-STD-810H methodologies
- 312.4 x 224 x 15.9 millimeters
- Starting at 1.05 kilograms (2.31 pounds)

Regulatory / Environmental Specifications

- EPEAT® Rated
- ENERGY STAR® Qualified
- RoHS Compatible

Warranty*

- 3-Year Standard Limited Warranty

Optional Accessories

- PS0120UA1PRP – Dynabook Thunderbolt™ 4 Dock
- PA5356U-1PRP – Dynabook USB-C® Dock
- PS0001UA1PRP – USB-C® to HDMI® / VGA / LAN / USB 3.0 Adapter with Power Delivery (PD) Charging
- PS0089UA1PRP – USB-C® to VGA / LAN Adapter with Power Delivery (PD) Charging
- PA5270U-1PRP – USB-C® to VGA Adapter with Power Delivery (PD) Charging
- PA5352U-1ACA – 65W USB-C® AC Adapter (5V / 9V / 15V / 20V)

1. Weight. Weight may vary depending on product configuration, vendor components, manufacturing variability and options selected. 2. Warranty. Dynabook's standard limited warranty terms and limitations apply. Visit www.support.dynabook.com/warranty for details.

+Care Service® Warranty with On-Site

Portégé laptops are backed by one of the best standard warranties in the business. For even greater peace of mind, Dynabook's industry-leading +Care Service® Warranty with On-site can be added for worry-free reliability with up to four years of coverage. With comprehensive warranty coverage and access to a vast service and support network, Dynabook helps businesses minimize downtime, reduce IT costs, and ensure uninterrupted productivity.



* Based on Configuration

** Visit <http://us.dynabook.com/info> for a complete list of all product legal footnotes