

Lenovo  
**LEGION**

## Lenovo Legion 25-10 Monitor

# PRECISION BORN FOR FLAWLESS GAMING.

The Lenovo Legion 25-10 gaming monitor boasts a lightning-fast 320Hz Extreme Refresh Rate and 0.5ms MPRT<sup>1</sup> response time for ultra-smooth gameplay and seamless action. Cutting-edge screen technology delivers stunning visual fidelity and immersive color tailored for esports enthusiasts, while a user-centric design ensures comfort and personalized control for every gaming session.



### Esports-optimized visual performance

- **Competitive screen size**  
Designed for competitive gaming, the 24.5-inch FHD 1920 x 1080 display delivers sharp details with minimal distractions.
- **Excellent color performance**  
Cream of the crop color performance with 99% sRGB ensures vibrant, accurate visuals you can trust.
- **Striking contrast and realism**  
HDR10 enhances game worlds with striking contrast—bringing deeper blacks and brighter whites to every scene for immersive gameplay.



### React with pro gamer speed

- **Extremely smooth gameplay**  
Never miss a beat with up to 320Hz extreme refresh rate—delivering flawlessly smooth gameplay.
- **Seamless gaming visuals**  
AMD FreeSync™ Premium and VESA Adaptive Sync eliminate screen tearing, stuttering, and ghosting for ultra-responsive, uninterrupted immersion.
- **Super-fast responsiveness**  
With a 0.5ms MPRT<sup>1</sup> (1ms OD) response time, you gain the speed advantage—minimizing input lag so you hit your targets faster every time.



### Win with confidence and comfort

- **Tailored for gamer comfort**  
A fully function stand—lift, tilt, pivot, and swivel—lets you find the perfect play position, supporting posture during epic gaming sessions.
- **Versatile connectivity**  
Two HDMI 2.1<sup>2</sup> ports and a DP 1.4<sup>3</sup> port deliver flexible connectivity, seamlessly integrating your consoles, accessories, and devices into one powerful ecosystem.
- **Personalized gaming experience**  
Lenovo Artery (Lenovo Accessory and Display Manager)<sup>4</sup> puts full control at your fingertips—fine-tune display settings, manage audio devices, or use advanced functions for an optimized, personalized gaming experience.

Lenovo

# Lenovo Legion 25-10 Monitor

## SPECIFICATIONS

| DISPLAY                          |                                                                                                   |
|----------------------------------|---------------------------------------------------------------------------------------------------|
| Panel Size                       | 24.5-inch                                                                                         |
| Screen Dimensions                | 552.4 mm x 313.4 mm                                                                               |
| Panel Type                       | 3-sided NearEdgeless, In-Plane Switching                                                          |
| Active Area                      | 543.7 mm x 302.6 mm                                                                               |
| Backlight                        | WLED                                                                                              |
| Aspect Ratio                     | 16:9                                                                                              |
| Resolution                       | 1920 x 1080                                                                                       |
| Pixel Pitch                      | 0.2832 mm x 0.2802 mm                                                                             |
| Dot/Pixel Per Inch (DPI/PPI)     | 90                                                                                                |
| Viewing Angle (H x V @ CR 10:1)  | 178° / 178°                                                                                       |
| Response Time                    | 0.5ms (MPRT <sup>1</sup> ), 1ms (Level 4), 2ms (Level 3), 3ms (Level 2), 4ms (Level 1), 6ms (Off) |
| Refresh Rate                     | 320Hz                                                                                             |
| Brightness                       | 300 cd/m <sup>2</sup>                                                                             |
| Contrast Ratio (Typical)         | 1000:1                                                                                            |
| Dynamic Contrast Ratio (Typical) | 3M:1                                                                                              |
| Color Gamut (Coverage Ratio)     | 99% sRGB (CIE 1931)                                                                               |
| Color Support (Typical)          | 16.7 Million                                                                                      |
| Color Depth                      | True 8-bit                                                                                        |
| HDR Compliance                   | Yes (HDR10)                                                                                       |
| Anti-glare                       | Yes                                                                                               |

| CONNECTIVITY |                                                                  |
|--------------|------------------------------------------------------------------|
| Video Signal | 2 x HDMI 2.1 <sup>2</sup> TMDS<br>1 x DP 1.4 (HBR3) <sup>3</sup> |
| Audio Signal | 1 x Audio Out (3.5 mm)                                           |

| SPECIAL FEATURES       |                                                                     |
|------------------------|---------------------------------------------------------------------|
| Software               | Lenovo Artery (Lenovo Accessories and Display Manager) <sup>4</sup> |
| Sync Technology        | AMD FreeSync™ Premium / VESA Adaptive Sync                          |
| Gaming Console Support | Yes                                                                 |
| Natural Low Blue Light | Yes                                                                 |
| Mirrored Power Button  | Yes                                                                 |

| POWER                             |                           |
|-----------------------------------|---------------------------|
| Power Consumption (Typ. / Max.)   | 24.5W / 43.0W             |
| Power Consumption Sleep/Off Mode  | < 0.5W                    |
| Power Consumption Switch-Off Mode | < 0.3W                    |
| Power Supply                      | Internal                  |
| Voltage Required                  | AC 100 to 240 V (50-60Hz) |

| MECHANICAL                    |                    |
|-------------------------------|--------------------|
| Tilt Angle (Front / Back)     | -5° / 22°          |
| Swivel Angle (Left / Right)   | -30° / 30°         |
| Lift (Max. Range)             | 135 mm             |
| Pivot                         | -90° / 90°         |
| VESA Mount Capability         | Yes (100 x 100 mm) |
| Kensington Lock Slot          | Yes (3 mm x 7 mm)  |
| Cable Management              | Yes                |
| Bezel Color                   | Eclipse Black      |
| The Minimum Thickness of Head | 15.1 mm            |
| Bezel Width (Side)            | 1.8 mm             |
| Bezel Width (Top)             | 1.8 mm             |
| Bezel Width (Bottom)          | 20.4 mm            |

| DIMENSION                                                        |                                                         |
|------------------------------------------------------------------|---------------------------------------------------------|
| Size Packed (W x D x H, mm/inch)                                 | 615.0 x 145.0 x 420.0 mm<br>24.21 x 5.71 x 16.54 inches |
| Size Unpacked with Stand (Highest Position) (W x D x H, mm/inch) | 557.0 x 214.0 x 514.3 mm<br>21.93 x 8.43 x 20.25 inches |
| Size Unpacked with Stand (Lowest Position) (W x D x H, mm/inch)  | 557.0 x 214.0 x 379.3 mm<br>21.93 x 8.43 x 14.93 inches |
| Size Unpacked without Stand (Head Only) (W x D x H, mm/inch)     | 557.0 x 47.2 x 332.1 mm<br>21.93 x 1.86 x 13.07 inches  |
| Weight Packed (kg / lbs.)                                        | 6.3 kg / 13.9 lbs.                                      |
| Weight Unpacked (kg / lbs.)                                      | 5.2 kg / 11.5 lbs.                                      |
| Weight (Head only) (kg / lbs.)                                   | 3.1 kg / 6.8 lbs.                                       |

| WHAT'S IN THE BOX          |                          |
|----------------------------|--------------------------|
| Monitor with Stand         | Yes                      |
| Power Cable (Cable Length) | 1 x Power Cable (1.8 m)  |
| DP Cable (Cable Length)    | 1 x DP 1.4 Cable (1.8 m) |
| Quick Setup Guide          | Yes                      |
| Warranty Booklet           | Yes                      |
| Tools                      | 4 x Screws               |

| CERTIFICATION                                    |                        |
|--------------------------------------------------|------------------------|
| Windows Certification                            | Windows 10, Windows 11 |
| EU Energy Level Certification                    | Yes (Level-E)          |
| China Energy Efficiency Standard                 | Tier 2                 |
| TÜV Rheinland Low Blue Light (Hardware Solution) | Yes                    |
| Eyesafe Display Certification                    | Yes (Eyesafe 2.0)      |



<sup>1</sup> Moving Picture Response Time (MPRT) improves the response time and reduces motion blur in the monitor. Enabling MPRT will disable AMD FreeSync™, and you may notice a negligible flicker. | <sup>2</sup> Supports 1920 x 1080 @ 240Hz as specified in HDMI 2.1. | <sup>3</sup> Supports 1920 x 1080 @ 320Hz as specified in DP 1.4. Maximum bandwidth: 32.4Gbps. | <sup>4</sup> Formerly Lenovo Display Control Center. Supports Windows 10 & 11, Mac OS (functions vary across systems).

© 2025 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A. Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others. Specifications may vary depending upon region.

