

Lenovo 300e Yoga Chromebook Gen 4

Powered by MediaTek Kompanio 520 processor, this lightweight, convertible device is purpose-built with the versatility to help professionals annotate documents and collaborate easily. It comes with up to 16 hours of battery life enabling users to work from anywhere without any hassle. Plus, dual USB 3.2 Gen1, USB-C 3.2 Gen1, HDMI, and a 3.5-mm headphone or microphone combo jack allow users to connect to peripherals or plug-in headphones for listening to meetings on the go.



Redefining possibilities with powerful performance and groundbreaking on-device AI

Purpose-built for modern education. Robust, secure, and easy to manage, our laptops offer versatile performance and collaboration tools to support teachers and students in the classroom or at home.

The 11.6-inch multi-touch display provides a rich visual experience while its 360-degree hinge allows for a seamless transition between use modes for reading, content creation, or presentations. Additionally, with optional Lenovo USI pen navigate through documents easily.

Configured with up to 64GB SSD storage and up to 8GB LPDDR4 memory, this device enables multitasking productivity helping professionals with faster retrieval of detailed spreadsheets.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo Essential Compact Wireless Mouse



- Compact and easy to carry, weighs just under 50g (1.76oz)
- Ergonomic and ambidextrous design with 3 buttons
- Highly durable design, tested to last up to 8 million clicks

PN: 4Y50R20864 – (with battery) 4Y50R20865 – (w/o battery)

Lenovo Go Wireless Numeric Keypad



- 21-key numeric keypad with industry-leading scissor switch keys
- Minimalist design with ultra slim profile at 13 mm with dedicated productivity keys (Calculator, Tab, Equal, Esc keys)
- Rechargeable , up to 3 months use in single charge (may vary based on usage)

PN: 4Y41C33791, GY41C33979

Lenovo 300e Yoga Chromebook Gen 4

Performance

Processor
MediaTek Kompanio 520

Operating System*
ChromeOS

Graphics
ARM Mali-G52 2EE MC2 GPU (integrated)

Memory
4GB LPDDR4x-3733, soldered
8GB LPDDR4x-3600, soldered

Storage¹
32GB eMMC 5.1 on systemboard
64GB eMMC 5.1 on systemboard

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio*
High Definition (HD) Audio
Stereo speakers, 2W x2, optimized with Waves MaxxAudio
Single microphone or two microphones

Camera*
Front HD 720p, with privacy shutter
Front HD 720p, with privacy shutter; rear 5.0MP

Battery²
47Wh battery (up to 19.36 hr), Rapid Charge with 65W AC adapter

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*
45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0

Design

Display³
11.6" HD (1366x768) IPS glossy 16:9
- 250nits, 50% NTSC, Anti-fingerprint, 60Hz, Corning Gorilla Glass, touch

³IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Multimode
Laptop, tent, stand, and tablet modes supported by 360° hinge

Pen*
Lenovo Integrated Pen*

Keyboard
Chrome keyboard, 6-row, spill-resistant,
Anti-pick proof keycaps with full skirt design

Touchpad
Mylar surface touchpad
60.5 x 104 mm (2.38 x 4.09 inches)

Dimensions⁴
287 x 200 x 18.6 mm (11.3 x 7.9 x 0.73 inches)

⁴The system dimensions may vary depending on configurations.

Weight⁵
1.33 kg (2.93 lbs)

⁵The system weight is approximate and may vary depending on configurations

Color
Graphite grey

Case material
PC-ABS (top)
PC-ABS (bottom)

Connectivity

WLAN + Bluetooth*
Mediatek Wi-Fi 6 MT7921, 802.11ax, Bluetooth 5.3

Ports
2x USB 3.2 Gen 1
1x USB-C 3.2 Gen 1 (data, PD, DP)
1x HDMI 1.4b
1x Headphone / microphone combo jack (3.5mm)

Security & Privacy

Security
Google Security Chip H1
Camera privacy shutter
Kensington Nano Security Slot

Environmental

Material
90% recycled content in PIC cushion
50% Ocean-Bound recycled plastic in Ocean-bound plastic bag
Bamboo fiber screen film

Certifications

Green Certifications^{6 7 8}
ENERGY STAR 9.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 9.0
RoHS compliant

⁶The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁷EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

⁸EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.