

Lenovo Chrome 100e G5 M89

Powered by the MediaTek Kompanio 540 processor, this Chromebook offers dependable, energy-efficient performance for everyday business use. With 8GB LPDDR5-6400 memory and up to 64GB SSD storage, professionals can seamlessly manage multiple browser tabs, spreadsheets, and collaboration applications at once, boosting productivity and minimizing interruptions. Moreover, a 50Wh rechargeable Li-ion battery with Rapid Charge Pro technology provides all-day power, supporting extended work sessions without frequent recharging.



Redefining possibilities with powerful performance and groundbreaking on-device AI

Whether you're crunching numbers, analyzing market trends, or collaborating on presentations, these laptops, equipped with the latest-generation processors and ample memory, ensure unparalleled efficiency and reliability.

Dual 2W stereo speakers, enhanced with Waves MaxxAudio®, deliver rich, clear audio for virtual meetings and training sessions, enabling effective communication. The integrated dual-microphone array ensures precise voice capture during calls, even in shared or noisy work environments.

The 11.6" HD IPS display enhances the readability of documents and dashboards, helping to reduce eye strain during extended work sessions. Furthermore, the multi-touch capability allows professionals to easily navigate, zoom, scroll, and switch between documents or web applications using intuitive touch gestures.

The built-in 720p HD front camera enhances professional presence during virtual meetings, while the integrated privacy shutter provides added peace of mind when the camera is not in use.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Lenovo 65W USB-C AC Travel Adapter

- Ultraportable, lightweight design perfect for frequent commutes and travel
- Charge USB-C devices up to 65W. Universal travel plugs cover most regions and are easily replaceable
- Convenient carry pouch for travelers included



PN: 40AW0065WW GOA6N065WW 40AW0065EU-(EU plug)

Lenovo Go Wireless Multi-Device Mouse

- Compact ambidextrous design, programmable Utility Button on the side, default functions optimized for Teams calls
- Connects to up to 3 devices via 1x USB-C dongle, 2x Bluetooth 5.0; quick switch button to jump control across devices
- Comes with a blue optical sensor that tracks on most surfaces and wireless Qi or wired USB-C fast-chargeable battery



PN: 4Y51C21217

Lenovo Chrome 100e G5 M89



Performance

Processor
MediaTek Kompanio 540

Operating System*
ChromeOS

Graphics
Arm Mali-G57 MC2 GPU (integrated)

Memory
4GB LPDDR5-6400, soldered
8GB LPDDR5-6400, soldered

Storage¹
64GB UFS 2.2 on systemboard

¹The storage capacity supported is based on the test results with current
Lenovo storage offerings.

Audio*
High Definition (HD) Audio, Smart Amplifier (AMP)
2W x2, optimized with Waves MaxxAudio
Dual-microphone array

Camera*
HD 720p, with privacy shutter

Battery²
50Wh (up to 14 hr) battery, Rapid Charge Pro

²Battery life claims are approximate maximum. Actual result will vary
depending on many factors and the maximum battery capacity will
decrease with time and use.

Power Adapter*
65W USB-C adapter, PD 3.0

Design

Display³
11.6" HD (1366x768) IPS glossy 16:9, 250nits, 50% NTSC, touch
11.6" HD (1366x768) IPS Anti-glare 16:9, 250nits, 50% NTSC

³IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard
6-row, backlight

Touchpad
Mylar surface touchpad, 60.5 x 104 mm (2.38 x 4.09 inches)

Dimensions⁴
288.9 x 210 x 18.5 mm (11.37 x 8.27 x 0.73 inches)

⁴The system dimensions may vary depending on configurations.

Weight⁵
Models with touch panel: starting at 1.26 kg (2.78 lbs)
Models with non-touch panel: Starting at 1.22 kg (2.69 lbs)

⁵The system weight is approximate and may vary depending on
configurations

Color
Luna grey

Case material
PC-ABS (top)
PC-ABS (bottom)

Connectivity

WLAN + Bluetooth*
AMD RZ616, 802.11ax (Wi-Fi 6E), Bluetooth 5.3
Mediatek MT7925, 802.11be (Wi-Fi 7), Bluetooth 5.3

WWAN*
4G LTE CAT6*

Ports
2x USB-A (USB 5Gbps)
2x USB-C (USB 5Gbps), with USB PD 45-65W & Display Port
1x HDMI 1.4b
1x Headphone / microphone combo jack (3.5mm)

Docking
Docking support via USB-C

Security & Privacy

Security
Google Security Chip H1
Camera privacy shutter
Kensington Nano Security Slot

Environmental

Material
50% PCC recycled plastic used in D cover
30% PCC recycled plastic used in keyboard keycaps and frame
90% PCC recycled plastic used in the battery and adapter enclosure pack
Recycled aluminum keyboard bracket
Recycled steel touchpad bracket
90% recycled sustainable content in packaging

Certifications

Green Certifications⁶
ENERGY STAR 9.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified, generation 10
RoHS compliant

⁶The items listed under the "Green Certifications" section may not only refer
to certification but also registration or self-declaration.

Other Certifications
ASTM F963*
MIL-STD-810H military test passed
TÜV Rheinland Low Blue Light (Software Solution)

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2025 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.