

ThinkBook 14 G9 IPL

Designed for momentum beyond the office, this laptop supports mobile professionals as they analyze data, collaborate remotely, and create on the move. Powered by Intel Core Ultra 5 / 7 Processor (Series 3) with an AI-enabled NPU up to 49 TOPS and Windows 11, it accelerates multitasking, predictive workflows, and Copilot-assisted research. Up to 64GB DDR5 memory, fast PCIe NVMe storage, and Intel integrated graphics ensure smooth transitions between presentations, analytics, and creative reviews, while Dolby Audio and an FHD IR camera elevate virtual meetings for distributed teams across industries.



Redefining possibilities with powerful performance and groundbreaking on-device AI

ThinkBook combines the style and user experience of consumer devices with the security and business-class support of ThinkPad.

A lightweight 1.36 kg chassis with a 14-inch 16:10 display supports travel-heavy roles, enabling detailed reviews and touch interaction. Meanwhile, a 64Wh battery with Rapid Charge Pro and Modern Standby keeps professionals productive between flights, sites, and meetings across diverse work environments.

With Thunderbolt 4 docking, Wi-Fi 7 connectivity, TPM 2.0 security, and recycled materials, it adapts to secure offices and hybrid setups, helping modern professionals stay compliant, connected, and environmentally responsible.

Efficient power consumption supports productivity throughout the day. Long battery life, Modern Standby, and Rapid Charge Pro reduce charging interruptions, enable quick power top-ups, and ensure consistent performance during extended mobile workdays.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Accessories

Thinkpad 15.6" Essential Plus Backpack

- Made with recycled PET, equivalent to over 8 plastic bottles
- Spacious compartments keep your devices and essentials secure, organized, and accessible
- Ballistic nylon and rugged hardware protect against weather and daily wear.



PN: 4X41A30364

Lenovo Essential Wireless Combo Keyboard & Mouse Gen 2

- Embrace the freedom of a clutter-free and cable-free work setup.
- Ergonomically sculpted cups and low-profile island keys for maximum comfort.
- A 2.4 MHz receiver for a seamless keyboard and mouse connection.



PN: 4X31N50708 – 4X31N50757

ThinkBook 14 G9 IPL



Performance

Processor

Intel Core Ultra 5 / 7 Processor (Series 3)

AI PC Category*

Copilot+ PC

Operating System*

Windows 11 Pro or Home

NPU*

Up to 49 TOPS

Graphics

Intel Graphics (integrated)

Memory¹

Up to 64GB DDR5-5600, 2x SODIMM

¹Maximum memory is only to test technical readiness of notebook but not shipped by Lenovo.

Storage²

Up to two M.2 PCIe NVMe SSD
M.2 2242 SSD up to 2TB
M.2 2280 SSD up to 2TB

²The system supports dual SSD via two M.2 slots, but Lenovo offers only one SSD configuration with a second slot for user self-expansion. The max storage capacity is only technical readiness and may be different from current Lenovo storage offerings.

Audio*

High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Dual-microphone array with smart noise-cancelling

Camera*

FHD 1080p + IR hybrid, with privacy shutter
5.0MP, with privacy shutter

Battery³

48Wh or 64Wh battery, up to 13.88 hr
48Wh battery supports Rapid Charge Pro

³Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter*

65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display⁴

14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 45% NTSC, 60Hz
- 400nits, 45% NTSC, 60Hz, In-cell touch
14" 2.8K (2880x1800) IPS Anti-glare 16:10
- 500nits, 100% sRGB, 120Hz

⁴IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Screen-to-Body Ratio

90%

Keyboard

6-row, spill-resistant, Copilot key, optional backlight

Touchpad

Mylar surface touchpad
75 x 120 mm (2.95 x 4.72 inches)

Dimensions⁵

313.5 x 224 x 17.5 mm (12.34 x 8.82 x 0.69 inches)

⁵The system dimensions may vary depending on configurations.

Weight⁶

Starting at 1.36 kg (2.99 lbs)

⁶The system weight is approximate and may vary depending on configurations

Color

Arctic grey, dual-tone design

Case material

Aluminium (top), aluminium (bottom)
Aluminium (top), PC-ABS (bottom)

Special Features

Modern Standby

Connectivity

Ethernet*

Gigabit onboard Ethernet

WLAN + Bluetooth*

802.11ax (Wi-Fi 6), 802.11be (Wi-Fi 7)
Bluetooth 5.3 or 5.4
Up to Intel Wi-Fi 7 BE213, 802.11be, Bluetooth 5.4

Ports

1x USB-A (USB 5Gbps)
1x USB-A (USB 5Gbps), Always On
2x Thunderbolt 4, with USB PD 45-65W & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x SD card reader
1x Ethernet (RJ-45)
1x Headphone / microphone combo jack (3.5mm)

Docking

Docking support via Thunderbolt

Security & Privacy

Security

Discrete TPM 2.0
Kensington Nano Security Slot
Touch style fingerprint reader on power button, match-on-chip*
Camera privacy shutter
IR camera for Windows Hello (facial recognition)*

Environmental

Material

30% PCC recycled plastic used in the battery pack enclosure
50% PCC recycled plastic used in key caps
30% PCC recycled plastic used in speaker
90% PCC recycled plastic used in standard 65W adapter
Plastic free packaging (for EMEA & NA)
Dry pressed pulp cushion
90% recycled content in OBP bag or bamboo fiber ba
FSC certified content in carton box

Certifications

Green Certifications^{7 8 9}

ENERGY STAR 9.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified, generation 10
RoHS compliant

⁷The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁸EPEAT registration and ENERGY STAR certification are optional and only available on the models with preloaded OS.

⁹EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications

TÜV Rheinland Low Blue Light (Software Solution)*
TÜV Rheinland Low Blue Light (Hardware Solution)*
Eyesafe Certified 2.0*
MIL-STD-810H

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2025 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.