

LENOVO L15 MOBILE MONITOR

CRAFTED TO CATCH YOUR ATTENTION

BALANCING WORK AND LEISURE WITH AN ULTRA-PORTABLE MONITOR

For users who are constantly on the move, engaged in some work from home, or busy studying in a crowded dormitory, the ultra-portable Lenovo L15 mobile monitor makes perfect sense. Weighing only 860 g¹ with an ultra-slim 6mm head thickness and an integrated stand, the L15 is easy to carry around and fits on the corner of a multipurpose table or shelving unit. With its 15.6-inch screen, the L15 is a handy 'second screen' that gives you flexibility whether you are taking notes while attending online lectures or simply binge-watching your favorite content. It easily connects to Notebooks of any screen size via a USB Type-C² cable, and power pass-through support lets you charge the PC and power the monitor simultaneously. With eye care technology to prevent eye strain and Lenovo Artery software³ to control settings, the L15 delivers an uncomplicated and delightful experience.

FEATURES OF LENOVO L15 MOBILE MONITOR



One Display for Everyone

The FHD 1920 x 1080 resolution makes your display experience, whether watching videos or browsing web-pages, a pleasurable one. The In-Plane Switching (IPS) panel offers impressive screen clarity and wide viewing angles of up to 178°, which make for distortion free images no matter where you place it. The 3-side narrow bezels look premium and provide wider screen real-estate for optimum use, so you can view content without distractions.



Connectivity with Convenience

The L15 comes equipped with two USB Type-C² ports, which have data, power, audio, and video transfer capabilities—a single-cable solution for your connectivity needs. The USB Type-C port supports power pass-through, up to 65W⁴ to charge your notebook or smartphone and power the L15 simultaneously. This keeps your study corner clear of troublesome snaking cables, offering a clutter-free desk space. Exclusive Lenovo Artery software³ provides advanced and assistive tools to help you seamlessly manage and control your L15 monitor and other devices.



Stylish and Purposeful

Sleek design—enhanced by the raven black narrow bezel design—makes for wider screen space in a premium package. Ultra-slim build with height adjustment lets you carry it with ease and position the display at eye level atop a desk so you can enjoy multimedia or engage in learning anytime, anywhere. Harmful blue light emissions are reduced with the L15's TÜV Rheinland Low Blue Light technology so users can comfortably binge content or get work done without eye strain.

Lenovo L15 Mobile Monitor

DISPLAY

Panel Size

15.6-inch

Screen Dimensions

360.0 mm x 234.0 mm

Panel Type

3-side Narrow Bezel Design
In-Plane Switching

Active Area

344.2 mm x 193.6 mm

Backlight

WLED

Aspect Ratio

16:9

Resolution

1920 x 1080

Pixel pitch

0.1793 mm x 0.1793 mm

Pixel Per Inch (DPI/PPI)

141

Viewing Angle (H x V @ CR 10:1)

178° / 178°

Response Time

6ms (Extreme Mode)
14ms (Normal Mode)

Refresh Rate

60 Hz

Brightness (typical)

250 cd/m²

Contrast Ratio (typical)

1000:1

Dynamic Contrast Ratio (typical)

3M:1

Color Gamut

45% NTSC (CIE 1931)

Color Support (typical)

16.7 Million

Color Depth

8-bit

Anti-glare

Yes

CONNECTIVITY

Video Signal

2 x USB Type-C 3.2 Gen1
(DP1.2 Alt Mode)

USB Hub

Yes

USB Upstream

1 x USB2.0 (1 by USB Type-C²)

USB Downstream

1 x USB2.0 (1 by USB Type-C²)

SPECIAL FEATURES

Software

Lenovo Artery³
(Lenovo DisplayControl Center)

Others

Height Adjustment

POWER

Power Consumption (typical/max)

8W / 9.5W

Power Consumption Sleep/Off Mode

< 0.3W

Power Consumption Switch-Off Mode

< 0.3W

Power Supply

External

USB Type-C (DP Alt Mode) power delivery

Up to 65 W⁴

USB Type-C (Downstream) power delivery

Up to 65 W⁴

Voltage Required

DC 5/9/15/20 V

MECHANICAL

Lift (Max range)

10 mm

VESA Mount Capability

Yes (2 screw holes, 100 mm)

Kensington Lock Slot

Yes

Cable Management

Yes

Bezel Color

Raven Black

Bezel Width (side)

7.3 mm

Bezel Width (top/bottom)

7.3 / 31.9 mm

DIMENSION

Size Packed (D x H x W, mm/inch)

407.9 x 75.9 x 279.9 mm
16.06 x 2.99 x 11.02 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)

235.5 x 360.0 x 108.4 mm
9.27 x 14.17 x 42.67 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)

245.5 x 360.0 x 108.4 mm
9.66 x 14.17 x 42.67 inches

Weight Packed (kg/lb)

1.7 kg / 3.7 lbs.

Weight Unpacked (kg/lb)

0.86 kg / 1.90 lbs.¹

WHAT'S IN THE BOX

1 x L15 Monitor
1 x Pair of clips
1 x Sleeve
1 x USB Type-C to Type-C cable (1m)
Quick setup guide

CERTIFICATION

CCC

Yes

EPEAT

Silver

RoHS (EU 2002/95/EC)

Yes

Windows Certification

Window 7, Windows 10

China Energy Efficiency Standard

Tier 2

TÜV Rheinland Low Blue Light

Yes

TÜV Rheinland Flicker Free

Yes



¹Actual weight may vary due to components, manufacturing process and options.

²USB Type-C[®] and USB-C[®] are registered trademarks of USB Implementers Forum.

³This software can only be used with Windows 10.

⁴Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting.

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen2x2.

© 2021 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo