



SPECIFICATIONS

Panel Size	34"
Active Display Area (mm)	800.06 (H) x 337.06 (V)
Curvature	Curve 1800R
Panel Type	QD-OLED
Panel Resolution	3440 x 1440 (UWQHD)
Pixel Pitch (H x V)	0.2315 (H) x 0.2315 (V)
Aspect Ratio	21:9
Brightness (nits)	SDR: 300 HDR: 1300
Contrast Ratio	1500000:1 (Typ.)
DCR	N/A
Signal Frequency	30~596.2 KHz (H) / 48~360 Hz (V)
ACTIVATED RANGE	48~360Hz
Refresh Rate	360Hz
Response time	0.03ms (GtG)
DYNAMIC REFRESH RATE TECHNOLOGY	NVIDIA G-SYNC Compatible AMD FreeSync™ Premium Pro
HDR Support	VESA DisplayHDR True Black 500
VESA ClearMR Certified	VESA ClearMR 18000
Video ports	2x HDMI™ 2.1 (UWQHD@360Hz) 1x DisplayPort 2.1a (UHBR13.5) 1x Type-C (DP alt.) w/ 98W PD
USB ports	2x USB 5Gbps Type-A 1x USB 5Gbps Type-B
Audio ports	1x Headphone-out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	98% / 99% / 139% (CIE1976 Standard)
Surface Treatment	Anti-Reflection
Display Colors	1.07B, 10 bits
Frameless Design	Yes
PIP / PBP Function	Yes
Power Type	Internal Power Board
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 15°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Pivot)	-10° ~ 10°
Adjustment (Height)	0 ~ 110 mm
Kensington Lock	Yes
VESA Mounting	100 x 100 mm

FEATURES



QD-OLED Display

MSI's renowned QD tech, combined with the latest OLED panel technology, these displays exhibit the best picture quality and incredible high contrast when gaming.



5th-gen QD-OLED

The 5th-gen Tandem QD-OLED pixel arrangement utilizes the RGB Stripe layout, fundamentally elevating display quality. This design minimizes color fringing and significantly enhances the clarity of text.



360Hz High Refresh Rate

Experience smooth gaming with a blazing fast refresh rate, that gives you the upper hand in fast-moving games.



0.03ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 0.03ms GtG response time.



OLED Care 3.0

MSI developing a more advanced version to provide several care services and significantly reduce the chances of OLED screen aging.



AI Care Sensor

AI Care integrates AI sensors to dynamically optimize OLED protection based on real-time usage, making the system even smarter.




USB Type-C Power Delivery 98W

Built-in an USB Type-C connection with 98W power delivery allows you to effortlessly connect to and charge your devices.

Dimension with Stand (W x D x H)	812.83 x 228.3 x 543.08 mm (32 x 8.9 x 21.3 inch)
Dimension without Stand (W x D x H)	812.83 x 118.54 x 372.09 mm (32 x 4.6 x 14.65 inch)
Weight (NW / GW)	7.77 kg (17.13 lbs) / 13.49 kg (29.7 lbs)
Carton Dimension (W X D X H)	995 x 200 x 505 mm (39.1 x 7.87 x 19.8 inch)
Accessories	1x HDMI™ Cable (2.1) 1x DisplayPort Cable (2.1a) 1x USB Type-B to A Cable 1x Power Cord (C13) 1x Quick Guide 4x VESA Wall Mount Screw 1x Fiber Cloth, 1x Color Report
Note	HDMI™: 3440 x 1440 (Up to 360Hz) DisplayPort: 3440 x 1440 (Up to 360Hz) Type-C: 3440 x 1440 (Up to 360Hz) Support: HDMI™ CEC, KVM, PIP/PBP
Warranty	3 years (including panel burn-in)

CONNECTIONS



- 1. Kensington Lock
- 2. AC-in
- 3. 5-way Joystick Navigator
- 4. Headphone-out
- 5. 2x HDMI™ 2.1 (UWQHD@360Hz)
- 6. DisplayPort 2.1a (UHBR13.5)
- 7. Type-C (DP alt.) w/ 98W PD
- 8. USB 2.0 Type-B
- 9. 2x USB 2.0 Type-A