



SPECIFICATIONS

PANEL SIZE	27"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	144Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GtG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	300 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1500:1
DCR	100000000:1
Signal Frequency	52.85~158.54 KHz(H) / 48~144 Hz(V)
ADOBE RGB / DCI-P3 / SRGB	83% / 87% / 116% (CIE 1976)
ACTIVE DISPLAY AREA (MM)	597.888(H) x 336.312(V)
PIXEL PITCH (H X V)	0.3114(H) x 0.3114(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M, 8 bits (6 bits + FRC)
HDR SUPPORT	HDR Ready
VIDEO PORTS	1x HDMI™ 2.0 (FHD@144Hz) 1x Type-C (DP alt.) w/ 15W PD
USB Ports	N/A
Audio Interface	1x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	2W x2
Webcam	N/A
VESA MOUNTING	100 x 100 mm
POWER TYPE	External Adaptor 12V 5.4A
POWER INPUT	100~240V, 50/60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	AMD FreeSync™
ADJUSTMENT (TILT)	-5° ~ 20°
ADJUSTMENT (SWIVEL)	N/A
ADJUSTMENT (PIVOT)	N/A
ADJUSTMENT (HEIGHT)	N/A
Dimension with Stand (W x D x H)	611.7 x 206.8 x 453.1 mm (24.08 x 8.14 x 17.84 inch)
Dimension without Stand (W x D x H)	611.7 x 51.4 x 355.5 mm (24.08 x 2.02 x 13.0 inch)

FEATURES



IPS Panel with Wide Viewing Angle

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best.



144Hz Game Ready

Thanks to the high refresh rate and adaptive-sync support, our gaming experience becomes completely smooth and free from interruptions.



PerfectEdge

Set-up multi-display immensely with the 4-side edgeless design and enjoy the wider and more immersive view.



Type C Display

Allows you to connect the latest devices more conveniently and with less trouble.



EyesErgo

An eye care solution designed with ergonomics in mind. Includes Eye care & Ergonomic features.



Accessory Slot Design

Enjoy a clean table with the accessory slot design where you can put MSI Pen or Smartphone, and you will not miss important messages anymore.



Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.



VESA Mountable

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.



PRO MP272 E14C

SLIM, SLEEK, SMOOTH

CARTON DIMENSION (W X D X H)	688 × 128 × 440 mm (27.09 x 5.04 x 17.32 inch)
WEIGHT (NW / GW)	3.7 kg (8.16 lbs) / 6.1 kg (13.45 lbs)
CERTIFICATES	CB/CE Energy Star
VIDEO INPUT COMPATIBILITY	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
ACCESSORIES	1x HDMI™ Cable (1.4), Type C USB 3.2 Gen 1 Cable, 1x Quick Guide, 1x Power Cord (C13), 1x Power Adaptor
Note	HDMI™: 1920 x 1080 (Up to 144Hz) Type-C: 1920 x 1080 (Up to 144Hz) Support: HDMI™ CEC/ MSI Power Link, FW Update ; Non Support: PIP/PBP, KVM

CONNECTIONS



- 1. 5-Way Navi Key
- 2. DC-in
- 3. 1x HDMI™ 2.0 (FHD@144Hz)
- 4. 1x Type-C (DP alt.) w/ 15W PD
- 5. 1x Headphone-out
- 6. Kensington Lock