



SPECIFICATIONS

PANEL SIZE	23.8"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	144Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GTG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	300 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CURVATURE	Flat
CONTRAST RATIO	1500:1
DCR	100000000:1
Signal Frequency	52.85~158.54 KHz(H) / 48~144 Hz(V)
ADOBE RGB / DCI-P3 / SRGB	85% / 84% / 107% (CIE1976)
ACTIVE DISPLAY AREA (MM)	527.04(H) x 296.46(V)
PIXEL PITCH (H X V)	0.2745(H) x 0.2745(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M, 8 bits (6 bits + FRC)
HDR SUPPORT	HDR Ready
VIDEO PORTS	1x HDMI™ 2.0 (FHD@144Hz) 1x DisplayPort 1.2a 1x D-Sub (VGA)
AUDIO PORTS	1x Line-in 1x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	2W x2
Webcam	N/A
VESA MOUNTING	100 x 100 mm
POWER TYPE	Internal Power Board
POWER INPUT	100~240V, 50/60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
Activated Range	48~144Hz
ADJUSTMENT (TILT)	-5° ~ 20°
ADJUSTMENT (SWIVEL)	-45°~45°
ADJUSTMENT (PIVOT)	-90°~90°
ADJUSTMENT (HEIGHT)	0~130 mm
Dimension with Stand (W x D x H)	539.36 x 226.93 x 519.29 mm (21.23 x 8.93 x 20.44 inch)

FEATURES



IPS Grade Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



PerfectEdge

Set-up multi-display immensely with the 4-side edgeless design and enjoy the wider and more immersive view.



144Hz Game Ready

Thanks to the high refresh rate and adaptive-sync support, our gaming experience becomes completely smooth and free from interruptions.




EyesErgo

An eye care solution designed with ergonomics in mind.



Eye-Q Check

Help have self-check eyes & remind to take a rest while using the monitor for a long time.



Adjustable stand

Adjust the stand to the angle that is most suitable for you to keep yourself work comfortably.



Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.



Mini-PC Mountable

The mini PC can be conveniently mounted behind the monitor, keeping your desk clutter-free and organized.



PRO MP245PG E14

SLIM, SLEEK, SMOOTH

Dimension without Stand (W x D x H)	539.36 x 51.71 x 314.67 mm (21.23 x 2.04 x 12.39 inch)
CARTON DIMENSION (W X D X H)	600 x 125 x 500 mm (23.62 x 4.92 x 19.69 inch)
WEIGHT (NW / GW)	5.25 kg (11.57 lbs) / 7.51 kg (16.56 lbs)
CERTIFICATES	CB/CE Energy Star
VIDEO INPUT COMPATIBILITY	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook All trademarks and the registered trademarks are the property of their respective owners.
ACCESSORIES	1x HDMI™ Cable (1.4), 1x Power Cord (C13), 1x Quick Guide, 4x Stand Screw, 1x VESA Plate, 4x VESA Plate Screw
Note	HDMI™: 1920 x 1080 (Up to 144Hz) DisplayPort: 1920 x 1080 (Up to 144Hz) D-Sub (VGA): (Up to 60Hz) Support: HDMI™ CEC/ MSI Power Link; Non Support: KVM, PIP/PBP

CONNECTIONS



- 1. 5-way Navigator
- 2. AC-in
- 3. 1x DisplayPort 1.4a
- 4. 1x HDMI™ 2.0 (FHD@144Hz)
- 5. 1x D-Sub (VGA)
- 6. 1x Line-in
- 7. 1x Headphone-out
- 8. Kensington Lock