

# ThinkPad P14s Gen 6 (Intel)

Driven by up to Intel® H Series Core Ultra 9 processor with support for as many as 16 cores, this laptop empowers mobile professionals with the speed to manage resource-intensive workloads. Integrated Intel® AI Boost, offering up to 13 TOPS, accelerates intelligent applications, from predictive analytics to creative design tools. Combined with up to 96GB DDR5 memory, multitasking feels seamless even across demanding software. And with the rapid connectivity of Wi-Fi® 7, collaboration, data transfers, and virtual meetings remain smooth wherever professionals choose to work.



## Elevate Professional Endeavors with Powerhouse Workstations

Designed for business users who tackle compute-intensive workflows. With professional-grade graphics and powerful, multi-core processors, Lenovo sets the standard for mobile workstations and ensures best-in-class reliability even when you're away from the office.

Equipped with up to NVIDIA® RTX PRO 1000 Blackwell Generation 8GB graphics, it delivers outstanding performance for visualization, rendering, and AI modeling. The 14.5" WQXGA display shines at 400 nits with add-on film touch capabilities and a 100% sRGB color gamut for precise, vibrant visuals.

With up to one 2TB storage, it accommodates large datasets, creative projects, and essential files with ease. Enhanced by Discrete TPM 2.0, a touch style fingerprint reader, and optional ultrasonic human presence detection, professionals gain robust data security.

With up to Intel® H Series Core Ultra 9 processor, Integrated Intel® AI Boost, and up to 96GB DDR5 memory, performance becomes the defining factor for mobile users, enabling seamless multitasking, faster insights, and uncompromised productivity anywhere.

## Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



### Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

## Accessories

### Lenovo Wired ANC Headset Gen 2

- Active Noise Cancellation
- Certified for Zoom and Microsoft Teams
- Inline Control Box with LED Indication



PN: Teams : 4XD1M45627, UC : 4XD1M39029

### Lenovo Essential Wireless Combo Keyboard & Mouse Gen 2

- Embrace the freedom of a clutter-free and cable-free work setup.
- Ergonomically sculpted cups and low-profile island keys for maximum comfort.
- A 2.4 MHz receiver for a seamless keyboard and mouse connection.



PN: 4X31N50708 – 4X31N50757

# ThinkPad P14s Gen 6 (Intel)

## Performance

### Processor

Intel H Series Core Ultra 5/7 /9 Processor (Series 2)

### AI PC Category\*

AI-Ready Workstations

### Operating System\*

Windows 11 Pro  
Windows 11 Home  
Windows 11 Home Single Language  
Ubuntu Linux  
Red Hat Enterprise Linux (certified only)

### NPU

Integrated Intel AI Boost, up to 13 TOPS

### Graphics

Intel Arc Graphics eligible (integrated)  
NVIDIA RTX PRO 500 Blackwell Generation Laptop GPU  
NVIDIA RTX PRO 1000 Blackwell Generation Laptop GPU

### Memory

Up to 96GB DDR5-5600, 2x CSODIMM / SODIMM slots

### Storage<sup>1</sup>

Up to one 2TB M.2 2280 Gen 5 Performance SSD

<sup>1</sup>The storage capacity supported is based on the test results with current Lenovo storage offerings.

### Audio\*

High Definition (HD) Audio  
Dolby Audio speakers  
Dual-microphone array, Dolby Voice\*

### Camera\*

5.0MP + IR, with privacy shutter and optional Ultrasonic Human Presence Detection, temporal noise reduction  
5.0MP with privacy shutter, temporal noise reduction

### Battery<sup>2</sup>

57Wh or 75Wh battery, Rapid Charge

<sup>2</sup>Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

### Power Adapter\*

100W USB-C adapter, PD3.0

## Design

### Display<sup>3</sup>

14.5" WUXGA (1920x1200) IPS Anti-glare  
- 400nits, 45% NTSC, 60Hz, Eyesafe, TÜV Low Blue Light  
- 400nits, 45% NTSC, 60Hz, Eyesafe, TÜV Low Blue Light, touch  
14.5" WQXGA (2560x1600) IPS Anti-glare,  
- 400nits, 100% sRGB, 90Hz, Eyesafe, TÜV Low Blue Light  
14.5" 3K (3072x1920) IPS Anti-glare  
- 500nits, 100% DCI-P3, 120Hz, Eyesafe, TÜV Low Blue Light

<sup>3</sup>IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

### Keyboard

6-row, spill-resistant, Copilot key, backlight

### Touchpad

TrackPoint and glass-like Mylar surface TrackPad  
60 x 115 mm (2.36 x 4.53 inches)

### Dimensions<sup>4</sup>

325.5 x 227.6 x 11.2 / 15.1 (front / rear), 21.7 (maximum) mm  
12.81 x 8.96 x 0.44 / 0.59 (front / rear), 0.85 (maximum) inches

<sup>4</sup>The system dimensions may vary depending on configurations.

### Weight<sup>5</sup>

Starting at 1.60 kg (3.53 lbs)

<sup>5</sup>The system weight is approximate and may vary depending on configurations

### Color

Black

### Case material

Aluminium (top), aluminium (bottom)

## Connectivity

### Ethernet\*

Gigabit onboard Ethernet

### WLAN + Bluetooth\*<sup>6</sup>

Intel Wi-Fi 7 BE201, 802.11be, Bluetooth 5.4

<sup>6</sup>Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

### Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1)  
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On  
2x Thunderbolt 4 (with Power Delivery 3.0 support)  
1x HDMI 2.1, up to 4K/60Hz  
1x Headphone / microphone combo jack (3.5mm)  
1x Security keyhole  
1x Ethernet (GbE RJ-45)  
1x Smart card reader\*

## Security & Privacy

### Security

Discrete TPM 2.0  
Kensington Nano Security Slot  
Smart card reader\*  
Touch style MOC fingerprint reader  
Camera privacy shutter  
IR camera for Windows Hello (facial recognition)\*  
Ultrasonic Human Presence Detection\*

## Manageability

### System Management\*

Intel vPro Enterprise\*

## Certifications

### Green Certifications<sup>7 8 9</sup>

ENERGY STAR 9.0  
EPEAT Gold Registered  
TCO Certified, generation 10  
RoHS compliant

<sup>7</sup>The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

<sup>8</sup>EPEAT registration and ENERGY STAR certification are optional and only available on the models with preload OS.

<sup>9</sup>EPEAT is registered where applicable, please see [epeat.net](https://www.epeat.net) for registration status by country.

### Other Certifications

Eyesafe Certified 2.0  
TÜV Rheinland Low Blue Light  
MIL-STD-810H