

# Product data sheet

Specifications



## APC NetShelter Rack PDU Advanced Metered, 0U, 3 Phase, 208V, 28.8kVA 100A, 30 Outlets

APDU11551ME

### Main

|                           |          |
|---------------------------|----------|
| Color                     | Black    |
| Product or Component Type | PDU      |
| PDU Type                  | Metered  |
| Rated power in VA         | 28800 VA |

### Complementary

|                          |                                 |
|--------------------------|---------------------------------|
| Input Voltage            | 208 V AC 3 phase                |
| Height                   | 74.8 in (1900 mm)               |
| Width                    | 2.2 in (56 mm)                  |
| Output Voltage           | 208 V AC 3 phase                |
| Depth                    | 3.0 in (75 mm)                  |
| Product Weight           | 30.9 lb(US) (14 kg)             |
| Mounting Location        | Front<br>Rear                   |
| Mounting preference      | No preference                   |
| Input Plug Type          | IEC 309 100 A                   |
| Mounting Mode            | Rack-mounted                    |
| Rack units               | 0U                              |
| Mounting position        | Vertical                        |
| Input current limits     | 100 A                           |
| Input Frequency          | 50/60 Hz                        |
| Plug standard            | IEC 60309                       |
| Outlet type and quantity | 15 C13/C15/C19/C21<br>15C13/C15 |

### Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| IP Degree of Protection               | IP67                       |
| Ambient air temperature for operation | 23...140 °F (-5...60 °C)   |
| Relative Humidity                     | 5...90 %                   |
| Operating altitude                    | 0...10000 ft               |
| Ambient Air Temperature for Storage   | -4...140 °F (-20...60 °C)  |
| Storage Relative Humidity             | 5...95 %                   |
| Storage altitude                      | 0...50000 ft (0...15240 m) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Ordering and shipping details

|      |              |
|------|--------------|
| GTIN | 731304775652 |
|------|--------------|

## Packing Units

|                        |                       |
|------------------------|-----------------------|
| Unit Type of Package 1 | PCE                   |
| Nbr. of units in pkg.  | 1                     |
| Package 1 Height       | 83.07 in (211 cm)     |
| Package 1 Width        | 13.8 in (35 cm)       |
| Package 1 Length       | 6.5 in (16.5 cm)      |
| Package weight(Lbs)    | 43.7 lb(US) (19.8 kg) |



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

| Materials and Substances               |                                                                                        |
|----------------------------------------|----------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                                    |
| Packaging without single use plastic   | Yes                                                                                    |
| SCIP Number                            | 7547f066-9302-46d9-96e9-461928dd6901                                                   |
| EU RoHS Directive                      | <a href="#">Compliant By Exemption</a>                                                 |
| REACH Regulation                       | <a href="#">Reference contains Substances of Very High Concern above the threshold</a> |
| PVC free                               | No                                                                                     |
| Silicon free                           | Yes                                                                                    |

### Use Longer

| Lifetime extension |     |
|--------------------|-----|
| Repair             | No  |
| Upgradeability     | Yes |

### Use Again

| Repack and remanufacture |    |
|--------------------------|----|
| Take-back                | No |

Image of product / Alternate images

Alternative

---

