

12W One-Port USB-A Wall Charger, 1x USB-A, iPhone Pro/17/16, iPad, Samsung Galaxy, Portable USB Charger, USB Type A Wall Charger, Black

Product ID: 011NB-WALL-CHARGER



This 12W USB-A wall charger offers reliable, travel-ready power in a compact and lightweight form factor. With foldable prongs and a small footprint (38.9 x 34.6 x 32.8 mm, 1.4 oz / 40 g), it fits easily into a backpack, laptop bag, or purse; ideal for commuting, remote work, or daily use.

Delivering up to 12W (5V/2.4A) of power, the charger supports smartphones, tablets, and accessories including iPhone Pro/17/16, iPad, Samsung Galaxy, and other devices that charge via USB-A cable. Use with USB-A to USB-C or USB-A to Lightning cables (sold separately, e.g., StarTech USB2AC6FBKE or USB31AC1M) for flexible charging across platforms.

A built-in Smart Power Circuit protects against over-current and short-circuit damage. IEC 62368-1 certified through TUV testing, the charger supports 100-240V input for global use. Packaged in Forest Stewardship Council (FSC) certified materials to support sustainable sourcing and reduced environmental impact.

Certifications, Reports and Compatibility



Applications

Features

- **USB-A Charging On the Go**: This compact, lightweight 12W USB-A wall charger with foldable prongs is ideal for travel or everyday use; Supports charging for iPhone Pro / 17 / 16, iPad, Samsung Galaxy, and other

devices that charge via a USB-A cable

- **Reliable 12W Power Output**: Delivers up to 12W (5V/2.4A) for charging phones, tablets, and USB devices; Supports BC 1.2 (7.5W) for USB-C compatibility when proprietary fast-charge modes (e.g., Apple 2.4A) aren't supported; Optimized for USB-A charging
- **Flexible Cable Compatibility**: Designed for use with USB-A to USB-C or USB-A to Lightning cables (sold separately, e.g., StarTech USB2AC6FBKE or USB31AC1M); Supports charging a wide range of modern smartphones and accessories with the appropriate cable
- **Safe, Certified, and Sustainable**: Smart Power Circuit protects against over-current and short-circuit damage; IEC 62368-1 certified through TUV testing; 100-240V input supports global use; Forest Stewardship Council (FSC) certified packaging
- **The IT Pro's Choice**: Our power adapters offer a long-lasting, eco-conscious solution as manufacturers increasingly exclude chargers from new devices; Thoroughly tested in our Innovation Lab to ensure enterprise-grade reliability and operational safety

Connector(s)

Warranty	2 Years
Connector A	1 - NEMA 1-15 Power (North America)
Connector B	1 - USB 2.0 Type-A

Power

Input Voltage	100 - 240 AC
Output Current	5.0V3.0A, 9.0V1.5A (12.0W Max)
Plug Type	NEMA 1-15 Power (North America) Plug

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	20%RH ~ 90%RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	1.5 in [38.9 mm]
Product Width	1.4 in [34.6 mm]

Product Height	1.3 in [32.8 mm]
Weight of Product	1.4 oz [40 g]

**Packaging
Information**

Package Length	3.1 in [8.0 cm]
Package Width	3.7 in [9.3 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	0.0 oz [0.0 g]

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***