



SPECIFICATIONS

PANEL SIZE	27"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	144Hz
RESPONSE TIME	1ms (MPRT) / 4ms (GTG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	250 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1000:1
Signal Frequency	52.8~240.8 KHz(H) / 48~200 Hz(V)
ADOBE RGB / DCI-P3 / SRGB	86% / 86% / 111%
ACTIVE DISPLAY AREA (MM)	527.04(H) x 296.46(V)
PIXEL PITCH (H X V)	0.2745(H) x 0.2745(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M,
COLOR BIT	8 bits (6 bits + FRC)
HDR SUPPORT	HDR Ready
VIDEO PORTS	1x HDMI™ 2.0b (FHD@144Hz) 1x DisplayPort 1.2a 1x Type-C (DP alt.) w/ 65W PD
USB Ports	2x USB 5Gbps Type-A 1x USB 5Gbps Type-B
AUDIO PORTS	1x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	3W x2
VESA MOUNTING	75 x 75 mm
POWER TYPE	Internal Power Board
POWER INPUT	100~240V, 50/60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
ADJUSTMENT (TILT)	-5° ~ 20°
ADJUSTMENT (SWIVEL)	-30° ~ 30°
ADJUSTMENT (PIVOT)	-90° ~ 90°
ADJUSTMENT (HEIGHT)	0 ~ 110 mm
Dimension with Stand (W x D x H)	613.49 x 200.81 x 401.37 mm (24.15 x 7.91 x 15.80 inch)
Dimension without Stand (W x D x H)	613.49 x 63.81 x 362.45 mm (24.15 x 2.51 x 14.27 inch)

FEATURES



IPS Panel with Wide Viewing Angle

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best.



EyesErgo

An eye care solution designed with ergonomics in mind. Includes Eye care & Ergonomic features.



Circular Polarization

Converts harsh digital rays into soft, naturally-polarized light to prevent eye strain and maximize visual comfort.



144Hz Game Ready

Thanks to the high refresh rate and adaptive-sync support, our gaming experience becomes completely smooth and free from interruptions.



Type C 65W Power Delivery

Built-in an USB Type-C connection with 65W power delivery allows you to effortlessly connect to and charge your devices




Delta-E (ΔE) ≤ 2

Factory pre-calibrated to guarantee a truly expressive hues and color accuracy.

CARTON DIMENSION (W X D X H)	613.49 x 63.81 x 362.45 mm (24.15 x 2.51 x 14.27 inch)
WEIGHT (NW / GW)	6.4 kg (14.11 lbs) / 10 kg (22.05 lbs)
ACCESSORIES	1x HDMI Cable (2.0b), 1x Type-C Cable (3.2 Gen 1), 1x USB Type-B to A Cable (3.2 Gen 1), 1x Power Cord, 1x Quick Guide, 4x VESA Wall Mount Screw, Color Report
Note	HDMI™: 1920 x 1080 (Up to 144Hz) DisplayPort: 1920 x 1080 (Up to 144Hz) Type-C: 1920 x 1080 (Up to 144Hz) Support: HDMI™ CEC/ MSI Power Link, KVM 1.0, FW Update, PI Software ; Non Support: PIP/PBP

CONNECTIONS



- 1. 5-Way Navi-Key
- 2. 1x USB 5Gbps Type-B
- 3. 2x USB 5Gbps Type-A
- 4. 1x Type-C (DP alt.) w/ 65W PD
- 5. 1x DisplayPort 1.2a
- 6. 1x HDMI™ 2.0b (FHD@144Hz)
- 7. 1x Headphone-out
- 8. AC-in
- 9. Kensington-Lock