



## SPECIFICATIONS

<b>Panel Size</b>	34"
<b>Active Display Area (mm)</b>	797.22 (H) x 333.72 (V)
<b>Curvature</b>	Curve 1500R
<b>Panel Type</b>	Rapid VA
<b>Panel Resolution</b>	3440 X1440 (UWQHD)
<b>Pixel Pitch (H x V)</b>	0.23175(H) x 0.23175(V)
<b>Aspect Ratio</b>	21:9
<b>Brightness (nits)</b>	SDR: 300 cd/m <sup>2</sup>
<b>Contrast Ratio</b>	3500:1
<b>DCR</b>	100000000:1
<b>Signal Frequency</b>	71.51~285.31KHz(H) / 48~200 Hz(V)
<b>ACTIVATED RANGE</b>	48~200Hz
<b>Refresh Rate</b>	200Hz
<b>Response time</b>	0.5ms (GtG, Min.)
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	Adaptive-Sync
<b>HDR Support</b>	HDR Ready
<b>Video ports</b>	1x DisplayPort 1.4a(HBR3) 2x HDMI™ 2.0b (UWQHD@100Hz)
<b>Audio ports</b>	1x Headphone-out
<b>Viewing Angle</b>	178° (H) / 178° (V)
<b>Adobe RGB / DCI-P3 / sRGB</b>	88% / 90% / 110% (CIE1976 Standard)
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	1.07B, 10 bits (8 bits + FRC)
<b>Console Mode</b>	Supported Resolution & Refresh Rate: 1080p: 60Hz and 120Hz
	HDMI™ CEC: Supported VRR: PS5 and Xbox Supported
<b>Power Type</b>	External Adopter 19V 3.42A
<b>Power Input</b>	100~240V, 50/60Hz
<b>Adjustment (Tilt)</b>	-5°~20°
<b>Adjustment (Swivel)</b>	-30° ~ 30°
<b>Adjustment (Pivot)</b>	-5° ~ 5°
<b>Adjustment (Height)</b>	0 ~ 90 mm
<b>Kensington Lock</b>	Yes
<b>VESA Mounting</b>	75 x 75 mm
<b>Dimension with Stand (W x D x H)</b>	808.60 x 269.97 x 423.97 mm (31.8 x 10.6 x 16.6 inch)

## FEATURES



### 1500R Curved Gaming

Immerse in a captivating experience with a 1500R curvature rate.



### Rapid VA

Provide ultra-fast 1ms GTG response time, make sure the intensity and purity of colors when gaming.



### 200Hz High Refresh Rate

Experience smooth gaming with a blazing fast 200Hz refresh rate, that gives you the upperhand in fast moving games.



### 0.5ms (GtG, Min.) Response Time

Eliminate screen tearing and choppy frame rates with 0.5ms (GtG, Min.) Response Time.



### HDR Ready

Enhance eye-catching details through adjustments in contrast and shadows.




### Console Mode

Optimized for seamless compatibility with gaming consoles like PS5 and Xbox Series X|S.

<b>Dimension without Stand (W x D x H)</b>	808.60 x 119.67 x 363.95 mm (31.8 x 4.7 x 14.3 inch)
<b>Weight (NW / GW)</b>	6.95 kg (15.3 lbs) / 10.75 kg (23.7 lbs)
<b>Carton Dimension (W X D X H)</b>	918 x 214 x 489 mm (36.1 x 8.4 x 19.2 inch)
<b>Accessories</b>	1x DisplayPort Cable (1.4a), 1x Power Cord (C13), 1x AC Adaptor, 1x Quick Guide, 4x VESA Screw
<b>Note</b>	HDMI™: 3440 x 1440 (Up to 100Hz) DisplayPort: 3440 x 1440 (Up to 200Hz) Support: HDMI™ CEC; PIP/PBP; Non Support: KVM

## CONNECTIONS



1. 2x HDMI™ 2.0b (UWQHD@100Hz)
2. DisplayPort 1.4a (HBR3)
3. Headphone out
4. DC-in
5. Kensington lock