



SPECIFICATIONS

Panel Size	27"
Active Display Area (mm)	596.736 (H) x 335.664 (V)
Curvature	Flat
Panel Type	Rapid IPS
Panel Resolution	2560 x 1440 (WQHD)
Pixel Pitch (H x V)	0.2331 (H) x 0.2331 (V)
Aspect Ratio	16:9
Brightness (nits)	SDR: 300 cd/m ² HDR: 400 cd/m ² (Peak)
Contrast Ratio	1000:1
DCR	100000000:1
Signal Frequency	70.5~460KHz (H) / 48~320Hz (V)
ACTIVATED RANGE	48~320Hz
Refresh Rate	320Hz
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	VESA DisplayHDR 400
Video ports	1x DisplayPort 1.4a (HBR3) 2x HDMI™ 2.1 (WQHD@320Hz)
Audio ports	1x Headphone-out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	95% / 97% / 129% (CIE1976 Standard)
Surface Treatment	Anti-glare
Display Colors	1.07B, 10 bits (8 bits + FRC)
Power Type	Internal Power Board
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Pivot)	-90° ~ 90°
Adjustment (Height)	0~130 mm
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Dimension with Stand (W x D x H)	613.5 x 227.9 x 405 mm (24.1 x 8.9 x 15 inch)
Dimension without Stand (W x D x H)	613.5 x 62 x 362.5 mm (24.1 x 2.4 x 14.2 inch)
Weight (NW / GW)	6.7 kg (14.7 lbs) / 9.3 kg (20.5 lbs)

FEATURES



Rapid IPS

Make sure the intensity and purity of colors when gaming.



High Refresh Rate

Experience smooth gaming with a blazing fast 320Hz refresh rate that gives you the upper hand in fast moving games.



0.5ms (GtG, Min.) Response Time

Eliminate screen tearing and choppy frame rates with 0.5ms (GtG, Min.) Response Time.

VESA CERTIFIED



VESA DisplayHDR 400

VESA certified eye-catching details through precise contrast and shadow adjustment.




Console Mode

Optimized for seamless compatibility with gaming consoles like PS5 and Xbox Series X|S.

Carton Dimension (W X D X H)	820 x 148 x 460 mm (32.2 x 5.8 x 18.1 inch)
Accessories	1x DisplayPort Cable (1.4a), 1x Power Cord (C13), 1x Quick Guide, 4x Stand Screw
Note	HDMI™: 2560 x 1440 (Up to 320Hz) DisplayPort: 2560 x 1440 (Up to 320Hz) Support: HDMI™ CEC, PIP/PBP; Non Support: KVM

CONNECTIONS



1. 5-Way Navi Key
2. 2x HDMI™ 2.1 (WQHD@320Hz)
3. DisplayPort 1.4a
4. Headphone-out
5. AC-in
6. Kensington Lock