



Reliable power and a spacious display for a smart price

HP ProBook 4 G2a 16-inch Notebook combines trusted performance, business-grade security and a spacious display for seamless multitasking in a traditional PC. Designed for modern hybrid workflows and priced for scale, this device offers fast processing, lasting battery life and simplified manageability for IT teams and growing businesses.

Rapid speed. Big screen clarity. Practical price.

Easily manage diverse tasks with swift performance on a large screen with dependable power—highly secure and cost-optimized for growing businesses.

Highlight your presence on every team project

Make the best of the spotlight with an HDR camera and audio expertly tuned for immersive engagement—no matter where you work.

HP BIOS and Wolf Security

Fortify your most essential data with built-in, multi-layered protection from HP Wolf Security for Business.[5]

Featuring

HP recommends Windows 11 Pro for business

Work anywhere without compromising on performance with Windows 11 and HP collaboration, security, and connectivity technology. Summarize and rewrite content, get relevant content recommendations, and stay organized with Microsoft Copilot. [1]

Ready to meet the demands of your day

Get through your deadline-driven, multi-tasking day using the AMD Ryzen™ processor with a perfect combination of performance, power consumption, and value. [2]

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit data rate Wi-Fi 7. [3]

Browse confidently

Help protect your PC from websites and read only Microsoft Office and PDF attachments with embedded malware, ransomware, or viruses with hardware-enforced security from HP Sure Click. [4]

HP Sure Sense

Malware is evolving rapidly beyond traditional antivirus capabilities. Protect your PC against never-before-seen attacks with HP Sure Sense, which combines behavioral analysis with advanced AI techniques to provide exceptional protection. [6]

Specifications

Operating System Software	Windows 11 Pro ^[1]
Product Color Description (fixed)	Pike silver
Processor Family	AMD Ryzen™ 5 processor
Processor Name	AMD Ryzen™ 5 220 (up to 4.9 GHz max boost clock, 16 MB L3 cache, 6 cores, 12 threads) ^[6,7]
Standard Memory Description 01	16 GB DDR5-5600 MT/s (2 x 8 GB)
Memory Slots	2 SODIMM
Hard Drive Description (01)	256 GB PCIe® NVMe™ M.2 SSD
Graphics Card Segment 01	Integrated
GScardseg 01 Available Card 01	AMD Radeon™ 740M Graphics
Display Description (metric)	40.6 cm (16") diagonal, WUXGA (1920 x 1200), touch, IPS, anti-glare, 300 nits, 62.5% sRGB
Display Description	16" diagonal, WUXGA (1920 x 1200), touch, IPS, anti-glare, 300 nits, 62.5% sRGB ^[13,14,15,16,17,21]
Audio Features	Audio by Poly Studio, dual stereo speakers, dual microphones enhanced by AI noise reduction
Product Dimensions (metric)	35.94 x 25.1 x 1.1 cm (minimum front); 35.94 x 25.1 x 1.7 cm (minimum rear); 35.94 x 25.1 x 1.15 cm (maximum front); 35.94 x 25.1 x 1.75 cm (maximum rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
Product Dimensions (imperial)	14.15 x 9.88 x 0.43 in (minimum front); 14.15 x 9.88 x 0.67 in (minimum rear); 14.15 x 9.88 x 0.45 in (maximum front); 14.15 x 9.88 x 0.69 in (maximum rear) <i>(Front height measurement is near the front edge where the chassis bottom cover taper begins. Back height measurement is near the back edge where the chassis bottom cover taper ends.)</i>
Weight (metric)	Starting at 1.73 kg <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Weight (imperial)	Starting at 3.83 lb <i>(Weight will vary by configuration. Does not include power adapter.)</i>
Keyboard	Spill-resistant, backlit keyboard with numeric keypad
Pointing Device	Clickpad with multi-touch gesture support, taps enabled as default
Sensors	HP Sure Platform; Thermal sensor; HP Tamper Lock; Hall effect sensor ^[13,45]
Integrated Camera	5 MP IR AI camera
External I/O Ports	1 HDMI 2.1; 1 stereo headphone/microphone combo jack; 1 RJ-45; 1 nano security lock slot; 2 USB Type-A 5Gbps signaling rate (powered); 2 USB Type-C® 10Gbps signaling rate (USB Power Delivery, DisplayPort™ 1.4) <i>(HDMI cable sold separately.)</i>
Wireless Technologies	MediaTek Wi-Fi 7 MT7925 (2x2) and Bluetooth® 6.0 wireless card
Power Supply Required	HP 65 W USB Type-C® GaN power adapter ^[13,21]
Battery Type	HP Long Life 3-cell, 56 Wh Li-ion
Sustainability Specifications	At least 25% recycled metal; Product Carbon Footprint; HP paper-based packaging is from recycled or certified sources; At least 30% post-consumer recycled plastic; At least 30% ocean-bound plastic; Low halogen; Bulk packaging available; External power supply 90% efficiency
UPC Number	826581062172
Manufacturer Warranty	1-year warranty and 90 day software limited warranty options depending on country. HP Worldwide Limited Warranty for the battery is aligned with the warranty period of the HP Hardware Product. Refer to http://www.hp.com/support/batterywarranty/ for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc .

Top Recommended Displays, Accessories and Services

Sleeves

HP Protective 15-16-inch Laptop Sleeve	C40BPUT
--	---------

Backpacks

HP Everyday 16-inch Laptop Backpack	A08KLUT
-------------------------------------	---------

Topload Bags

HP Renew Business 17.3-inch Laptop Bag	3E2U6AA
--	---------

Messaging Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows 11 is automatically updated, which is always enabled. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>. Microsoft Copilot requires Windows 11. Some features require an NPU. Timing and availability will be dependent on Microsoft and varies by market and device. Requires Microsoft account to log in. Where Copilot is not available, the Copilot key will lead to the Bing search engine. See <http://aka.ms/WindowsAIFeatures>.

[2] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[3] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 7 (802.11BE) functionality requires compatible Windows 11 OS, compatible processor, and separately purchased Wi-Fi 7 router to support backwards compatibility with prior 802.11 specs. Available in countries where Wi-Fi 7 is supported. The specification for 802.11BE is a draft specification and is not final. If the final specification differs from the draft specification, it may affect the ability of the device to communicate with other 802.11BE devices. Wi-Fi® supporting gigabit data rate is achievable with Wi-Fi 7 (802.11BE) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[4] HP Sure Click requires Windows 10 and higher. See https://bit.ly/2PrLT6A_SureClick for complete details.

[5] HP Wolf Security for Business requires Windows 10 and higher, includes various HP security features and is available on HP Pro, Elite, Workstation, and RPOS products. See product details for included security features and OS requirements.

[6] HP Sure Sense is available on select HP PCs with Windows 10 Pro, Windows 10 Enterprise, Windows 11 Pro, or Windows 11 Enterprise OS.

Technical Specifications Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[7] Max Boost clock frequency performance varies depending on hardware, software and overall system configuration.

[13] Sold separately or as an optional feature.

[14] WUXGA (FHD+) content required to view WUXGA (FHD+) images.

[15] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[16] Actual brightness will be lower with touchscreen.

[17] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[21] Availability may vary by country.

[45] HP Tamper Lock can be Enabled/disabled by customers or IT administrator with administrator authority.

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

