

2U 16in Depth Universal Vented Rack Mount Shelf - 50lbs / 22kg

2U 22in Depth Solid / Vented Fixed Rack Mount Shelf - 50lbs / 22kg

CABSHELFV

CABSHELF22/CABSHELF22V



*actual product may vary from photos

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

Introduction	1
Packaging Contents	1
System Requirements.....	1
Installation	1
Specifications	3

Introduction

The CABSHELFV 2U 16in Depth Universal Vented Rack Mount Shelf lets you add a compact, 2U shelf to virtually any standard 19-inch server rack or cabinet with front mount options.

Our vented rack shelves improve air flow and help to lower temperatures in the rack. Constructed using SPCC commercial grade cold-rolled steel, this durable fixed rack shelf can hold up to 22kg (50lbs) of equipment - a perfect solution for storing small, non-rackmount equipment, tools, peripherals or accessories in your rack to keep them readily accessible.

Backed by a StarTech.com Lifetime warranty.

Packaging Contents

- 1x 2U Fixed Rack Shelf
- 4x M6 Cage Nuts
- 4x M6 Screws
- 1x Instruction Manual

System Requirements

- EIA-310C compliant 19in server rack/cabinet
- At least 2U of available space in rack/cabinet to mount shelf
- If using a rack/cabinet that does not use square mounting points along the posts, the appropriate mounting hardware for the rack will be required (consult documentation for the rack or contact the manufacturer)

Installation

1. Locate a suitable location in the rack/cabinet to mount the shelf. The shelf itself requires 2U of space within the rack/ cabinet.
2. If the rack uses square mounting holes, install the included cage nuts into the square mounting holes on the front posts of the rack.
3. Place the shelf into the rack and align the mounting points on the front brackets of the shelf with the mounting points on the rack (e.g. the cage nuts, if used).
4. Use the provided cabinet screws to secure the shelf to the rack. If not using the included cage nuts or M6 threaded rack posts, the appropriate mounting hardware for the rack should be used.
5. Make sure the screws are properly tightened and the shelf has no movement before attempting to place anything on the shelf. Be sure to observe the maximum weight capacity of the shelf.

Specifications

	CABSHELFV	CABSHELF22/CABSHELF22V
Description	2U 16in Depth Universal Fixed Server Rack Cabinet Shelf	2U 22in Depth Solid / Vented Rack Mount Shelf
Material	SPCC (1.6mm thick)	
Color	Black	
Max Weight Capacity	22kg / 50lbs	
Mounting Height	2U	
External Dimensions (WxDxH)	482.7mm x 406.4mm x 88.0mm	482.7mm x 558.8mm x 88.0mm
Net Weight	2600g	4100g / 3560g
Certifications	CE, RoHS	

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a lifetime warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.