

6U/8U/12U 22in Depth Hinged Open Frame Wall Mount Server Rack

RK619WALLOH / RK819WALLOH / RK1219WALLOH

- DE: Bedienungsanleitung - de.startech.com
- FR: Guide de l'utilisateur - fr.startech.com
- ES: Guía del usuario - es.startech.com
- IT: Guida per l'uso - it.startech.com
- NL: Gebruiksaanwijzing - nl.startech.com
- PT: Guia do usuário - pt.startech.com

Packaging Contents

- 1 x Hinged Wall Mount RackWall
- 1 x Bag of #10-32 UNF Panel Screws
- 1 x Bag of #10-32 UNF Cage Nuts

System Requirements

- If mounting to a wall or other surface: Appropriate mounting hardware for surface type

Installation

To mount the cabinet to a wall, there are 4 anchor points on the side rear panel of the cabinet. Please use the appropriate screws or bolts for mounting heavy equipment to the specific type of wall (i.e. concrete, drywall, etc.).

NOTE: Mounting points are 16" from center to center for mounting to standard wooden studs. Ensure the wall and mounting hardware will be able to support the weight of the cabinet and any equipment that will be mounted into it. Please be sure to observe proper safety



*RK1219WALLOH Shown

procedures and use the appropriate tools. To install rack mountable equipment into the cabinet, use the provided square cage nuts on the rack posts (install from rear of posts), then use the provided cabinet screws to secure the equipment to the cage nuts (from front of posts).

WARNING! To prevent bodily injury, please ensure that the rack is installed in a structurally sound environment with a level floor and that all hardware has been assembled securely, and checked for stability before loading equipment. When installing equipment into the rack, start from the bottom of the rack first and move upwards, keeping the heaviest equipment at the bottom to avoid a situation where the rack becomes top-heavy.

Specifications

	RK619WALLOH	RK819WALLOH	RK1219WALLOH
Description	6U 22in Depth Hinged Open Frame Wall Mount Server Rack	8U 22in Depth Hinged Open Frame Wall Mount Server Rack	12U 22in Depth Hinged Open Frame Wall Mount Server Rack
Internal Height	6U	8U	12U
Mounting Depth		559.0mm (22")	
Maximum Weight Capacity	49.8 kg (110 lbs)	63.4 kg (140 lbs)	63.4 kg (140 lbs)
Material		SPCC	
Color		Black	
Equipment Mounting Hole Type		Square	
External Dimensions (WxHxD)	604mm x 408mm x 555mm	604mm x 488mm x 555mm	604mm x 647mm x 555mm
Net Weight	13.94 kg	15.06 kg	17.48 kg
Standards		EIA RS310-D	
Certifications		CE, RoHS	

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a lifetime warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.