

Product Line
UB-RACK

Type
RM-UB-T3

Supported Models **UBIQUITI
UCK G2 PLUS
USG**

DIMENSIONS 1U
COLOR Metallic Dark Blue
PACKING DIMENSIONS 80 x 520 x 270 mm
3.14 x 20.47 x 10.63 in
PRODUCT DIMENSIONS 44 x 482 x 217 mm
(height x width x depth) 1.73 x 18.98 x 8.54 in



MOUNTING INSTRUCTIONS

1. Remove the four rubber feet from the USG.
2. Remove two bolts (situated on the back side of the appliance) from the bottom of the USG.
3. Place your USG on the rack, & fix it with the two original bolts.
4. Place the power supply on the rack and fix it with two zip ties.
5. Plug in the power cord and secure the cable with another zip tie on the rack (detail 1).
6. Tie the excess length of the power cord down with the fourth zip tie.
7. Place the Unifi Cloud Key Gen2+ on the rack and fix it with the provided bolts on both sides of the appliance.
8. Connect the cable from the Unifi Cloud Key Gen2+ to the connector.
9. Place your UB-Rack in your 19 inch rack.



Detail 1

Please ensure proper ventilation according to the network appliance manufacturer guidelines.

PACKAGE CONTENTS

Qty	Description
1	UB-Rack
2	Bolts M3x4mm
1	Allen Key
4	Zip ties
1	Cable - 0.25 meter



**Consider the environment,
recycle where applicable.**

Rackmount.IT rack mount kits are RoHS compliant, developed & manufactured in the Netherlands and made of first quality parts.

In case of problems please contact your reseller or sales@rackmount.it.

Revision 1 - 04-11-2021

EMEA Office
Nonneveld 27
4811 HN Breda
The Netherlands
T +31 76 200 37 40
E sales@rackmount.it
WWW.RACKMOUNT.IT

US Office
9201 Metric Blvd - Unit A
Austin - TX 78758
United States
T +1 512 521 03 33
E sales-us@rackmount.it

RACKMOUNT.IT