

尺寸: 55X80MM

User Manual

65W Triple Port Car Charger

Part #: A01111




CODi.

+1 800.263.4462

custsupport@codiworldwide.com


Product Specifications

Model	A01111
Description	85W Max Type-C Car Charger
Input	DC12-24V=7.5A
Type C1 Output	5V=3A (15W), 9V=3A (21W), 12V=3A (36W), 15V=3A (45W) 20V=3.25A (65W Max) PPS: 3.3-11V/5A (55W Max)
Type C2 Output	5V=3A (15W), 9V=2.22A (20W), 12V=1.67A (20W Max)
USB Output	5V=3A (15w), 9V=2A (18W), 12V=1.5A (18W)
USB+Type C2 Output	5V=3A (15W Max)
Size	1.8x1.2x3in (45x31x78mm)
Net weight	.08lb (35g)



1

Product Functionality Diagram



Note

If you use either the USB-A or USB-C 20W port individually, the smart chip will charge your device at the maximum wattage output of the port.

However, if you use both the USB-C2 and the USB-A port simultaneously, the charging output will share 15W between the two ports.

Warranty Information

CODi offers a non-transferable, 1 Year Limited Warranty, from date of purchase, to the original purchaser, who has properly registered the Product through www.codiworldwide.com.

CODi warrants that all products will be free from defects in workmanship and materials under normal use, for 12 months, unless otherwise specified in a Product Specification Sheet ("Limited Warranty").

2

3

4