

Input:
HDMI x4

Output:
HDMI x1


- Supports to switch 5 HDMI sources to 1 HDMI display
- Multifunctional on switching: intelligent or mechanical
- Supports highest video resolution up to 4kx2k@60Hz
- Supports Full 3D
- HDCP Pass through
- EDID bypass



User Manual

5 Port HDMI® Splitter - 4K 60Hz - supports HDR & (EDID)
Includes 5V 1A power adapter - Gray

Y10A267-A1

Congratulations

Thank you for purchasing this premium Rocstor product. For optimum performance and safety, please read these instructions carefully before connecting, operating or using this product. Please keep this manual for future reference.

Introduction

This is a premium Rocstor high-performance HDMI UHD Switcher. This HDMI UHD Switcher not only has the key-press-switching function, but also has intelligent function.

This HDMI UHD Switcher routes high definition video (in multiple resolutions up to 4kx2k@60Hz) and digital audio from any one of the several sources to display units. All inputs accommodate the connections of the high definition video sources simultaneously, compatible well for DMR-BZT9600, BDP-LX88, SONY FMP-X10-001, nVidia GTX970, GTX980 series, output sends the high definition audio/video signals to a high

Package Contents

Before attempting to use this unit, please check the packaging and make sure the following items are contained in the Packaging:

- Main unit x1
- User Manual x1
- Remote control
- 5V/1A Power Adapter

System Requirement

1. Connect the HDMI input source into the HDMI Switcher
 *Please refer to connection diagram section
2. Press the button to select the inputs
3. It is recommended to give a 5V DC power supply to the switch unit.
 Attention: Insert / Extract cable gently.

Specification
Input / Output Connector

Input	HDMI x5
Output	HDMI 1x
Maximum Single Link Range	Full 3D and 4kx2k@60Hz

Operating Frequency

Vertical Frequency Range	24/30/50/60Hz
Video Amplifier Bandwidth	6Gbps/600MHz

Resolutions(HDTV)

Interlaced(50&60Hz)	480i,576i,1080i
Progressive(50&60Hz)	480p,576p,720p,1080p, 4kx2k@30HZ, 4kx2k@60HZ,

Warranty

2 Year

Environmental

Operating Temperature	0°C to + 45°C - (32°F to + 113°F)
Operating Humidity	10% to 90 % RH (no condensation)
Storage Temperature	-10°C to + 70°C - (14°F to + 158°F)
Storage Humidity	10% to 90 % RH (no condensation)

Regulatory Approvals

Certifications	FCC, CE
----------------	---------

Mechanical

Size(L-W-H)	158x60x18.5mm - (6.2"x2.3"x0.7")
Weight(Net)	210.7g - (0.46Lbs)

Power Requirement

External Power Supply	5V/1A
Power Consumption	1.8W

Accessory

User Manual	English Version
-------------	-----------------



Support

Technical support is available to all the registered users of Rocstor products.

Technical Support / RMA
 Hours: 9:00 am - 5:00 pm PST
 Monday to Friday (except holidays)

Tell: +1 (818) 727-7000 (National and international)
 Fax: +1 (818) 875-0002
 Email: support@Rocstor.com

⚠ Safety Information:

WARNING: Please follow these safety instructions. Failure to do so may result damages or injury. It is normal that the Rocstor adapter becomes very warm during use.

Please note that:
 continuous contact with warm surfaces for extended time may cause discomfort or injury. In order to reduce the possibility of overheating or heat-related injuries, always allow needed ventilation around the Rocstor adapter and use care when handling it. Avoid instances where your skin is in extended contact with the hub when plugged into the host computer. It is not recommended to sleep with the adapter when plugged into a host computer. Avoid placing the hub adapter under a pillow, blanket, or your body when connected to a host computer. If you have a medical condition that affects your ability to detect heat against the body, extra care should be used. Never use the adapter in locations with water, such as a sink, bathtub, or shower stall. Never connect or disconnect the adapter with wet hands.



Warranty Information

Warranty Information
 This product is backed by a (2) two-year warranty. Rocstor warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. Rocstor does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability
 In no event shall the liability of Rocstorage, Inc. and Rocstor (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

©2021 Rocstroge, Inc. All rights reserved. Rocstor is registered trademark of Rocstorage, Inc. Apple®, the Apple logo, Mac®, MacBook®, MacBook Pro®, MacBook Air®, iPad®, iPad Air®, iPad mini®, iPad Air®, iPhone®, MacOS® are registered trademarks of Apple, Inc. Google® and Chromebook™ are registered trademarks of Google, LLC. Microsoft® is registered trademarks of Microsoft corporation. All other product names and logos mentioned herein may be trademarks of their respective companies. Thunderbolt is a trademark of Intel Corporation or its subsidiaries. USB Type-C® and USB-C® are registered trademark of USB Implementers Forum. Feature and specification are subject to change without notice. All trademarks and registered trademarks are the property of their respective. All rights reserved.

