

---

# USB Travel Docking Station

---

USB 3.1 Gen 2 Travel Docking Station with LAN

User Manual


# Introduction

The USB 3.1 Gen 2 Travel Docking Station with LAN provides a quick and easy connection to all the workspace peripherals you use every day. It features a single HDMI video port enabled by DP Alt Mode as well as x1 Giga LAN port (RJ-45), x1 USB-C and x1 USB-A 3.1 (Gen 2) ports. Simply plug in the USB Travel Docking Station into your PC or Laptop for instant access to your preferred 4K monitor, ethernet line, and other USB peripherals such as printers, scanners, keyboard, mouse, or external storage.

# Key Features

- Supports USB-A 3.1 Gen 2
- Supports USB-C 3.1
- Supports DP Alt Mode
- Supports Gigabit Ethernet
- Up to 4K resolutions/30Hz (when supported by host)

# Application Diagram



# Specifications

| USB 3.1 Gen 2 Travel Docking Station with LAN | Description                                      |  |
|---|--|--|
| Interfaces                                    | Upstream:  | SB-C integrated cable x1                               |
|   | Downstream:                                      | USB- Type A x1 (USB Gen 2)                             |
|   |  | USB Type c x1 (USB Gen 2 Data only)                    |
|   |  | HDMI x 1   |
|   |  | Gigabit Ethernet x1                                    |
| Interface Transfer Rates                      | USB 3.1 Gen 2:                                   | 10 Gbps  |
| Max. Video Resolutions                        | HDMI:  | 3840 x 2160 /30Hz (when supported by host and display) |
| USB-C Support                                 | Upstream:  | Data transfer  |
|   |  | DisplayPort Alt Mode                                   |
| OS Support                                    | Windows 10 and later, Mac OS X 10.10.2 and later |  |
| Power Supply                                  | Bus-Powered                                      |  |
| Environments                                  | Operating temperature: 0°C~60°C                  |  |
|   | Storage temperature: -20°C~60°C                  |  |
|   | Humidity: <90% RH                                |  |
| Weight  | 0.167kg  |  |
| Dimensions                                    | 61x60x17mm                                       |  |