


Intensifier® Series HD-TVI 1080p 2MP Dome Camera
Wall/Ceiling Mount, UTC, 2BNC out for TVI & CVBS, Dual voltage



200 New Highway, Amityville, NY 11701
 800-645-5516 / www.specotech.com

HT7250TM – 5~50mm motorized zoom focus lens, dark gray housing

DIMENSIONS



FEATURES


- Full HD resolution over coax (HD-TVI)
- Supports up to Full HD 1080p @ 30fps
- True WDR operation
- Superior low-light performance
- Amplify existing light with no distance limitation
- Presets: Outdoor, Low Light, Hallway, Lobby, Elevator, Indoor
- Built-in heater and anti-fog glass reduces condensation
- 3-axis for wall and ceiling mounting
- Chameleon Cover™: snaps on and can be painted to match any décor!*
- Full OSD operation through on-board control and UTC (up the coax)
- Additional 960H analog output
- Signal distance up to 1600 feet*
- Vandal / tamper resistant
- IP67 compliant, weather resistant
- 12VDC & 24VAC dual voltage operation
- 5 year warranty

SPECIFICATIONS

Image Sensor.....	1/3" Progressive Scan CMOS, 2MP
Minimum Illumination.....	0.001 lux (Sens-up X32)
Effective Pixels.....	1984 (H) x 1105 (V)
Total Pixels.....	2000 (H) x 1121 (V)
Scanning System.....	Progressive
S/N Ratio.....	More than 50dB
Output Resolution.....	1920x1080 @ 30fps
Video Output.....	1.0Vp-p / 75 Ohms
Electronic Shutter.....	Auto / Manual (1/30 – 1/30,000 sec.)
Day / Night.....	Auto / Color / BW / External
Test Monitor Output.....	CVBS (BNC out in Yellow)
Communication.....	UTC (up the coax)
Power.....	12VDC / 24VAC
Power Consumption.....	600mA max. (DC), 450mA max. (AC)
Operating Temperature.....	-4° F – 122° F
Unit Dimensions.....	3.97" (H) x 5.23" (Dia.)
Unit Weight.....	3.3 lbs
Certifications.....	FCC, RoHS
Signal Distance.....	Up to 1600 feet (depending on coax quality)*

OSD MENU TREE

- PRESET MODE
 - OUTDOOR • LOW LIGHT • HALLWAY • LOBBY • ELEVATOR • INDOOR
- MAIN SETUP
 - IRIS
 - 2-MOTOR
 - EXPOSURE
 - BRIGHTNESS • SHUTTER • INTENSIFY • AGC
 - BACKLIGHT
 - WDR • BLC • HLC
 - DAY / NIGHT
 - COLOR • B/W • EXTERN • AUTO
 - COLOR
 - AWB • COLOR GAIN
 - SPECO DNR
 - LOW • MIDDLE • HIGH
 - IMAGE
 - SHARPNESS • GAMMA • MIRROR • FLIP • D-ZOOM
 - ACE • DEFOG • SHADING • PRIVACY
 - MOTION
 - SYSTEM
 - OUTPUT • FRAME RATE • FREQ. • COM. • IMAGE RANGE
 - COLOR SPACE • COLOR BAR • LANGUAGE • CAM TITLE • RESET
 - EXIT



Intensifier T® Series HD-TVI 1080p 2MP Dome Camera

Wall/Ceiling Mount, UTC, 2BNC out for TVI & CVBS, Dual voltage



200 New Highway, Amityville, NY 11701
800-645-5516 / www.specotech.com

HT7250TM – 5~50mm motorized zoom focus lens, dark gray housing

OSD MENU Details

IRIS : 'ALC' as a default value

2-MOTOR : AF Mode, Scanning, OnepushAF, Sync TDN, Initial

EXPOSURE : adjusts exposure settings.

- BRIGHTNESS : Adjusts image brightness. (0~20)
- SHUTTER : Outdoor / Indoor / Deblur
- INTENSIFY : Sets the desired multiple of the digital exposure length.
- AGC(Auto Gain Control): Adjusts the AGC level. (0~10)

BACKLIGHT : Adjusts backlight options.

- WDR : WDR illuminates darker areas of an image while retaining the same light level for brighter areas to even out the overall brightness of images with high contrast between bright and dark area
 - Adjusts the WDR Weight (LOW/MIDDLE/HIGH)
 - * CVBS out cannot adjust this function.
- BLC : Produces a clearer image of an object darkened by strong backlighting.
 - H-POS : Adjusts the horizontal position(0~20)
 - V-POS : Adjusts the Vertical position(0~20)
 - H-SIZE : Adjusts the horizontal block size (0~20)
 - V-SIZE : Adjusts the vertical block size (0~20)
- HLC : Uses to contain extremely bright areas such as from car headlight, the light can be masked out much of the on-screen details.

DAY / NIGHT : Adjust Day / Night options.

- COLOR : Always Color mode, Default value for these cameras
- B/W : Always B/W mode.
 - ANTI-SAT. : Adjusts the Anti Saturation level (0~20)
- EXT : please do not use this mode for these cameras
- AUTO : Day / Night is switching automatically by AGC level.
 - ANTI-SAT. : Adjusts the Anti Saturation level (0~20)
 - AGC THRES : Adjusts AGC THRES (0~20)
 - AGC MARGIN : Adjusts AGC margin (0~20)
 - DELAY : Adjusts the changing delay time (LOW/MIDDLE/HIGH)

COLOR : Adjusts white balancing options.

- AWB : it goes to optimized color level automatically.
- COLOR GAIN : Sets the desired Color Gain value (0~20)

SPECO DNR : Uses to reduce the background noise in a low luminance environment with 2D + 3D filtering system.

IMAGE : Adjusts various image options.

- SHARPNESS: Adjusts sharpness level. Increasing this value, the picture outline becomes stronger and clear. (0~10)
- GAMMA : Sets the desired Gamma value. (0.45 ~ 0.75)
- MIRROR : Change the video direction horizontally.
- FLIP: Change the video direction perpendicularly.
- ACE (D-WDR) : Uses a digital wide dynamic range to balance dark and over saturated areas within the image.
- DEFOG : Activated this mode when the video or the weather is foggy.
- PRIVACY : Used to hide regions of the image.

MOTION : Adjust motion detection settings.

- DET WINDOW
- DET TONE
- MDRECT FILL
- SENSITIVITY : Sets the desired of "Motion" (0~20)
- MOTION OSD
- TEXT ALARM
- SIGNAL OUT

SYSTEM : Adjusts various camera system options.

- OUTPUT
- MAIN OUTPUT ANALOG OUT0
 - ANALOG OUT0 TVI
 - Y GAIN
 - CB GAIN
 - CR GAIN
 - FRAME RATE: 1080P 30 / 720P 60
 - FREQ 60Hz
 - COM.
 - IMAGE RANGE
 - COLOR SPACE
 - COLOR BAR : Manufacturer's option
 - LANGUAGE : Sets the desired OSD language
 - CAM TITLE
 - RESET: Press with long to reset all settings to factory defaults.



LIMITED WARRANTY - VIDEO PRODUCTS

THIS WARRANTY IS VALID ONLY ON PRODUCTS PURCHASED AND USED IN THE UNITED STATES OF AMERICA AND CANADA. THIS WARRANTY APPLIES ONLY TO THE ORIGINAL USER.

SUBJECT TO CONDITIONS AND EXCLUSIONS FOUND BELOW, THIS PRODUCT IS WARRANTED AGAINST MANUFACTURING DEFECTS IN MATERIAL AND WORKMANSHIP FOR THE FOLLOWING PERIOD FOR PARTS AND LABOR:

SPECO TECHNOLOGIES CAMERAS	5 YEARS	DVRS	5 YEARS
SPECO TECHNOLOGIES IP CAMERAS.....	5 YEARS	NVRS	5 YEARS
SPECO PTZ	1 YEAR	BALANCE OF	
SPECO TECHNOLOGIES MONITORS.....	1 YEAR	SPECO TECHNOLOGIES LINE	1 YEAR
IR LEADS	90 DAYS		

SPECO TECHNOLOGIES WILL REPAIR OR REPLACE (AT OUR DISCRETION) ANY PARTS FOUND TO BE DEFECTIVE FOR THE WARRANTY PERIOD SPECIFIED. WE WILL PROVIDE A REPLACEMENT FOR ANY DEFECTIVE PART.

CONDITIONS

- YOU MUST OBTAIN A RETURN AUTHORIZATION (RA) NUMBER FOR ANY MERCHANDISE BEING RETURNED TO SPECO TECHNOLOGIES, WHETHER FOR RETURN/EXCHANGE OR REPAIR, WHETHER IN OR OUT OF WARRANTY.
- THIS WARRANTY WILL BE HONORED ONLY UPON PRESENTATION OF THE ORIGINAL DATED BILL OF SALE OR SALES SLIP.
- TRANSPORTATION OF THE PRODUCT TO OUR SERVICE DEPARTMENT IS THE RESPONSIBILITY OF THE USER. REPAIRED OR REPLACED PRODUCT WILL BE RETURNED PREPAID DURING THE WARRANTY PERIOD.
- SPECO TECHNOLOGIES DOES NOT AUTHORIZE ANY INTERNET OR MAIL ORDER PRODUCT SALES. IF A SPECO TECHNOLOGIES PRODUCT IS PURCHASED FROM AN UNAUTHORIZED DISTRIBUTOR OR OTHER SOURCE, INCLUDING RETAILERS, MAIL ORDER SELLERS AND ONLINE SELLERS, IT WILL NOT BE HONORED OR SERVICED UNDER THE EXISTING SPECO TECHNOLOGIES WARRANTY POLICY. ANY SPECO TECHNOLOGIES PRODUCT PURCHASED FROM THESE ONLINE MERCHANTS WILL VOID THE APPLICABLE WARRANTY AND IS INELIGIBLE FOR TECHNICAL SUPPORT. IF YOU HAVE QUESTIONS ABOUT A RESELLER, PLEASE CONTACT SPECO TECHNOLOGIES AT 1-800-645-5516 FOR A LIST OF UNAUTHORIZED DEALERS, VISIT: www.specotech.com/unauthorized.

EXCLUSIONS

- THIS WARRANTY SHALL NOT COVER ADJUSTMENT OF CUSTOMER OPERATED CONTROLS AS EXPLAINED IN THE APPROPRIATE MODEL'S INSTRUCTION MANUAL OR PRODUCTS WHICH HAVE BEEN ALTERED, ABUSED, OR HAVE MISSING OR ALTERED SERIAL NUMBERS.
 - THIS WARRANTY SHALL NOT APPLY TO UNCRATING, SETUP, INSTALLATION, OR THE REMOVAL AND REINSTALLATION OF PRODUCTS AFTER REPAIR.
 - THIS WARRANTY SHALL NOT APPLY TO REPAIRS OR REPLACEMENTS NECESSITATED BY ANY CAUSE BEYOND THE RESULT OF MANUFACTURE INCLUDING, BUT NOT LIMITED TO, ANY MALFUNCTION, DEFECTS OR FAILURE CAUSED BY OR RESULTING FROM UNAUTHORIZED SERVICE OR PARTS, IMPROPER MAINTENANCE, MODIFICATION OR REPAIR BY THE USER, ABUSE, MISUSE, NEGLIGENCE, ACCIDENT, FIRE, FLOOD, OR OTHER ACTS OF NATURE, INCORRECT LINE VOLTAGE, DAMAGE OR IMAGE BURNS TO TELEVISION PICTURE TUBES CAUSED BY OR ATTRIBUTABLE TO THE USE OF ANY ACCESSORY, ELECTRONICS GAME OR DEVICE, OR DAMAGE CAUSED TO IMAGE PICKUP DEVICES BY EXCESSIVE LIGHT.
- THE FOREGOING IS IN LIEU OF ALL OTHER EXPRESSED WARRANTIES AND WE DO NOT AUTHORIZE ANY PARTY TO ASSUME FOR US ANY OTHER OBLIGATION OR LIABILITY. IN NO EVENT SHALL WE BE LIABLE FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING FROM THE USE OF THIS PRODUCT, OR FOR ANY DELAY IN THE USE OF THIS PRODUCT DUE TO CAUSES BEYOND OUR CONTROL. SOME STATES DO NOT ALLOW LIMITATIONS OF HOW LONG AN IMPLIED WARRANTY LASTS AND DO NOT ALLOW THE EXCLUSION OR LIMITATION OF CONSEQUENTIAL DAMAGES. THE ABOVE LIMITATIONS ON IMPLIED WARRANTY AND CONSEQUENTIAL DAMAGES MAY NOT APPLY TO YOU. THIS WARRANTY GIVES YOU SPECIFIC LEGAL RIGHTS. YOU MAY HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.
- NOTE: FOR YOUR PROTECTION IN THE EVENT OF THEFT OR LOSS OF THIS PRODUCT, PLEASE FILL IN THE INFORMATION REQUESTED BELOW AND RETAIN WITH YOUR SALES RECEIPT.**

MODEL NO.: _____ SERIAL NO.: _____
(LOCATED ON BACK OR BOTTOM OF UNIT)
DATE OF PURCHASE: _____
WHERE PURCHASED: _____ PURCHASE PRICE: _____

Speco Technologies 200 New Highway Amityville, NY 11701 www.specotech.com	FOR MORE INFORMATION REGARDING SERVICE OR RETURN, CALL US TOLL FREE: 1-800-645-5516 IN METRO NY: 631-957-8700
---	--

ALWAYS USE DISCRETION WHEN INSTALLING VIDEO AND/OR AUDIO SURVEILLANCE EQUIPMENT ESPECIALLY WHEN THERE IS AN EXPECTATION OF PRIVACY. INQUIRE REGARDING FEDERAL, STATE AND/OR LOCAL REGULATIONS APPLICABLE TO THE LAWFUL INSTALLATION OF VIDEO AND/OR AUDIO RECORDING OR SURVEILLANCE EQUIPMENT. PARTY CONSENT MAY BE REQUIRED.

Speco Technologies is constantly developing product improvements.
We reserve the right to modify product design and specifications without notice and without incurring any obligation. Rev. 220324