

SKU Sheet

SKU Sheet: Elgato Wave XLR MK.2



Core Product Info

Full Name: Elgato Wave XLR MK.2
Embargo Date: March 3rd, 2026 – 6AM PDT / 2PM BST / 3PM CEST
MSRPs:

- USD: 169.99
- CAD: 229.99
- EUR: 169.99
- GBP: 159.99
- SEK: 1,990
- PLN: 849
- AUD: 279
- JPY: 28,980

Listing Title: Elgato Wave XLR MK.2 – USB Audio Interface and DSP Mixer for XLR Microphones, 80dB Gain, Onboard Effects, LED Feedback, Touch Mute, Works with Stream Deck, PC & Mac
Marketing Assets Link: https://corsair.mediavalet.com/portals/Elgato_Wave_XLR_MK_2_PLK

Unique Selling Points (Style Two – Hook + Description)

1. **Elite Soundstage:** 80dB gain powers any XLR mic.
2. **Powerful Amp:** Loud, clear headphone output.
3. **Onboard Effects:** Voice Tune, Compressor, EQ, Expander, Low Cut
4. **Wave FX Processor:** Runs DSP effects and VST Inserts in one signal chain.
5. **Ultra-Low Latency:** Hear what your audience hears.
6. **Auto Gain Wizard:** Effortless mic gain setup.
7. **Tactile Control:** Touch to mute, adjust levels on the fly.
8. **LED Feedback:** See levels and status at a glance.
9. **Modular Ecosystem:** Integrates with Stream Deck.
10. **Wave Link Software:** Route audio, chain effects, and mix input sources.

Sell Copy

25 Words:
Wave XLR gives your mic superpowers. 80dB gain, onboard effects, touch to mute, and Stream Deck control—all with ultra-low-latency monitoring that keeps you in sync.

50 Words:

Wave XLR is your all-in-one mic interface and mixer. Power any XLR mic with 80dB gain, shape your sound with onboard DSP effects, and control everything with a touch. Enjoy loud, unbelievably responsive monitoring, customizable LED feedback, and seamless Stream Deck integration. Studio sound and control, right on your desk.

100 Words:

Wave XLR brings pro audio to your desktop. Plug in any XLR mic and get up to 80dB of clean gain—no booster needed. Set gain automatically and mute with a touch. Loud, clear headphone output keeps you dialed into your mix while customizable LED feedback shows your levels at a glance. At the core, Wave FX Processor runs Clipguard 2.0, DSP effects, and VST inserts to keep your signal pristine. Everything flows through one unified signal chain for ultra-low latency monitoring, while Wave Link software lets you route and mix like never before.

SEO Meta Description

Wave XLR is a USB audio interface and DSP mixer for XLR microphones. 80dB gain, onboard effects, touch to mute, LED feedback, and Stream Deck integration for creators and pros.

SEO Terms

USB audio interface, XLR mic preamp, DSP mixer, Stream Deck compatible, Touch mute, RGB audio interface, Ultra low latency monitoring, Onboard effects, Creator audio gear, [PLACEHOLDER]

Technical Specifications

- Resolution: 24bit
- Sample rate: 48kHz
- Frequency response (XLR input): 20Hz - 20kHz
- Frequency response (Headphones, 32 Ohm): 20Hz - 20kHz
- Dynamic range XLR input: 135 dB
- Equivalent Input Noise (EIN), A-weighted: -130 dB
- Maximum input level: 6 dBV
- Connectors: Microphone (XLR), Headphone (3.5 mm Jack, Stereo), Host I/O (USB-C)
- Power Consumption: 900 mA max

System Requirements

- Windows 11 (64-bit) or newer
- macOS Sonoma 14.2 or newer
- USB-C Port

Product Dimensions

- mm (D × W × H): 93 x 118 x 73 mm
- in (D × W × H): 3.66 x 4.65 x 2.87 in
- Weight: 320 g / 0.71 lbs

In the Box

- Wave XLR MK.2
- USB-C to C cable (150 cm | 59 in)
- Quick Start Guide

Product Data

Dimensions (Depth x Width x Height):

- Metric: 93 x 118 x 73 mm
- Imperial: 3.66 x 4.65 x 2.87 in

Weight:

- Metric: 320 g
- Imperial: 0.71 lbs

Packaging Data

Dimensions (Depth x Width x Height):

- Metric: 190 x 155 x 95 mm
- Imperial: 7,48 x 6,10 x 3,74 in.

Weight:

- Metric: 725 g
- Imperial: 1,60 lbs

Master Pack Data

Dimensions (Depth x Width x Height):

- Metric: 409 x 336 x 430 mm
- Imperial: 16,10 x 13,23 x 16,93 in.

Weight:

- Net: 11,60 kg / 25,57 lbs
- Gross: 13,00 kg / 28,66 lbs

Shipping Data

Master Pack Quantity: 16

Pallet Quantity: 256

Warranty: 2 Years

Tariff Code: 8518.40.2000

Country of Origin: Vietnam

SKU Number: 10MAN9901

UPC Code: 840440497967

EAN Code: 0840440497967

GTIN: 10840440497964