

# HPE ProLiant DL360 Gen10 server

ProLiant DL300 Servers



---

## What's new

- Support for additional second generation Intel® Xeon® Scalable processors with improved price/performance.
- Networking Choice (NC) server models provide greater flexibility in the primary networking selection.
- Enhanced iLO 5 security features such as Server Configuration Lock, iLO Security Dashboard and Workload Performance Advisor.
- HPE InfoSight provides a cloud-based analytics tool that predicts and prevents problems before your business is impacted.

## Overview

Does your data center need a secure, performance driven dense server that you can confidently deploy for virtualization, database, or high-performance computing?

The HPE ProLiant DL360 Gen10 server delivers security, agility and flexibility without compromise. It supports the Intel® Xeon® Scalable processor with up to a 60% performance gain [1] and 27% increase in cores [2], along with 2933 MT/s HPE DDR4 SmartMemory supporting up to 3.0 TB [2] with an increase in performance of up to 82% [3]. With the added performance that Intel® Optane™ persistent memory 100 series for HPE [6], HPE NVDIMMs [7] and 10 NVMe bring, the HPE ProLiant DL360 Gen10 means business. Deploy, update, monitor and maintain with ease by automating essential server life cycle management

- Intel® Optane™ persistent memory 100 series for HPE offers the flexibility to deploy as dense memory or fast storage and enables per-socket memory capacity of up to 3.0 TB. [5]
- HPE 800 Watt Flex Slot Titanium hot-plug power supply available for EMEA

tasks with HPE OneView and HPE Integrated Lights Out 5 (iLO 5). Deploy this 2P secure platform for diverse workloads in space constrained environments.

## Features

### Industry-leading Performance with Versatile Compute

HPE ProLiant DL360 Gen10 server supports industry-standard technology leveraging the Intel Xeon Scalable processor with up to 28 cores, 12G SAS and 3.0 TB of 2933 MT/s HPE DDR4 SmartMemory.

Supporting the second generation Intel® Xeon® Scalable processor family with up to a 11% per-core performance gain [4] over first generation and with memory speeds up to 2933 MT/s.

Intel® Optane™ persistent memory 100 series for HPE works with DRAM to provide fast, high capacity, cost effective memory and storage to transform big data workloads and analytics by enabling data to be stored, moved, and processed quickly. [6]

Achieve greater capacity with flexible drive configurations with up to 10 SFF and four LFF drives along with an option to support up to 10 NVMe PCIe SSDs delivering enhanced performance, capacity, and reliability to meet various customer segments and workload requirements at the right economics.

With support for up to 12 NVDIMMs per chassis and 2X capacity of first-generation HPE NVDIMMs, HPE ProLiant DL360 Gen10 server delivers up to 192 GB per system. [7]

### Innovative Design for Flexibility and Choice

The premium 10 SFF NVMe chassis backplane provides the ability to mix and match SAS/SATA and NVMe within the same chassis along with 8 + 2 SFF and 4 LFF chassis that supports new uFF and M.2 storage options.

Embedded 4 x 1GbE (select models) or HPE FlexibleLOM and PCIe standup 1GbE, 10GbE, 25GbE, or 100GbE adapters provides flexibility of networking bandwidth and fabric so you can adapt and grow to changing business needs.

Unmatched expandability is packed in a dense 1U rack design with up to three PCIe 3.0 slots.

### Security Innovations

HPE iLO 5 enables the world's most secure industry standard servers with HPE silicon root of trust technology to protect your servers from attacks, detect potential intrusions and recover your essential server firmware securely.

New features include Server Configuration Lock that ensures secure transit and locks server hardware configuration, iLO Security Dashboard helps detect and address possible security vulnerabilities and Workload Performance Advisor provides server tuning recommendations for better server performance.

With Runtime Firmware Verification the server firmware is checked every 24 hours verifying validity and credibility of essential system firmware. Secure Recovery allows server firmware to rollback to the to last known good state or factory settings after detection of compromised code.

Additional security options are available with Trusted Platform Module (TPM) to prevent unauthorized access to server and securely stores artifacts used to authenticate the server platforms while the Intrusion Detection Kit logs and alerts when the server hood is removed.



### **Industry-Leading Serviceability and Deployment**

HPE ProLiant DL360 Gen10 server comes with a complete set of services offered by HPE Pointnext, delivering confidence, reducing risk, and helping customers realize agility and stability.

Services from HPE Pointnext simplifies the stages of the IT journey. Advisory and Transformation Services professionals understand customer challenges and design an enhanced solution. Professional Services enable rapid deployment of solutions and Operational Services provide ongoing support.

Services provided under Operational Services include - HPE Flexible Capacity, HPE Datacenter Care, HPE Infrastructure Automation, HPE Campus Care, HPE Proactive Services and multi-vendor coverage.

HPE IT investment solutions help you transform to a digital business with IT economics that align to your business goals.



## Technical specifications

## HPE ProLiant DL360 Gen10 server

<b>Processor Name</b>	Intel
<b>Processor family</b>	Intel® Xeon® Scalable 8100/8200 series - Intel® Xeon® Scalable 3100/3200 series
<b>Number of processors</b>	2, maximum depending on model
<b>Processor core available</b>	4 to 28 core, depending on model
<b>Processor cache</b>	8.25 - 38.50 MB L3, depending on processor
<b>Processor speed</b>	3.9 GHz, maximum depending on processor
<b>Expansion slots</b>	3, for detailed descriptions refer to the QuickSpecs
<b>Maximum memory</b>	3.0 TB with 128 GB DDR4 6.0 TB with HPE 512GB 2666 Persistent Memory Kit
<b>Memory, standard</b>	3.0 TB (24 X 128 GB) LRDIMM 6.0 TB (12 X 512 GB) HPE Persistent Memory
<b>Memory slots</b>	24 DIMM slots
<b>Memory type</b>	HPE DDR4 SmartMemory and Intel® Optane™ persistent memory 100 series for HPE, depending on model
<b>System fan features</b>	Hot-plug redundant standard
<b>Network controller</b>	Embedded 4 X 1GbE Ethernet Adapter (select models) or HPE FlexibleLOM and optional PCIe stand-up cards, depending on model
<b>Storage controller</b>	HPE Smart Array S100i and/or HPE Essential or Performance RAID controllers, depending on model
<b>Product Dimensions (metric)</b>	SFF Chassis: 4.29 x 43.46 x 70.7 cm, LFF Chassis: 4.29 x 43.46 x 74.98 cm
<b>Weight</b>	13.04 kg minimum, 16.78 kg maximum
<b>Infrastructure management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download) Optional- HPE iLO Advanced, and HPE OneView Advanced (require licenses)
<b>Warranty</b>	3/3/3 - Server Warranty includes three years of parts, three years of labor, three years of onsite support coverage. Additional information regarding worldwide limited warranty and technical support is available at: <a href="http://h20564.www2.hp.com/hpsc/wc/public/home">http://h20564.www2.hp.com/hpsc/wc/public/home</a> . Additional HPE support and service coverage for your product can be purchased locally. For information on availability of service upgrades and the cost for these service upgrades, refer to the HPE website at <a href="http://www.hp.com/support">http://www.hp.com/support</a>
<b>Drive supported</b>	4 LFF SAS/SATA, 8 SFF SAS/SATA + 2 NVMe, 10 SFF SAS/SATA, 10 SFF NVMe, 1 SFF or 1 Dual UFF rear drive optional depending on model
<b>Processor Type</b>	Intel
<b>Processor number</b>	1 or 2
<b>Security</b>	Optional locking Bezel Kit, Intrusion Detection Kit, and HPE TPM 2.0
<b>Form factor</b>	1U
<b>NVDIMM capacity</b>	16 GB
<b>NVDIMM rank</b>	Single rank

---

**NVDIMM type**HPE NVDIMM-N \*Only available on 1st Generation Intel® Xeon® Scalable Processors

---

[1] HPE measurements: Up to 60% performance increase of Intel Xeon Platinum vs. previous generation E5-2600 v4 average gains of STREAM, LINPACK, SPEC CPU 2006 & SPEC CPU2017 metrics on HPE servers comparing 2-socket Intel Xeon Platinum 8280 to E5-2699 v4 family processors. Any difference in system hardware or software design or configuration may affect actual performance. April 2019.

[2] Up to 27% core increase of Intel Xeon Platinum versus previous generation comparing 2-socket Intel Xeon Platinum 8280 (28 cores) to E5-2699 v4 (22 cores). Calculation  $28 \text{ cores} / 22 \text{ cores} = 1.27 = 27\%$ . April 2019.

[3] Percentage compare Gen10 vs Gen9: Gen10 = 12 Channels x 2933 data rate x 8 bytes = 281 GB/sec. Gen 9 = 8 channels x 2400 x 8 bytes = 154 GB/Sec.  $281/154 = 1.82$  or Gen10 is 82% greater bandwidth. Any difference in system hardware or software design or configuration may affect actual performance. April 2019.

[4] HPE measurements: Up to 11% performance increase of Intel Xeon Platinum vs. previous generation average gains of STREAM, LINPACK, & SPEC CPU2017 metrics on HPE servers comparing 2-socket Intel Xeon Platinum 8280 to Intel Xeon Platinum 8180 family processors. Any difference in system hardware or software design or configuration may affect actual performance. April 2019.

[5] 3.0 TB per socket with HPE 512GB 2666 Persistent Memory Kit

[6] Supported by the 2nd generation Intel Xeon Scalable Processors

[7] Supported by the 1st generation Intel Xeon Scalable Processors



For additional technical information, available models and options, please reference the [QuickSpecs](#)

## HPE Pointnext Services

[HPE Pointnext Services](#) brings together technology and expertise to help you drive your business forward and prepare for whatever is next.

### Operational Services from HPE Pointnext Services

[HPE Pointnext Tech Care](#) provides fast access to product-specific experts, an AI-driven digital experience, and general technical guidance to help enable constant innovation. We have reimagined IT support from the ground up to deliver faster answers and greater value. By continuously searching for better ways to do things—as opposed to just fixing things that break—HPE Pointnext Tech Care helps you focus on achieving your business goals.

[HPE Pointnext Complete Care](#) is a modular, edge-to-cloud IT environment service that provides a holistic approach to optimizing your entire IT environment, and achieving agreed upon IT outcomes and business goals through a personalized and customer-centric experience. All delivered by an assigned team of HPE Pointnext Services experts.

**HPE Integration and Performance Services** help you customize your experience at any stage of your product lifecycle with a menu of services based on individual needs, workloads, and technologies.

- Advise, design, and transform
- Deploy
- Integrate and migrate
- Operate and improve
- Financial Services
- GreenLake Management Services
- Retire and sanitize
- IT Training and personal development

### Other related services

[HPE Education Services](#) delivers a comprehensive range of services to support your people as they expand their skills required for a digital transformation. Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and support options.

**Defective Media Retention** is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.



## HPE GreenLake

[HPE GreenLake](#) is HPE's market-leading IT as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model. HPE GreenLake delivers public cloud services and infrastructure for workloads on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

[Explore HPE GreenLake](#)

Make the right purchase decision.  
Contact our presales specialists.



© Copyright 2023 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware. Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Intel Xeon and Intel are trademarks of Intel Corporation in the U.S. and other countries. ClearOS is either registered trademark or trademark of ClearCenter Corporation in the United States and/or other countries. All other third-party trademark(s) is/are property of their respective owner(s).

Image may differ from the actual product  
[PSN1010007891USEN](#), February, 2023.