

Overview

HPE USB Keyboard/Mouse Kit

1 USB Keyboard and 1 USB optical Mouse per option kit (one price, one SKU part number for the bundle) with HPE Black color and BFR-PVC, offer by OD1 for BTO/CTO configurations - FIO kits and standalone options. Ideal environment is a low cost basic USB keyboard and mouse with long product life, out-of-the-box solution for ProLiant Servers and Integrity Rack Servers.



Models

HPE USB US Keyboard/Mouse Kit	631341-B21
HPE USB UK Keyboard/Mouse Kit	631344-B21
HPE USB FR Keyboard/Mouse Kit	631346-B21
HPE USB ES Keyboard/Mouse Kit	631348-B21
HPE USB DE Keyboard/Mouse Kit	631358-B21
HPE USB JP Keyboard/Mouse Kit	631360-B21
HPE USB IT Keyboard/Mouse Kit	631362-B21
HPE USB CN Keyboard/Mouse Kit	631364-B21
HPE USB AE Keyboard/Mouse Kit	638212-B21
HPE USB RU Keyboard/Mouse Kit	638214-B21
HPE USB IN Keyboard/Mouse Kit	672097-D63
HPE USB AP/INTL Keyboard/Mouse Kit	672097-373
HPE USB INTL Keyboard/Mouse Kit	672097-B33
HPE USB PT Keyboard/Mouse Kit	672097-133
HPE USB TR Keyboard/Mouse Kit	672097-143
HPE USB CZ Keyboard/Mouse Kit	672097-223

Overview

HPE USB FI Keyboard/Mouse Kit	672097-353
HPE USB SE Keyboard/Mouse Kit	672097-103
HPE USB CH Keyboard/Mouse Kit	672097-113
HPE USB KR Keyboard/Mouse Kit	672097-KD3

What's New

- Now available in configurations for twenty languages.
-

Compatibility

US Keyboard/Mouse Kit

ProLiant BL (blades system):

- HPE ProLiant BL280c G6
- HPE ProLiant BL420c Gen8
- HPE ProLiant BL460c G7
- HPE ProLiant BL460c Gen8
- HPE ProLiant BL460c Gen9
- HPE ProLiant BL465c G7
- HPE ProLiant BL490c G7
- HPE ProLiant BL620c G7
- HPE ProLiant BL660c G7
- HPE ProLiant BL660c G8
- HPE ProLiant BL660c G9
- HPE ProLiant BL680c G7
- HPE ProLiant BL685c G7
- BCS BLc3000 Enclosure
- BCS BLc7000 Enclosure

ProLiant DL (rack-optimized):

- HPE ProLiant DL120 G7
- HPE ProLiant DL120 Gen9
- HPE ProLiant DL160 G6
- HPE ProLiant DL160 Gen8
- HPE ProLiant DL160 Gen9
- HPE ProLiant DL165 G7
- HPE ProLiant DL170e G6
- HPE ProLiant DL180 G6
- HPE ProLiant DL180 Gen9
- HPE ProLiant DL20 Gen9
- HPE ProLiant DL320 G6
- HPE ProLiant DL320e Gen8
- HPE ProLiant DL320e Gen8 v2
- HPE ProLiant DL360 G7
- HPE ProLiant DL360e Gen8
- HPE ProLiant DL360p Gen8
- HPE ProLiant DL360 Gen9
- HPE ProLiant DL370 G6
- HPE ProLiant DL380 G7



Overview

- HPE ProLiant DL380e Gen8
- HPE ProLiant DL380p Gen8
- HPE ProLiant DL380 Gen9
- HPE ProLiant DL385 G7
- HPE ProLiant DL385p Gen8
- HPE ProLiant DL560 Gen8
- HPE ProLiant DL560 Gen9
- HPE ProLiant DL580 G7
- HPE ProLiant DL580 Gen8
- HPE ProLiant DL580 Gen9
- HPE ProLiant DL585 G7
- HPE ProLiant DL60 Gen9
- HPE ProLiant DL80 Gen9

ProLiant ML (expansion-optimized):

- HPE ProLiant ML10
- HPE ProLiant ML10 Gen9
- HPE ProLiant ML10v2
- HPE ProLiant ML110 G7
- HPE ProLiant ML110 Gen9
- HPE ProLiant ML150 G6
- HPE ProLiant ML150 Gen9
- HPE ProLiant ML30 Gen9
- HPE ProLiant ML310e Gen8
- HPE ProLiant ML310e Gen8 v2
- HPE ProLiant ML350 G6
- HPE ProLiant ML350e Gen8
- HPE ProLiant ML350e Gen8 v2
- HPE ProLiant ML350p Gen8
- HPE ProLiant ML350 Gen9
- HPE ProLiant ML370 G6

ProLiant SL (scalable system):

- HPE ProLiant SL160s G6
- HPE ProLiant SL165s G7
- HPE ProLiant SL165z G7
- HPE ProLiant SL170s G6
- HPE ProLiant SL230 Gen8
- HPE ProLiant SL250 Gen8
- HPE ProLiant SL390s G7

Apollo Servers

- Apollo 2000 - XL1x0 Node
- Apollo 4200
- Apollo 4500 – 4500 Chassis
- Apollo 6000 – XL220a Gen8 v2(OBS)
- Apollo 6000 – XL230b Gen9
- Apollo 6000 – XL250a Gen9



Overview

ProLiant MicroServer (Just Right First Server):

- HPE ProLiant MicroServer
- HPE ProLiant MicroServer Gen8

Integrity Rack Servers

- HPE Integrity rx2800 i4
- HPE Integrity rx2800 i2

Only the following models are supported for Integrity Rack Servers:

- 631341-B21
- 631360-B21
- 672097-373

Notes: [This is a list of supported servers. Some may be discontinued.](#)

Warranty

The warranty for this device is 1 year parts only. Maximum: The remaining warranty of the HPE server product in which it is installed (to a maximum three-year limited warranty).

- Response - Upgrade on-site response from next business day to same day 4 hours
 - Coverage - Extend hours of coverage from 9 hours x 5 days to 24 hours x 7 days
 - Duration - Select duration of coverage for a period of 1, 3, or 5 years
 - Warranty upgrade options can come in the form of Care Packs, which are sold at the HPE System level this product attaches too.
-



Service and Support

HPE Services

No matter where you are in your digital transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

<https://www.hpe.com/services>

Consulting Services

No matter where you are in your journey to hybrid cloud, experts can help you map out your next steps. From determining what workloads should live where, to handling governance and compliance, to managing costs, our experts can help you optimize your operations.

<https://www.hpe.com/services/consulting>

HPE Managed Services

HPE runs your IT operations, providing services that monitor, operate, and optimize your infrastructure and applications, delivered consistently and globally to give you unified control and let you focus on innovation.

[HPE Managed Services | HPE](#)

Operational services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources. Meet service-level targets and business objectives with features designed to drive better business outcomes.

<https://www.hpe.com/services/operational>

HPE Complete Care Service

HPE Complete Care Service is a modular, edge-to-cloud IT environment service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals through a personalized experience. All delivered by an assigned team of HPE Services experts. HPE Complete Care Service provides:

- A complete coverage approach -- edge to cloud
- An assigned HPE team
- Modular and fully personalized engagement
- Enhanced Incident Management experience with priority access
- Digitally enabled and AI driven customer experience

<https://www.hpe.com/services/complecare>

HPE Tech Care Service

HPE Tech Care Service is the operational support service experience for HPE products. The service goes beyond traditional support by providing access to product specific experts, an AI driven digital experience, and general technical guidance to not only reduce risk but constantly search for ways to do things better. HPE Tech Care Service delivers a customer-centric, AI driven, and digitally enabled customer experience to move your business forward. HPE Tech Care Service is available in three response levels. Basic, which provides 9x5 business hour availability and a 2-hour response time. Essential which provides a 15-minute response time 24x7 for most enterprise level customers, and Critical which includes a 6-hour repair commitment where available and outage management response for severity 1 incidents.

<https://www.hpe.com/services/techcare>



Service and Support

HPE Lifecycle Services

HPE Lifecycle Services provide a variety of options to help maintain your HPE systems and solutions at all stages of the product lifecycle. A few popular examples include:

- Lifecycle Install and Startup Services: Various levels for physical installation and power on, remote access setup, installation and startup, and enhanced installation services with the operating system.
- HPE Firmware Update Analysis Service: Recommendations for firmware revision levels for selected HPE products, taking into account the relevant revision dependencies within your IT environment.
- HPE Firmware Update Implementation Service: Implementation of firmware updates for selected HPE server, storage, and solution products, taking into account the relevant revision dependencies within your IT environment.
- Implementation assistance services: Highly trained technical service specialists to assist you with a variety of activities, ranging from design, implementation, and platform deployment to consolidation, migration, project management, and onsite technical forums.
- HPE Service Credits: Access to prepaid services for flexibility to choose from a variety of specialized service activities, including assessments, performance maintenance reviews, firmware management, professional services, and operational best practices.

Notes: To review the list of Lifecycle Services available for your product go to:

<https://www.hpe.com/services/lifecycle>

For a list of the most frequently purchased services using service credits, see the [HPE Service Credits Menu](#)

Other Related Services from HPE Services:

HPE Education Services

Training and certification designed for IT and business professionals across all industries. Broad catalogue of course offerings to expand skills and proficiencies in topics ranging from cloud and cybersecurity to AI and DevOps. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options.

<https://www.hpe.com/services/training>

Defective Media Retention

An option available with HPE Complete Care Service and HPE Tech Care Service and applies only to Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and services options.

Parts and Materials

HPE will provide HPE-supported replacement parts and materials necessary to maintain the covered hardware product in operating condition, including parts and materials for available and recommended engineering improvements.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

How to Purchase Services

Services are sold by Hewlett Packard Enterprise and Hewlett Packard Enterprise Authorized Service Partners:

- Services for customers purchasing from HPE or an enterprise reseller are quoted using HPE order configuration tools.
- Customers purchasing from a commercial reseller can find services at <https://ssc.hpe.com/portal/site/ssc/>



Service and Support

AI Powered and Digitally Enabled Support Experience

Achieve faster time to resolution with access to product-specific resources and expertise through a digital and data driven customer experience

Sign into the HPE Support Center experience, featuring streamlined self-serve case creation and management capabilities with inline knowledge recommendations. You will also find personalized task alerts and powerful troubleshooting support through an intelligent virtual agent with seamless transition when needed to a live support agent.

<https://support.hpe.com/hpesc/public/home/signin>

Consume IT On Your Terms

HPE GreenLake edge-to-cloud platform brings the cloud experience directly to your apps and data wherever they are—the edge, colocations, or your data center. It delivers cloud services for on-premises IT infrastructure specifically tailored to your most demanding workloads. With a pay-per-use, scalable, point-and-click self-service experience that is managed for you, HPE GreenLake edge-to-cloud platform accelerates digital transformation in a distributed, edge-to-cloud world.

- Get faster time to market
- Save on TCO, align costs to business
- Scale quickly, meet unpredictable demand
- Simplify IT operations across your data centers and clouds

To learn more about HPE Services, please contact your Hewlett Packard Enterprise sales representative or Hewlett Packard Enterprise Authorized Channel Partner. Contact information for a representative in your area can be found at "Contact HPE"

<https://www.hpe.com/us/en/contact-hpe.html>

For more information

<http://www.hpe.com/services>



Technical Specifications

Physical characteristics	Keys	104, 105, 109 layout (depending upon country)
	Shipping Dimensions	21.19 x 12.06 x 3.69 in (53.8 x 30.6 x 9.4 cm)
	Drive Dimensions - USB Keyboard (H x W x L, maximum)	0.98 x 6.43 x 18.06 in (24.8 x 163.2 x 458.8 mm)
	Drive Dimensions - USB Mouse (H x W x L, maximum)	1.59 x 24.33 x 45.98 in (40.28 x 61.81 x 116.79 mm)
	Shipping Weight Drive Weight - USB Keyboard (H x W x L, maximum)	2 lb (0.9 kg) minimum
	Shipping Weight Drive Weight - USB Mouse (H x W x L, maximum)	0.27 lb (0.12 kg)
Electrical	Operating voltage	+ 5VDC \pm 5%
	Power consumption	USB Keyboard : 50mA maximum (with three LEDs ON) USB Mouse: 100mA maximum
	System interface	USB Type A plug connector
	ESD	CE level 4, 15-kV air discharge
	EMI - RFI	Conforms to FCC rules for a Class B computing device
	Microsoft® PC 99 - 2001	Functionally compliant
Mechanical	Keycaps	Low Speed
	Resolution	400 \pm 20% DPI
	Cable length	6 ft (1.8 m)
	Microsoft PC99 - 2001	Mechanically compliant
	Acoustics	43-dBA maximum sound pressure level
MTBF	100,000 Power On Hours (POH)	
Ambient Temperature	Operating	50° to 122° F (10° to 50° C)
	Storage/Transportation	- 22° to 140° F (- 30° to 60° C)



Technical Specifications

Relative Humidity	Operating humidity	10% to 90% (non-condensing at ambient)
	Non-operating humidity	20% to 80% (non-condensing at ambient)
Regulatory approvals (Compliant)	USB Keyboard	UL, cUL, FCC Class B, CE-Mark, C.I.S.P.R, ICES-003 class B, TUV, TUV GS, VCCI, BSMI, MIC
	USB Mouse	UL, cUL, FCC Class B, CE Mark, TUV, TUV GS, VCCI, BSMI, C-Tick, KCC, ICES-003 class B

Environment-friendly Products and Approach

End-of-life Management and Recycling

Hewlett Packard Enterprise offers end-of-life Hewlett Packard Enterprise product return, trade-in, and recycling programs in many geographic areas. For trade-in information, please go to: <http://www.hpe.com/info/recycle>. To recycle your product, please go to: <http://www.hpe.com/info/recycle> or contact your nearest Hewlett Packard Enterprise sales office. Products returned to Hewlett Packard Enterprise will be recycled, recovered or disposed of in a responsible manner.

The EU WEEE directive (2002/95/EC) requires manufacturers to provide treatment information for each product type for use by treatment facilities. This information (product disassembly instructions) is posted on the Hewlett Packard Enterprise web site at: <http://www.hpe.com/info/recycle>. These instructions may be used by recyclers and other WEEE treatment facilities as well as HPE OEM customers who integrate and re-sell Hewlett Packard Enterprise equipment.



Summary of Changes

Date	Version History	Action	Description of Change
08-Jan-2024	Version 11	Changed	Service and Support section was updated
15-Nov-2021	Version 10	Changed	Service and Support Pointnext Tech Care and Complete Care information updated
23-Oct-2017	From Version 8 to 9	Changed	Care Pack naming and Service and Support- Parts and Materials updated
16-Dec-2016	From Version 7 to 8	Changed	Overview section was updated.
07-Oct-2016	From Version 6 to 7	Changed	QuickSpecs was rebranded.
28-Sep-2015	From Version 5 to 6	Changed Added	Overview and Technical Specifications sections were updated. SKUs added in Overview section: 631341-B21, 631360-B21, 672097-373.
21-Jun-2013	From Version 4 to 5	Changed	Color was revised.
28-Dec-2012	From Version 3 to 4	Changed	Service and Support: URL change made in Additional Services Information section.
06-Mar-2012	From Version 2 to 3	Changed	Models and Compatibility were revised.
20-Jun-2011	From Version 1 to 2	Removed	Mentions of StorageWorks were removed.



Copyright

Make the right purchase decision.
Contact our presales specialists.



© Copyright 2024 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Windows are US registered trademarks of Microsoft Corporation.

c04168349 - 13972 - Worldwide - V11 - 08-January-2024