

Cisco Network Convergence System 5500 Series: 55A1 Fixed Chassis

Contents

| | |
|------------------------------------|----|
| Product overview | 3 |
| Features and benefits | 4 |
| Cisco IOS XR Software overview | 4 |
| Software requirements | 4 |
| Specifications | 5 |
| Supported transceivers modules | 8 |
| Environment | 8 |
| Regulatory standards compliance | 9 |
| Ordering information | 9 |
| Warranty | 14 |
| Cisco environmental sustainability | 14 |
| Service and Support | 15 |
| Cisco Capital | 15 |

Product overview

According to Cisco's 2019 VNI Global Mobile Data Traffic Forecast, mobile data traffic is expected to grow at a 46 percent Compound Annual Growth Rate (CAGR) from 2017 to 2022, two times faster than the growth of global IP fixed traffic during the same period. To help network providers meet these challenges, the Cisco® Network Convergence System 5500 Series is built with features such as high port densities, deep packet buffering, and forwarding hardware optimized for these types of deployments.

The Cisco NCS 55A1 are the second generation of fixed chassis available for the Cisco NCS 5500 Series. That new series offers three fixed configuration chassis, the NCS 55A1-36H-S, NCS 55A1-36H-SE-S and NCS 55A1-24H. These systems provide functionality vital to both the Top of Rack (ToR) and spine or leaf roles common to modern spine-and-leaf architectures. Capabilities such as advanced packet classification, segment routing, ultra-wide ECMP, programmable network management and telemetry are added to the robust and mature features already present in Cisco IOS® XR Software Release 6.3.1.

The Cisco NCS 55A1-36H-S and NCS 55A1-36H-SE-S (Figure 1) provide 36 ports of 100 Gigabit Ethernet with full line rate MACsec capability. All the ports can support 100GE and 40GE optics as well as 25GE to 10GE breakout. They use QSFP28/QSFP+ form factor transceivers. They are designed for base and high scale configuration needs and are supported starting with Cisco IOS XR Software Release 6.3.1.



Figure 1.
The Cisco NCS 55A1-36H-S and NCS 55A1-36H-SE-S Chassis

The Cisco NCS 55A1-24H (Figure 2) provide 24 ports of 100 Gigabit Ethernet. All the ports can support 100GE and 40GE optics as well as 25G and 10GE breakout. This chassis uses QSFP28/QSFP+ form factor transceivers. This chassis is designed for high scale configuration needs and is supported starting with Cisco IOS XR Software Release 6.3.1.



Figure 2.
The Cisco NCS-55A1-24H Chassis

Features and benefits

MACsec is a Layer 2 IEEE 802.1AE standard for encrypting packets between two MACsec-capable routers. MACsec secures the data on physical media, making it impossible for data to be compromised at higher layers. As a result, MACsec encryption takes priority over any other encryption method for higher layers, such as IPsec and SSL. MACsec provides encryption at Layer 2, which is provided by the Advanced Encryption Standard (AES) algorithm that replaces the DES algorithm. MACsec uses the MACsec Key Agreement protocol (MKA) to exchange session keys, and manage encryption keys.

Advantages of Using MACsec Encryption:

- **Client-oriented mode:** MACsec is used in setups where two routers that are peering with each other can alternate as a key server or a key client prior to exchanging keys. The key server generates and maintains the CAK between the two peers.
- **Data integrity check:** MACsec uses MKA to generate an Integrity Check Value (ICV) for the frame arriving on the port. If the generated ICV is the same as the ICV in the frame, then the frame is accepted; otherwise, it is dropped.
- **Data encryption:** MACsec provides port-level encryption on the line card of the router. This means that the frames sent out of the configured port are encrypted, and frames received on the port are decrypted. MACsec also provides a mechanism with which you can configure whether only encrypted frames or all frames (encrypted and plain) are accepted on the interface.
- **Replay protection:** When frames are transmitted through the network, there is a possibility of frames getting out of the ordered sequence. MACsec provides a configurable window that accepts a specified number of out-of-sequence frames.
- **Support for clear traffic:** If configured accordingly, data that is not encrypted is allowed to transit through the port.

Cisco IOS XR Software overview

The Cisco NCS 55A1 Series fixed chassis is powered by industry leading carrier-class 64-bit version of Cisco IOS XR Software designed on operational efficiency, optimized utilization and service agility ([evolved programmable network](#)). Cisco IOS XR Software offers rich features such as iPXE boot, auto provisioning, native support for third-party application hosting, machine-to-machine interface, telemetry, and flexible software package delivery.

For a complete list of supported features, refer to [Cisco Feature Navigator](#).

Software requirements

The Cisco NCS 55A1 Series fixed chassis support Cisco IOS XR Software Release 6.3.1 and later.

Specifications

Tables 1 through 11 list key specifications for the Cisco NCS 55A1 Series fixed chassis.

Table 1. Features and benefits of Cisco NCS 55A1 Series Fixed Chassis (Cisco IOS XR Software 6.3.1 Release or Beyond)

| Feature | Specification |
|--|--|
| Integrated Interface | 10GE/25GE (breakout using certain transceivers) 40GE/100 Gigabit Ethernet support |
| MACsec encryption NCS-55A1-36H-S / NCS-55A1-36H-SE-S | IEEE 802.1AE standards-based Layer 2 hop-by-hop encryption that provides data confidentiality and integrity for media access independent protocols |
| Industry leading carrier-class Cisco IOS XR Software | Visibility and telemetry Machine-to-machine interface Application hosting Flexible platform and packaging Modularity Automation |
| Management ports | Provides easy access to system console |
| External USB port | Helps simplify image and file management |
| Embedded USB (eUSB) storage | Flash memory devices for storing software image, configuration, logging, and recovery |
| Power consumption | Ultra-low power per Gigabit Ethernet |
| Redundancy | Redundant fan tray Redundant AC or DC power supply |

Table 2. Cisco NCS 55A1 Fixed Chassis specification

| Feature | Specification | | | | |
|------------------------------------|--|------------------------------------|--|--------------|---|
| Chassis PID | NCS-55A1-36H-S NCS-55A1-36H-SE-S NCS-55A1-24H | | | | |
| Interfaces | <table border="1"> <tr> <td>NCS-55A1-36H-S / NCS-55A1-36H-SE-S</td> <td>144 ports of 10GE/25GE (breakout using certain transceivers) 36 ports of 40GE/100GE</td> </tr> <tr> <td>NCS-55A1-24H</td> <td>96 ports of 10GE/25GE (breakout using certain transceivers) 24 ports of 40GE/100GE</td> </tr> </table> | NCS-55A1-36H-S / NCS-55A1-36H-SE-S | 144 ports of 10GE/25GE (breakout using certain transceivers) 36 ports of 40GE/100GE | NCS-55A1-24H | 96 ports of 10GE/25GE (breakout using certain transceivers) 24 ports of 40GE/100GE |
| NCS-55A1-36H-S / NCS-55A1-36H-SE-S | 144 ports of 10GE/25GE (breakout using certain transceivers) 36 ports of 40GE/100GE | | | | |
| NCS-55A1-24H | 96 ports of 10GE/25GE (breakout using certain transceivers) 24 ports of 40GE/100GE | | | | |
| Integrated Route Processor | IOS-XR 64-bit software running on a 8 cores x86 CPU @ 1.6Ghz | | | | |
| System Memory | 32GB | | | | |

| Feature | Specification | |
|---|---|--|
| Solid-State Disk (SSD) drive | NCS-55A1-36H-S / NCS-55A1-36H-SE-S: 128GB NCS-55A1-24H: 128GB | |
| Management Ports | 2x RJ45, one for console and one for management LAN ports | |
| Timing Ports | TOD ports: UART1 with RS422 and RS232 support Pin 1: RS-232 Output Pin 5: GND Pin 2: RS-232 Input Pin 6: 1PPS+ Input/Output Pin 3: 1PPS- Input/Output Pin 7: RS-422- Input/Output Pin 4: GND Pin 8: RS-422+ Input/Output 10Mhz and 1PPS I/O connector *NCS-55A1-36H-S timing capable from hardware shipped after July 2019 | |
| Flexible Forwarding Ports | 100 Gigabit Ethernet or 25GE (breakout using certain transceivers) with QSFP28 optics QSFP+ optics to support 40GE and 4x 10GE breakout options available | |
| Performance | NCS-55A1-36H-S / NCS-55A1-36H-SE-S: Up to 3.6 Tbps of system throughput Full line rate MACsec encryption on all 36 x 100G ports NCS-55A1-24H: Up to 1.8 Tbps of system throughput | |
| Route Scale | NCS-55A01-36H-S: Up to 1M FIB entries NCS-55A01-36H-SE-S: Up to 4M FIB entries NCS-55A1-24H: Up to 2M FIB entries | |
| Power & cooling features | 2 hot-swappable power supplies providing 1+1 redundancy Reversible airflow available (power supply PID determines airflow direction) NCS-55A1-36H-S / NCS-55A1-36H-SE-S: 3 hot-swappable fan trays provide redundant system cooling NCS-55A1-24H: 3 hot-swappable fan trays provide redundant system cooling | |
| Power Consumption Output power. For input power, divide by 0.91, which represents average supply efficiency | NCS-55A1-36H-S | Typical: 1100W at 27 degrees Celsius Maximum: 1450W at 55 degrees Celsius |
| | NCS-55A1-36H-SE-S | Typical: 1300W at 27 degrees Celsius Maximum: 1700W at 55 degrees Celsius |
| | NCS-55A1-24H | Typical: 600W at 27 degrees Celsius Maximum: 800W at 55 degrees Celsius |
| Physical Specification | NCS-55A1-36H-S / NCS-55A1-36H-SE-S Height: 1RU 1.72 in. (4.36 cm) Width: 17.3 in. (43.94 cm) Depth: 30.0 in. (76.20 cm) NCS-55A1-36H-S Weight: 33 lbs (14.97 kgs) NCS-55A1-36H-SE-S Weight: 33 lbs (14.97 kgs) | NCS-55A1-24H Height: 1RU 1.72 in. (4.36 cm) Width: 17.3 in. (43.94 cm) Depth: 21.7 in. (55.12 cm) Weight: 24 lbs (10.89 kgs) |

Table 3. Software feature support on NCS 55A1 Fixed Chassis in Cisco IOS XR Software 6.3.1 release or beyond

| Description | Specification |
|---------------------------------|---|
| Layer 2 | <ul style="list-style-type: none"> • Layer 2 switch ports • IEEE 802.1Q VLAN encapsulation/Q-in-Q encapsulation • IEEE 802.1ad • Cisco Bundle Ethernet technology (up to 32 ports per Ethernet Bundle) • Link Aggregation Control Protocol (LACP): IEEE 802.3ad • Jumbo frames on all ports (up to 9216 bytes) • L2 ingress Access Control List (ACL) • L2 AC-AC cross-connect • Ethernet Flow Point (EFP) and VLAN trunks • Virtual Router Redundancy Protocol (VRRP) |
| Layer 3 | <ul style="list-style-type: none"> • IPv4 and IPv6 unicast • Layer 3 interfaces: physical and sub-interfaces • Routing protocols: static, Open Shortest Path First (OSPFv2), OSPFv3, Intermediate System to Intermediate System (ISIS), ISISv6, and Border Gateway Protocol (BGP) • 32-way equal-cost multipath (ECMP) • L3 ingress and egress IPv4 ACL and IPv6 ACL • Bidirectional Forwarding Detection (BFD) • Cisco Bundle Ethernet technology (up to 32 ports per Ethernet Bundle) • Link Aggregation Control Protocol (LACP): IEEE 802.3ad • Jumbo frame support (up to 9216 bytes) • Hot Standby Router Protocol (HSRP)/Virtual Router Redundancy Protocol (VRRP) • Layer 3 Virtual Private Network (L3VPN) |
| MPLS | <ul style="list-style-type: none"> • Label switching • LDP • MPLS Traffic Engineering • Ethernet over MPLS (EoMPLS) |
| Segment Routing (SR) | <ul style="list-style-type: none"> • Segment routing-based transport • ISIS extensions to segment routing • OSPF extensions to segment routing • BGP egress peering engineering • Segment Routing Traffic Engineering (SR-TE) • Segment Routing Topology Independent Loop Free Alternatives (TI-LFA) |
| Quality of Service (QoS) | <ul style="list-style-type: none"> • Hierarchical QoS • Ingress classification based on Class of Service (L2), IP differentiated service code point (L3), IP ACL (L3/L4), IP precedence (type of service) (L3) • DSCP marking • 8 number of queues for user traffic • Support for priority queuing |
| Timing | <ul style="list-style-type: none"> • SyncE, G.8265.1, G.8275.1, G.8275.2, G.8273.2 <ul style="list-style-type: none"> ◦ NCS-55A1-24H support from 6.5.2 and beyond ◦ NCS-55A1-36H-SE-S support from 7.0.1 and beyond ◦ NCS-55A1-36H-S support from 7.0.1 and beyond |

| Description | Specification |
|-------------------|---|
| Automation | <ul style="list-style-type: none"> • Zero-Touch Provisioning (ZTP), iPXE • Configuration management • Network Configuration Protocol (NETCONG/YANG model) |
| Security | <ul style="list-style-type: none"> • Provides comprehensive network security features, including ACLs; control-plane protection; management plane protection; routing authentications; Authentication, Authorization, and Accounting (AAA) and Terminal Access Controller Access-Control System Plus (TACACS+); Secure Shell (SSH) Protocol; SNMPv3; and RPL support • Layer 2 ingress ACLs • Layer 3 ingress ACLs |
| Management | <ul style="list-style-type: none"> • MIB, XML, JSON, GPB, and SNMP • MPLS OAM (label switched path [LSP] ping, LSP traceroute) • Ethernet OAM |

Supported transceivers modules

Check the data sheet for Cisco NCS 5500 Series supported transceivers module.

Environment

Table 4. Environmental properties for NCS 55A1 Fixed systems

| Property | Cisco NCS 5500 Series |
|--|---|
| Normal Operating Temperature | Port-S Intake supply: 32 to 104° F (0 to 40° C) – Port-S Exhaust supply: 32 to 95° F (0 to 35° C) |
| Non-operating (storage) Temperature | -40 to 158° F (-40 to 70° C) |
| Operating Humidity | 5% to 95% (noncondensing) Note: Not to exceed 0.024 kg water or dry air |
| Storage (relative) Humidity | 5% to 95% at 40C per NEBS GR-63-Core Note: Not to exceed 0.024 kg water or dry air |
| Altitude | 0 to 9,842 ft (0 to 3000m) |
| Power Inputs | Worldwide ranging AC (90–265V; 50–60 Hz) Worldwide ranging DC (-40V to -72V) |
| Air Flow | Front to back (port-side intake) Back to front (port-side exhaust) |

Regulatory standards compliance

Table 5. Regulatory standards compliance: Safety and EMC

| Specification | Description |
|--|---|
| Regulatory compliance | Products should comply with CE Markings according to directives 2004/108/EC and 2006/95/EC |
| Network Equipment Building Standards (NEBS) | Designed to meet GR-63-CORE and GR-1089-CORE |
| Safety | <ul style="list-style-type: none"> • UL 60950-1 Second Edition • CAN/CSA-C22.2 No. 60950-1 Second Edition • EN 60950-1 Second Edition • IEC 60950-1 Second Edition • AS/NZS 60950-1 • GB4943 |
| EMC Standards | <ul style="list-style-type: none"> • 47CFR Part 15 (CFR 47) Class A • AS/NZS CISPR22 Class A • CISPR22 Class A • EN55022 Class A • ICES003 Class A • VCCI Class A • EN61000-3-2 • EN61000-3-3 • KN22 Class A • CNS13438 Class A |
| EMC Immunity | <ul style="list-style-type: none"> • EN55024 • CISPR24 • EN300386 • KN 61000-4 series |
| RoHS | The product is RoHS-6 compliant with exceptions for leaded-Ball Grid-Array (BGA) balls and lead press-fit connectors. |

Additional information related to [NCS5500 regulatory compliance and safety standards](#).

Ordering information

Table 6. Ordering information for NCS 55A1-36H-SE-S

| Category | Part Number | Description |
|-----------------------|------------------|--|
| Bundle Chassis | NCS-55A1-36H-B | NCS55A1 Fixed 36x100G Base chassis bundle |
| RTU | NC55-A1-36HB-RTU | NCS 55A1 36x100G Base Right To Use License |
| Chassis | NCS-55A1-36H-S | NCS55A1 Fixed 36x100G Base chassis |

| Category | Part Number | Description |
|--------------------|-------------------|--|
| SW | XR-NC55-P-06.06 | Cisco NCS 5500 IOS XR 6.6 Image |
| | XR-NC55-PK9-06.06 | Cisco NCS 5500 IOS XR 6.6 PK9 Image |
| Fan Option | NC55-A1-FAN-FW | NCS 5500 Fan Tray 1RU Chassis Port-S Intake / Front-to-back Port-Side intake |
| | NC55-A1-FAN-RV | NCS 5500 Fan Tray 1RU Chassis Port-S Exhaust / Back-to-Front Port-side exhaust |
| Power Option | NC55-2KW-ACFW | NCS 5500 AC 2KW Power Supply Port-S Intake / Front-to-back |
| | NC55-2KW-ACRV | NCS 5500 AC 2KW Power Supply Port-S Exhaust / Back-to-Front |
| | NC55-2KW-DCFV | NCS 5500 DC 2KW Power Supply Port-S Intake / Front-to-back |
| | NC55-2KW-DCRV | NCS5500 DC 2KW Power Supply Port-S Exhaust/Back-to-Front |
| Accessories Option | NC55-A1-ACC-KIT | NCS 5500 Accessory Kit for 1RU Chassis |
| | NC55-A1-NEBS-KIT | NCS 5500 NEBS Kit for 1RU Chassis |

Table 7. Ordering information for NCS 55A1-36H-SE-S

| Category | Part Number | Description |
|--------------------|--------------------|--|
| Bundle Chassis | NCS-55A1-36H-SE-B | NCS55A1 Fixed 36x100G Scale chassis bundle |
| RTU | NC55-A1-36HSEB-RTU | NCS 55A1 36x100G Scale Right To Use License |
| Chassis | NCS-55A1-36H-SE-S | NCS55A1 Fixed 36x100G Scale chassis |
| SW | XR-NC55-P-06.06 | Cisco NCS 5500 IOS XR 6.6 Image |
| | XR-NC55-PK9-06.06 | Cisco NCS 5500 IOS XR 6.6 PK9 Image |
| Fan Option | NC55-A1-FAN-FW | NCS 5500 Fan Tray 1RU Chassis Port-S Intake / Front-to-back Port-Side intake |
| | NC55-A1-FAN-RV | NCS 5500 Fan Tray 1RU Chassis Port-S Exhaust / Back-to-Front Port-side exhaust |
| Power Option | NC55-2KW-ACFW | NCS 5500 AC 2KW Power Supply Port-S Intake / Front-to-back |
| | NC55-2KW-ACRV | NCS 5500 AC 2KW Power Supply Port-S Exhaust / Back-to-Front |
| | NC55-2KW-DCFV | NCS 5500 DC 2KW Power Supply Port-S Intake / Front-to-back |
| | NC55-2KW-DCRV | NCS5500 DC 2KW Power Supply Port-S Exhaust/Back-to-Front |
| Accessories Option | NC55-A1-ACC-KIT | NCS 5500 Accessory Kit for 1RU Chassis |
| | NC55-A1-NEBS-KIT | NCS 5500 NEBS Kit for 1RU Chassis |

Table 8. Ordering information for NCS 55A1-24H

| Category | Part Number | Description |
|---------------------------|-------------------|--|
| Bundle Chassis | NCS-55A1-24H-B | NCS55A1 Fixed 24x100G chassis bundle |
| RTU | NC55-A1-24HB-RTU | NCS 55A1 24x100G Right To Use License |
| Chassis | NCS-55A1-24H | NCS55A1 Fixed 24x100G chassis |
| SW | XR-NC55-P-06.06 | Cisco NCS 5500 IOS XR 6.6 Image |
| | XR-NC55-PK9-06.06 | Cisco NCS 5500 IOS XR 6.6 PK9 Image |
| Fan Option | NC55-A1-FAN-FW | NCS 5500 Fan Tray 1RU Chassis Port-S Intake / Front-to-back Port-Side intake |
| | NC55-A1-FAN-RV | NCS 5500 Fan Tray 1RU Chassis Port-S Exhaust / Back-to-Front Port-side exhaust |
| Power Option | NCS-1100W-ACFW | NCS 5500 AC 1100W Power Supply Port-S Intake / Front-to-back |
| | NCS-1100W-ACRV | NCS 5500 AC 1100W Power Supply Port-S Exhaust/Back-to-Front |
| | NCS-1100W-DCRV | NCS 5500 DC 1100W Power Supply Port-S Exhaust/Back-to-Front |
| | NCS-950W-DCFV | NCS 5500 DC 950W Power Supply Port-S Intake/Front-to-back |
| Accessories Option | NC55-A1-ACC-KIT | NCS 5500 Accessory Kit for 1RU Chassis |
| | NC55-24H-NEBS-KIT | NCS 5500 NEBS Kit for NCS-55A1-24H Chassis |

Table 9. Ordering information for optics supported on NCS 55A1 chassis

| Type | Part Number | Description |
|------------|----------------------------|--|
| 40G | QSFP-40G-SR4 | 40GBASE-SR4 QSFP+ transceiver module for MMF, 4-lanes, 850-nm wavelength, 12-fiber MPO/MTP connector |
| | QSFP-40G-SR4-S | 40GBASE-SR4 (IEEE 802.3ba Spec.) QSFP+ transceiver module for MMF, 4-lanes, 850-nm wavelength, 12-fiber MPO/MTP connector |
| | QSFP-40G-CSR4 | 40GBASE-CSR4 QSFP+ transceiver module for MMF, 4-lanes, 850-nm wavelength, MPO-12 connector, 300 m reach with OM3 fiber |
| | QSFP-40G-SR-BD | 40G QSFP Bi-Directional transceiver module, Duplex Multi-mode Fiber, LC Duplex connector, 100m reach with OM3 fiber |
| | QSFP-40G-LR4 | 40GBASE-LR4 QSFP40G transceiver module for SMF, 4 CWDM lanes in 1310nm window Mixed inside module, Duplex LC connector, 10km, Multi-rate Support (40G Ethernet and OTU3) |
| | QSFP-40G-LR4-S | 40GBASE-LR4 QSFP40G transceiver module for SMF, 4 CWDM lanes in 1310nm window Mixed inside module, Duplex LC connector, 10km |
| | WSP-Q40GLR4L | 40GBASE-LR4 QSFP40G transceiver module for SMF, 4 CWDM lanes in 1310nm window Mixed inside module, Duplex LC connector, 2km |
| | QSFP-4x10G-LR-S (40G-PSM4) | 4x10GBASE-LR/40G PSM4 transceiver |
| | QSFP-40G-ER4 | 40GBASE-LR4 QSFP40G transceiver module for Single Mode Fiber, 4 CWDM lanes in 1310nm window Mixed inside module, Duplex LC connector, 40km |

| Type | Part Number | Description |
|------|-------------------|--|
| 100G | QSFP-100G-SR4-S | 100GBASE SR4 QSFP Transceiver, MPO, 100m over OM4 MMF |
| | QSFP-100G-LR4-S | 100GBASE LR4 QSFP Transceiver, LC, 10km over SMF |
| | QSFP-100G-CWDM4-S | 100GBASE CWDM4 QSFP Transceiver, LC, 2km over SMF |
| | QSFP-100G-PSM4-S | 100GBASE PSM4 QSFP Transceiver, MPO, 500m over SMF |
| | QSFP-100G-AOC1M | 100GBASE QSFP Active Optical Cables 1 meter |
| | QSFP-100G-AOC2M | 100GBASE QSFP Active Optical Cables 2 meter |
| | QSFP-100G-AOC3M | 100GBASE QSFP Active Optical Cables 3 meter |
| | QSFP-100G-AOC5M | 100GBASE QSFP Active Optical Cables 5 meter |
| | QSFP-100G-AOC7M | 100GBASE QSFP Active Optical Cables 7 meter |
| | QSFP-100G-AOC10M | 100GBASE QSFP Active Optical Cables 10 meter |
| | QSFP-100G-AOC15M | 100GBASE QSFP Active Optical Cables 15 meter |
| | QSFP-100G-AOC20M | 100GBASE QSFP Active Optical Cables 20 meter |
| | QSFP-100G-AOC25M | 100GBASE QSFP Active Optical Cables 25 meter |
| | QSFP-100G-AOC30M | 100GBASE QSFP Active Optical Cables 30 meter |
| | QSFP-4SFP25G-CU5M | 100GBASE QSFP to 4xSFP25G Passive Copper Splitter Cables 5 meter |

Table 10. Ordering information for power cables supported on NCS 55A1 chassis

| Part Number | Description |
|------------------------|--|
| PWR-CORD-ROK-A | Power Cord ROK 1.8m BlackYP-22K To YC-12 |
| CAB-250V-10A-AR | AC Power Cord - 250V, 10A - Argentina |
| CAB-250V-10A-BR | Power Cord - 250V, 10A - Brazil |
| CAB-250V-10A-CN | AC Power Cord - 250V, 10A - PRC |
| CAB-250V-10A-ID | AC Power Cord - 250V, 10A, India |
| CAB-250V-10A-IS | AC Power Cord - 250V, 10A - Israel |
| CAB-9K10A-AU | Power Cord, 250VAC 10A 3112 Plug, Australia |
| CAB-9K10A-EU | Power Cord, 250VAC 10A CEE 7/7 Plug, EU |
| CAB-9K10A-IT | Power Cord, 250VAC 10A CEI 23-16/VII Plug, Italy |
| CAB-9K10A-SW | Power Cord, 250VAC 10A MP232 Plug, SWITZ |
| CAB-9K10A-UK | Power Cord, 250VAC 10A BS1363 Plug (13 A fuse), UK |
| CAB-9K12A-NA | Power Cord, 125VAC 13A NEMA 5-15 Plug, North America |
| CAB-AC-L620-C13 | AC Power Cord, NEMA L6-20 - C13, 2M/6.5ft |

| Part Number | Description |
|------------------|--|
| CAB-ACTW | AC Power Cord (Taiwan), C13, EL 302, 2.3M |
| CAB-C13-C14-2M | Power Cord Jumper, C13-C14 Connectors, 2 Meter Length |
| CAB-C13-CBN | Cabinet Jumper Power Cord, 250 VAC 10A, C14-C13 Connectors |
| CAB-IND-10A | 10A Power cable for India |
| CAB-N5K6A-NA | Power Cord, 200/240V 6A North America |
| CAB-C13-C14-JMPR | Recessed receptacle AC power cord 27in |
| CAB-3P-JPN | AC Power Cord (Japan), C13, 3 Prong Plug, 2.3M |

Table 11. Ordering information for software licenses available on NCS-55A1-36H-S, NCS-55A1-36H-SE-S, NCS-55A1-24H

| Category | Part Number | Description |
|--------------------------|------------------|--|
| NCS-55A1-36H-S | NC55P-ADVL3-36HT | NCS 5500 L3VPN Lic for NC55-36X100G & NC55-36X100G-S & NCS-55A1-36H-S |
| | NC55P-ADVL2-36HT | NCS 5500 L2VPN Lic for NC55-36X100G & NC55-36X100G-S & NCS-55A1-36H-S |
| | NC55P-CRAGR-36HT | NCS 5500 Core and Aggregation Lic for NC55-36X100G & NC55-36X100G-S & NCS-55A1-36H-S |
| | NC55P-PEER-36HT | NCS 5500 Peering Lic for NC55-36X100G & NC55-36X100G-S & NCS-55A1-36H-S |
| | NC55P-ADVDC-36HT | NCS 5500 Advance Data Center Lic for NC55-36X100G & NC55-36X100G-S & NCS-55A1-36H-S |
| | NC55P-MSEC-36HT | NCS 5500 MACsec Lic for NC55-36X100G-S |
| | NC55P-TIMING-F | NCS 5500 Timing and Mobility Lic for Fixed Chassis **Supported 7.0.1 and beyond |
| NCS-55A1-36H-SE-S | NC55P-ADVL3-36HS | NCS 5500 L3VPN Lic for NC55-36X100G-A-SE & NCS-55A1-36H-SE-S |
| | NC55P-ADVL2-36HS | NCS 5500 L2VPN Lic for NC55-36X100G-A-SE & NCS-55A1-36H-SE-S |
| | NC55P-CRAGR-36HS | NCS 5500 Core and Aggregation Lic for NC55-36X100G-A-SE & NCS-55A1-36H-SE-S |
| | NC55P-PEER-36HS | NCS 5500 Peering Lic for NC55-36X100G-A-SE & NCS-55A1-36H-SE-S |
| | NC55P-ADVDC-36HS | NCS 5500 Advance Data Center Lic for NC55-36X100G-A-SE & NCS-55A1-36H-SE-S |
| | NC55P-MSEC-36HS | NCS 5500 MACsec Lic for NC55-36X100G-A-SE & NCS-55A1-36H-SE-S |
| | NC55P-TIMING-F | NCS 5500 Timing and Mobility Lic for Fixed Chassis **Supported 7.0.1 and beyond |

| Category | Part Number | Description |
|--------------|------------------|--|
| NCS-55A1-24H | NC55P-ADVL3-24HT | NCS 5500 L3VPN Lic for NCS-55A1-24H |
| | NC55P-ADVL2-24HT | NCS 5500 L2VPN Lic for NCS-55A1-24H |
| | NC55P-CRAGR-24HT | NCS 5500 Core and Aggregation Lic for NCS-55A1-24H |
| | NC55P-PEER-24HT | NCS 5500 Peering Lic for NCS-55A1-24H |
| | NC55P-ADVDC-24HT | NCS 5500 Advance Data Center Lic for NCS-55A1-24H |
| | NC55P-TIMING-F | NCS 5500 Timing and Mobility Lic for Fixed Chassis **Supported 6.5.2 and beyond |

Table 12. Ordering information - Flexible Consumption Model Software Licenses

| Part number | Product description |
|----------------|--|
| ESS-100G-RTU-1 | NCS 5500 Core & Aggregation Essentials SW RTU v1.0 100G |
| ADV-100G-RTU-1 | NCS 5500 Core & Aggregation Advantage w/o Essentials SW RTU v1.0 100G |
| ADN-100G-RTU-1 | NCS 5500 Core & Aggregation Advantage w/ Essentials SW RTU v1.0 100G |
| ESS-100G-SIA-3 | NCS 5500 Core & Aggregation Essentials SIA per 100G 3-5 Year Subscription |
| ADV-100G-SIA-3 | NCS 5500 Core & Aggregation Advantage w/o Essentials SIA per 100G 3-5 Year Subscription |
| ADN-100G-SIA-3 | NCS 5500 Core & Aggregation Advantage w/ Essentials SIA per 100G 3-5 Year Subscription |
| ESS-100G-SIA-5 | NCS 5500 Core & Aggregation Essentials SIA per 100G 5-10 Year Subscription |
| ADV-100G-SIA-5 | NCS 5500 Core & Aggregation Advantage w/o Essentials SIA per 100G 5-10 Year Subscription |
| ADN-100G-SIA-5 | NCS 5500 Core & Aggregation Advantage w/ Essentials SIA per 100G 5-10 Year Subscription |

For details on the Cisco Network Convergence System 5500 Series Perpetual Software Licenses, refer to this [data sheet](#) and details on the flexible consumption model for the NCS 5500 Series are available in the [data sheet](#) for the IOS XR Software flexible consumption model.

Warranty

The Cisco NCS 5500 Series has a 1-year limited hardware warranty. The warranty includes hardware replacement with a 10-day turnaround from receipt of a Return Materials Authorization (RMA).

Cisco environmental sustainability

Information about Cisco's environmental sustainability policies and initiatives for our products, solutions, operations, and extended operations or supply chain is provided in the "Environment Sustainability" section of Cisco's [Corporate Social Responsibility](#) (CSR) Report.

Reference links to information about key environmental sustainability topics (mentioned in the “Environment Sustainability” section of the CSR Report) are provided in the following table:

| Sustainability topic | Reference |
|--|---------------------------------|
| Information on product material content laws and regulations | Materials |
| Information on electronic waste laws and regulations, including products, batteries, and packaging | WEEE compliance |

Cisco makes the packaging data available for informational purposes only. It may not reflect the most current legal developments, and Cisco does not represent, warrant, or guarantee that it is complete, accurate, or up to date. This information is subject to change without notice.

Service and Support

Cisco offers a wide range of services to help accelerate your success in deploying and optimizing the Cisco NCS 5500 Series. These innovative Cisco Services offerings are delivered through a unique combination of people, processes, tools, and partners, and they are focused on helping you increase operating efficiency and improve your data center network. Cisco Advanced Services uses an architecture-led approach to help you align your data center infrastructure with your business goals and achieve long-term value. Cisco SMARTnet™ Service helps you resolve mission-critical problems with direct access at any time to Cisco network experts and award-winning resources. With this service, you can take advantage of the Cisco Smart Call Home service, which offers proactive diagnostics and real-time alerts on your Cisco NCS 5500 Series. Spanning the entire network lifecycle, Cisco Services offerings help increase investment protection, optimize network operations, support migration operations, and strengthen your IT expertise.

Cisco Capital

Flexible payment solutions to help you achieve your objectives

Cisco Capital makes it easier to get the right technology to achieve your objectives, enable business transformation and help you stay competitive. We can help you reduce the total cost of ownership, conserve capital, and accelerate growth. In more than 100 countries, our flexible payment solutions can help you acquire hardware, software, services and complementary third-party equipment in easy, predictable payments. [Learn more.](#)

For more information

For more information about the Cisco NCS 5500 Series, visit [Cisco Network Convergence System 5500 Series.](#)

Americas Headquarters
Cisco Systems, Inc.
San Jose, CA

Asia Pacific Headquarters
Cisco Systems (USA) Pte. Ltd.
Singapore

Europe Headquarters
Cisco Systems International BV Amsterdam,
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at <https://www.cisco.com/go/offices>.

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: <https://www.cisco.com/go/trademarks>. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)