

Cisco Firepower 2100 Series

Cisco Secure Firewall

Cisco Secure IPS

Contents

Cisco Firepower 2100 Series appliances	3
Model overview	3
Detailed performance specifications and feature highlights	4
Hardware specifications	6
Cisco Capital	9
Document history	10

Cisco Firepower 2100 Series appliances

The Cisco Firepower 2100 Series is a family of four threat-focused security platforms that deliver business resiliency and superior threat defense. They offers exceptional sustained performance when advanced threat functions are enabled. These platforms uniquely incorporate an innovative dual multicore CPU architecture that optimizes firewall, cryptographic, and threat inspection functions. The series' firewall throughput range addresses use cases from the Internet edge to the data center. Network Equipment Building Standards (NEBS)-compliance is supported by the Cisco Firepower 2130 platform. 2100 Series platforms run either the Cisco Secure Firewall ASA or Threat Defense (FMC) software. They can be deployed in both firewall and dedicated IPS modes.

Model overview

Cisco Firepower 2110/2120 Model



Cisco Firepower 2130/2140 Model



Cisco Firepower 2100 series summary:

Model	Firewall	NGFW	IPS Throughput	Interfaces	Optional interfaces
FPR-2110	3G	2.6G	2.6G	12 x RJ45, 4 x SFP	N/A
FPR-2120	6G	3.4G	3.5G	12 x RJ45, 4 x SFP	N/A
FPR-2130	10G	5.4G	5.4G	12 x RJ45, 4 x SFP+	10G SFP+, 1/10G FTW
FPR-2140	20G	10.4G	10.5G	12 x RJ45, 4 x SFP+	10G SFP+, 1/10G FTW

Detailed performance specifications and feature highlights

Table 1. Performance specifications and feature highlights for 2100 Series with Cisco Threat Defense software

Features	2110	2120	2130	2140
Throughput: FW + AVC (1024B)	2.6 Gbps	3.4 Gbps	5.4 Gbps	10.4 Gbps
Throughput: FW + AVC + IPS (1024B)	2.6 Gbps	3.4 Gbps	5.4 Gbps	10.4 Gbps
Maximum concurrent sessions, with AVC	1 million	1.5 million	2 million	3 million
Maximum new connections per second, with AVC	14K	18K	30K	57K
TLS	365 Mbps	475 Mbps	760 Mbps	1.4 Gbps
Throughput: IPS (1024B)	2.6 Gbps	3.5 Gbps	5.4 Gbps	10.5 Gbps
IPSec VPN Throughput (1024B TCP w/Fastpath)	950 Mbps	1.2 Gbps	1.9 Gbps	3.6 Gbps
Maximum VPN Peers	1,500	3,500	7,500	10,000
Cisco Firepower Device Manager (local management)	Yes	Yes	Yes	Yes
Centralized management	Centralized configuration, logging, monitoring, and reporting are performed by the Management Center or alternatively in the cloud with Cisco Defense Orchestrator			
Application Visibility and Control (AVC)	Standard, supporting more than 4000 applications, as well as geolocations, users, and websites			
AVC: OpenAppID support for custom, open source, application detectors	Standard			
Cisco Security Intelligence	Standard, with IP, URL, and DNS threat intelligence			
Cisco Firepower NGIPS	Available; can passively detect endpoints and infrastructure for threat correlation and Indicators of Compromise (IoC) intelligence			
Cisco AMP for Networks	Available; enables detection, blocking, tracking, analysis, and containment of targeted and persistent malware, addressing the attack continuum both during and after attacks. Integrated threat correlation with Cisco Secure Endpoint is also optionally available			
Cisco AMP Threat Grid sandboxing	Available			
URL Filtering: number of categories	More than 80			
URL Filtering: number of URLs categorized	More than 280 million			

Features	2110	2120	2130	2140
Automated threat feed and IPS signature updates	Yes: class-leading Collective Security Intelligence (CSI) from the Cisco Talos Group (https://www.cisco.com/c/en/us/products/security/talos.html)			
Third-party and open-source ecosystem	Open API for integrations with third-party products; Snort® and OpenAppID community resources for new and specific threats			
High availability and clustering	Active/standby			
Cisco Trust Anchor Technologies	Firepower 2100 Series platforms include Trust Anchor Technologies for supply chain and software image assurance. Please see the section below for additional details			

Note: Performance will vary depending on features activated, and network traffic protocol mix, and packet size characteristics. Performance is subject to change with new software releases. Consult your Cisco representative for detailed sizing guidance.

Table 2. ASA Performance and capabilities on Firepower 2100 appliances

Features	2110	2120	2130	2140
Stateful inspection firewall throughput¹	3 Gbps	6 Gbps	10 Gbps	20 Gbps
Stateful inspection firewall throughput (multiprotocol)²	1.5 Gbps	3 Gbps	5 Gbps	10 Gbps
Concurrent firewall connections	1 million	1.5 million	2 million	3 million
Firewall latency (UDP 64B microseconds)	-	-	-	-
New connections per second	18,000	28,000	40,000	75,000
IPsec VPN throughput (450B UDP L2L test)	500 Mbps	700 Mbps	1 Gbps	2 Gbps
Maximum VPN Peers	1,500	3,500	7,500	10,000
Security contexts (included; maximum)	2; 25	2; 25	2; 30	2; 40
High availability	Active/active and active/standby	Active/active and active/standby	Active/active and active/standby	Active/active and active/standby
Clustering				
Scalability	VPN Load Balancing			

Features	2110	2120	2130	2140
Centralized management	Centralized configuration, logging, monitoring, and reporting are performed by Cisco Security Manager or alternatively in the cloud with Cisco Defense Orchestrator			
Adaptive Security Device Manager	Web-based, local management for small-scale deployments			

¹ Throughput measured with 1500B User Datagram Protocol (UDP) traffic measured under ideal test conditions.

² “Multiprotocol” refers to a traffic profile consisting primarily of TCP-based protocols and applications like HTTP, SMTP, FTP, IMAPv4, BitTorrent, and DNS.

³ In unclustered configuration.

Performance testing methodologies [LINK](#)

Hardware specifications

Table 3. Cisco Firepower 2100 Series hardware specifications

Features	Cisco Firepower Model			
	2110	2120	2130	2140
Dimensions (H x W x D)	1.73 x 16.90 x 19.76 in. (4.4 x 42.9 x 50.2cm)	1.73 x 16.90 x 19.76 in. (4.4 x 42.9 x 50.2 cm)	1.73 x 16.90 x 19.76 in. (4.4 x 42.9 x 50.2 cm)	1.73 x 16.90 x 19.76 in. (4.4 x 42.9 x 50.2 cm)
Form factor (rack units)	1RU	1RU	1RU	1RU
Integrated I/O	12 x 10M/100M/ 1GBASE-T Ethernet interfaces (RJ- 45), 4 x 1 Gigabit (SFP) Ethernet interfaces	12 x 10M/100M/ 1GBASE-T Ethernet interfaces (RJ- 45), 4 x 1 Gigabit (SFP) Ethernet interfaces	12 x 10M/100M/ 1GBASE-T Ethernet interfaces (RJ- 45), 4 x 10 Gigabit (SFP+) Ethernet interfaces	12 x 10M/100M/ 1GBASE-T Ethernet interfaces (RJ- 45), 4 x 10 Gigabit (SFP+) Ethernet interfaces
Network modules	None	None	10G SFP+, 1/10G FTW Options	10G SFP+, 1/10G FTW Options
Note: The 2100 Series appliances may also be deployed as dedicated threat sensors with fail-to-wire network modules. Please contact your Cisco representative for details.				
Maximum number of interfaces	Up to 16 total Ethernet ports, (12x1G RJ-45, 4x1G SFP)	Up to 16 total Ethernet ports, (12x1G RJ-45, 4x1G SFP)	Up to 24 total Ethernet ports (12x1G RJ-45, 4x10G SFP+, and network module)	Up to 24 total Ethernet ports (12x1G RJ-45, 4x10G SFP+, and network module)
Integrated network management ports	1 x 10M/100M/ 1GBASE-T Ethernet port (RJ-45)	1 x 10M/100M/ 1GBASE-T Ethernet port (RJ-45)	1 x 10M/100M/ 1GBASE-T Ethernet port (RJ-45)	1 x 10M/100M/ 1GBASE-T Ethernet port (RJ-45)

Features	Cisco Firepower Model			
Serial port	1 x RJ-45 console	1 x RJ-45 console	1 x RJ-45 console	1 x RJ-45 console
USB	1 x USB 2.0 Type-A (500mA)	1 x USB 2.0 Type-A (500mA)	1 x USB 2.0 Type-A (500mA)	1 x USB 2.0 Type-A (500mA)
Storage	1x 100 GB, 1x spare slot (for MSP)	1x 100 GB, 1x spare slot (for MSP)	1x 200 GB, 1x spare slot (for MSP)	1x 200 GB, 1x spare slot (for MSP)
Power supply configuration	Single integrated 250W AC power supply.	Single integrated 250W AC power supply.	Single 400W AC, Dual 400W AC optional. Single/Dual 350W DC optional1	Dual 400W AC. Single/dual 350W DC optional1
AC input voltage	100 to 240V AC	100 to 240V AC	100 to 240V AC	100 to 240V AC
AC maximum input current	< 2.7A at 100V	< 2.7A at 100V	< 6A at 100V	< 6A at 100V
AC maximum output power	250W	250W	400W	400W
AC frequency	50 to 60 Hz	50 to 60 Hz	50 to 60 Hz	50 to 60 Hz
AC efficiency	>88% at 50% load	>88% at 50% load	>89% at 50% load	>89% at 50% load
DC input voltage	-	-	-48V to -60VDC	-48V to -60VDC
DC maximum input current	-	-	< 12.5A at -48V	< 12.5A at -48V
DC maximum output power	-	-	350W	350W
DC efficiency			>88% at 50% load	>88% at 50% load
Redundancy	None	None	1+1 AC or DC with dual supplies	1+1 AC or DC with dual supplies
Fans	4 integrated (2 internal, 2 exhaust) fans2	4 integrated (2 internal, 2 exhaust) fans2	1 hot-swappable fan module (with 4 fans)2	1 hot-swappable fan module (with 4 fans)2
Noise	56 dBA @ 25C 74 dBA at highest system performance.	56 dBA @ 25C 74 dBA at highest system performance.	56 dBA @ 25C 77 dBA at highest system performance.	56 dBA @ 25C 77 dBA at highest system performance.

Features	Cisco Firepower Model			
Rack mountable	Yes. Fixed mount brackets included. (2-post). Mount rails optional (4-post EIA-310-D rack)	Yes. Fixed mount brackets included. (2-post). Mount rails optional (4-post EIA-310-D rack)	Yes. Mount rails included (4-post EIA-310-D rack)	Yes. Mount rails included (4-post EIA-310-D rack)
Weight	16.1 lb (7.3 kg): with 2x SSDs	16.1 lb (7.3 kg): with 2x SSDs	19.4 lb (8.8 kg) 1 x power supplies, 1 x NM, 1 x fan module, 2x SSDs	21 lb (9.53 kg) 2 x power supplies, 1 x NM, 1 x fan module, 2x SSDs
Temperature: operating	32 to 104°F (0 to 40°C)	32 to 104°F (0 to 40°C)	32 to 104°F (0 to 40°C) or NEBS operation (see below) ³	32 to 104°F (0 to 40°C)
Temperature: nonoperating	-4 to 149°F (-20 to 65°C)	-4 to 149°F (-20 to 65°C)	-4 to 149°F (-20 to 65°C)	-4 to 149°F (-20 to 65°C)
Humidity: operating	10 to 85% noncondensing	10 to 85% noncondensing	10 to 85% noncondensing	10 to 85% noncondensing
Humidity: nonoperating	5 to 95% noncondensing	5 to 95% noncondensing	5 to 95% noncondensing	5 to 95% noncondensing
Altitude: operating	10,000 ft (max)	10,000 ft (max)	10,000 ft (max) or NEBS operation (see below) ³	10,000 ft (max)
Altitude: nonoperating	40,000 ft (max)	40,000 ft (max)	40,000 ft (max)	40,000 ft (max)
NEBS operation (FPR-2130 Only)³			Operating altitude: 0 to 13,000 ft (3962 m) Operating temperature: Long term: 0 to 45°C, up to 6,000 ft (1829 m) Long term: 0 to 35°C, 6,000 to 13,000 ft (1829 to 3964 m) Short term: -5 to 55°C, up to 6,000 ft (1829 m)	

¹ Dual power supplies are hot-swappable.

² Fans operate in a 3+1 redundant configuration where the system will continue to function with only 3 operational fans. The 3 remaining fans will run at full speed.

³ FPR-2130 platform is designed to be NEBS ready. The availability of NEBS certification is pending.

Table 4. Cisco Firepower 2100 Series NEBS, Regulatory, Safety, and EMC Compliance

Specification	Description
Regulatory compliance	Products comply with CE markings per directives 2004/108/EC and 2006/108/EC
Safety	<ul style="list-style-type: none"> • UL 60950-1 • CAN/CSA-C22.2 No. 60950-1 • EN 60950-1 • IEC 60950-1 • AS/NZS 60950-1 • GB4943
EMC: emissions	<ul style="list-style-type: none"> • 47CFR Part 15 (CFR 47) Class A (FCC Class A) • AS/NZS CISPR22 Class A • CISPR22 CLASS A • EN55022 Class A • ICES003 Class A • VCCI Class A • EN61000-3-2 • EN61000-3-3 • KN22 Class A • CNS13438 Class A • EN300386 • TCVN7189
EMC: Immunity	<ul style="list-style-type: none"> • EN55024 • CISPR24 • EN300386 • KN24 • TVCN 7317 • EN-61000-4-2, EN-61000-4-3, EN-61000-4-4, EN-61000-4-5, EN-61000-4-6, EN-61000-4-8, EN61000-4-11

Cisco Capital

Flexible payment solutions to help you achieve your objectives

Cisco Capital® makes it easier to get the right technology to achieve your objectives, enable business transformation and help you stay competitive. We can help you reduce the total cost of ownership, conserve capital, and accelerate growth. In more than 100 countries, our flexible payment solutions can help you acquire hardware, software, services and complementary third-party equipment in easy, predictable payments.

[Learn more.](#)

Document history

New or Revised Topic	Described In	Date
Product Performance numbers updated	Series Summary Table and Table 1	July 14, 2021

Americas Headquarters
Cisco Systems, Inc.
San Jose, CA

Asia Pacific Headquarters
Cisco Systems (USA) Pte. Ltd.
Singapore

Europe Headquarters
Cisco Systems International BV Amsterdam,
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at <https://www.cisco.com/go/offices>.

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: <https://www.cisco.com/go/trademarks>. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)