



Hewlett Packard
Enterprise

HPE 36U 600MMX1075MM G2 KITTED ADVANCED PALLET RACK WITH SIDE PANELS AND BAYING (P9K05A)

Server Racks



WHAT'S NEW

- HPE G2 Advanced Series Racks are covered by a 10-year limited warranty.

OVERVIEW

Are you looking for a rack to fit your compute requirements that is designed to perform at a reasonable price? Take the guesswork out of infrastructure with HPE purpose-built racks.

-
- Front and rear doors support a variety of electronic and biometric locking solutions for improved physical security.
 - Flush-mounted side panels allow racks to be securely bayed together.
 - Single-key access to front, rear and sides provides a solution for all rack access points that's as convenient as it is secure.
 - Improved cable management provisions simplify installation, organization and maintenance.

Perfect for the server room or today's modern data center, HPE G2 Advanced Series Racks include a 3000 pound static capacity, design for better air flow, and cable management features. The welded frame is designed for durability and includes a door with greater perforation for better airflow. Designed for scalability, performance and ease of maintenance, G2 Advanced Series Racks include a rear bracket which eases installation and management of cable and power distribution. For those that require greater load capacity, HPE G2 Advanced Series Racks can be fully configured and shipped to your site. The HPE Rack family of products is optimized for your Infrastructure requirements now and in the future.

FEATURES

The Stronger the Rack, the Longer it Lasts

HPE G2 Advanced Series Racks are covered by a global 10-year limited warranty.

Heavy-gauge mounting rails support up to 3000 pounds (static load) and 2250 pounds (dynamic load), keeping a fully loaded rack safe in the truck and in the datacenter.

Fully-tested ship load allows racks to be shipped fully configured, reducing time to deployment.

Universal rack design compatible with all Hewlett Packard Enterprise rack mount products including servers, networking, and storage.

Full line of options and accessories to create the rack that supports your compute solution needs.

Our Racks Have Evolved to Stay a Step Ahead of Would-be Threats to your Servers

HPE G2 Advanced Series Racks front and rear doors support a variety of electronic and biometric locking solutions for improved physical security.

Flush-mounted side panels allow racks to be securely bayed together.

Single-key access to front, rear and sides provides a solution for all rack access points that's as convenient as it is secure.

Our Racks Give you More for Less, Keeping your Servers Working Hard and you Working Easy

HPE G2 Advanced Series Racks provide the industry's widest range of rack enclosures that supports a broad variety of workloads and configurations.

Improved cable management provisions simplify installation, organization and maintenance.



Hewlett Packard Enterprise Foundation Care services purchased for servers and storage extend to our rack and power infrastructure products. What is the HPE advantage for you? Save \$\$\$.

An extensive range of rack, power, and KVM products to outfit your rack.

Technical specifications

HPE 36U 600mmx1075mm G2 Kitted Advanced Pallet Rack with Side Panels and Baying

Product Number	P9K05A
Rack capacity	36U
Total cabinet area	23.5 x 42.72 x 68.66 in (59.78 x 108.52 x 174.39 cm)
Static load	3000 lb (1360.77 kg)
Dynamic load	2500 lb (1133.98 kg)
Door color	Black with industry standard flush locking handle
Frame color	Black
Rack height	36U
Rack depth	1075mm
Rack width	600mm
Product Dimensions (metric)	71.00 x 120.00 x 213.80 cm
Weight	129.50kg
Warranty	HPE G2 Advanced Series Racks are covered by a 10-year limited warranty. Additional information regarding worldwide limited warranty and technical support is available at: http://h17007.www1.hpe.com/us/en/enterprise/servers/warranty/index.aspx#.V-10xE3rvbq



For additional technical information, available models and options, please reference the [QuickSpecs](#)

HPE POINTNEXT SERVICES

[HPE Pointnext Services](#) brings together technology and expertise to help you drive your business forward and prepare for whatever is next.

Operational Services from HPE Pointnext Services

[HPE Pointnext Tech Care](#) provides fast access to product-specific experts, an AI-driven digital experience, and general technical guidance to help enable constant innovation. We have reimagined IT support from the ground up to deliver faster answers and greater value. By continuously searching for better ways to do things—as opposed to just fixing things that break—HPE Pointnext Tech Care helps you focus on achieving your business goals.

[HPE Pointnext Complete Care](#) is a modular, edge-to-cloud IT environment service that provides a holistic approach to optimizing your entire IT environment, and achieving agreed upon IT outcomes and business goals through a personalized and customer-centric experience. All delivered by an assigned team of HPE Pointnext Services experts.

HPE Integration and Performance Services help you customize your experience at any stage of your product lifecycle with a menu of services based on individual needs, workloads, and technologies.

- Advise, design, and transform
- Deploy
- Integrate and migrate
- Operate and improve
- Financial Services
- Greenlake Management Services
- Retire and sanitize
- IT Training and personal development

Other related services

[HPE Education Services](#) delivers a comprehensive range of services to support your people as they expand their skills required for a digital transformation. Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and support options.

Defective Media Retention is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

HPE GREENLAKE

[HPE Greenlake](#) is HPE's market-leading IT as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model. HPE GreenLake delivers public cloud services and infrastructure for workloads on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

Make the right purchase decision.
Contact our presales specialists.



Chat now (sales)



Call now



Buy now



Share now



Get updates

**Hewlett Packard
Enterprise**

© Copyright 2022 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Image may differ from the actual product
[PSN1009701868USEN](#), August, 2022.