



## FAMILY DATASHEET

# Meraki MS Series Switches

## Overview

Cisco Meraki offers a broad range of switches built from the ground up that are designed to be easy to manage without compromising any of the power and flexibility traditionally found in enterprise-class switches.

Meraki access and aggregation switches are all managed through an elegant, intuitive cloud interface, freeing administrators to spend less time on configuration and more time on meeting business needs.

To set up a Meraki switch, just plug it in; there's no need for repetitive, command-based configuration. Switches can be up and running within minutes of connecting them to the network.

A powerful centralized management interface gives administrators deep visibility into the network and how it is used. See which switches are near capacity across hundreds of sites. Quickly provision and reconfigure switch ports with security, quality of service (QoS), and more. The Meraki dashboard provides unified policies, event logs, and monitoring, making switch management efficient and scalable.

## Product highlights


- Range of enterprise switching options built on proven Cisco hardware technologies
- Basic layer 2 to high-performance layer 3 switches with up to 40 GbE uplinks on access and up to 100 GbE on aggregation switches, suitable for deployments of all sizes
- True zero-touch configuration model that scales with organization needs and requirements
- Integrated troubleshooting tools, logging, and alerting help reduce operational costs
- Energy-efficient design with low acoustics and fanless options
- Flexible stacking for scaled configuration and high performance in one
- Cloud management reduces cost, overhead, and time to resolution
- Industry-standard features allow for simple integration into existing and mixed infrastructures
- Role-based administration and automatic, secure firmware updates delivered via the web
- StackPower, improved physical stacking, and multigigabit options on select models

## Inside the Meraki MS350

Energy-efficient dual-power supplies with variable speed fans

Stacking connectors

High reliability/MTBF extended-life components



48× 1 GbE ports with 802.3af/802.3at PoE/PoE+

Enhanced CPU/memory Meraki cloud management

4× 10 GbE SFP+ uplink ports built in for uplink connectivity

### Enterprise-class hardware

Meraki switches feature high-end hardware and an exceptional feature set, including:

- Options for fixed and modular uplinks: 1 GbE, 10 GbE, and 40 GbE uplink ports for high-speed connectivity to aggregation-layer switches or other upstream devices
- Optional multigigabit ports providing up to 10 Gbps on a single cable, supporting the latest Wi-Fi performance capabilities
- Wire-speed, non-blocking switch fabric (up to 800 Gbps) and six dedicated QoS queues for high-performance, converged voice, video, and data deployments
- Power-efficient, quiet acoustic designs and shallow rack-depth options enable flexible deployment in wiring closets as well as offices and classrooms
- Fanless design on select models
- PoE, PoE+, and UPoE options available
- Up to 740 W PoE budget with PoE+ support for powering APs, phones, cameras, and other PoE-enabled devices (124 W for 120-8 series), with 830 W available on the MS390 UPoE model
- Lifetime hardware warranty and advanced replacement at no additional cost
- Field-replaceable, hot-swappable power supplies and fans; redundant power supply (RPS) options for mission-critical applications; StackPower on select models for added resilience

## Powerful feature set for deployments of all types

Meraki switches include all of the traditional Ethernet features found on the highest-end products, including:

- QoS to prioritize mission-critical traffic such as voice and video
- IEEE 802.1x support for port-based network access control
- MAC-based RADIUS auth and MAC allowlisting
- Voice VLAN support for simplified voice over internet protocol (VoIP) deployments
- Port mirroring support for monitoring network traffic at line rate
- Dynamic host configuration protocol (DHCP) snooping to prevent users from adding unauthorized DHCP servers on the network
- Internet group management protocol (IGMP) snooping to optimize network performance with multicast traffic
- Link aggregation control protocol (LACP) for high-capacity trunking, stacking, and increased availability
- Rapid spanning tree protocol (RSTP), bridge protocol data unit (BDPU) guard, root guard, and other safeguards to help prevent misconfigurations and reduce convergence time
- Per-port VLAN configuration
- Multiple administrative roles with sophisticated security policy management
- High-performance layer 3 routing capabilities on select models

## Access switching portfolio




|                              | MS120-8   | MS120  | MS125   |
|------------------------------|---|--|---|
|                              |  |  |  |
| <b>Usage</b>                 | Compact   | Branch and campus  | Branch and office   |
| <b>Interface</b>             | 8× 1 GbE RJ45   | 24/48× 1 GbE RJ45  | 24/48× 1 GbE RJ45   |
| <b>Uplinks</b>               | 2× 1 GbE SFP<br>Fixed   | 4× 1 GbE SFP<br>Fixed  | 4× 10 GbE SFP<br>Fixed  |
| <b>PoE capabilities</b>      | 67 W (LP model)<br>124 W (FP model)   | 370 W (P, LP models)<br>740 W (FP model)   | 370 W (P, LP models)<br>740 W (FP model)  |
| <b>Power configuration</b>   | External PSU (non-PoE, LP model)<br>Internal (FP model)                           | Internal   | Internal  |
| <b>Stacking capabilities</b> | Virtual only  | Virtual only   | Virtual only  |
| <b>Routing capabilities</b>  | DHCP relay  | DHCP relay   | DHCP relay  |
| <b>Models</b>                | MS120-8-HW<br>MS120-8LP-HW<br>MS120-8FP-HW  | MS120-24-HW<br>MS120-24P-HW<br>MS120-48-HW<br>MS120-48LP-HW<br>MS120-48FP-HW       | MS125-24-HW<br>MS125-24P-HW<br>MS125-48-HW<br>MS125-48LP-HW<br>MS125-48FP-HW        |

## Access switching portfolio

|                              | MS130 compact  | MS130  |
|------------------------------|--|--|
|                              |   |    |
| <b>Usage</b>                 | Compact  | Branch and campus  |
| <b>Interface</b>             | 8/12× 1 GbE RJ45<br><br>6/8× 1 GbE + 2/4× 2.5 GbE RJ45<br>(in select models)   | 24/48× 1 GbE RJ45<br><br>18/40× 1 GbE + 6/8× 2.5 GbE RJ45<br>(in select models)  |
| <b>Uplinks</b>               | 2× 1 GbE SFP<br><br>2× 10 GbE SFP+ (in select models)<br><br>Fixed   | 4× 1 GbE SFP<br><br>4× 10 GbE SFP+ (in select models)<br><br>Fixed   |
| <b>PoE capabilities</b>      | 120 W<br><br>240 W (MS130-12X only)  | 370 W<br><br>740 W (MS130-48P/X only)  |
| <b>Power configuration</b>   | External   | Internal   |
| <b>Stacking capabilities</b> | Virtual only   | Virtual only   |
| <b>Routing capabilities</b>  | DHCP relay   | DHCP relay   |
| <b>Models</b>                | MS130-8-HW<br>MS130-8P-HW<br>MS130-8X-HW<br>(mGig, 10 GbE SFP + option) <sup>1</sup><br>MS130-12X-HW<br>(mGig, 10 GbE SFP + option) <sup>1</sup> | MS130-24-HW<br>MS130-24P-HW<br>MS130-24X-HW<br>(mGig, 10 GbE SFP + option) <sup>1</sup><br>MS130-48-HW<br>MS130-48P-HW<br>MS130-48X-HW<br>(mGig, 10 GbE SFP + option) <sup>1</sup> |



<sup>1</sup> MS130 mGig (-X) models are hardware-ready for Adaptive Policy with a future firmware upgrade and advanced license.

## Stackable access switching portfolio

|                              | MS210   | MS225  | MS250   |
|------------------------------|---|--|---|
|                              |  |  |  |
| <b>Usage</b>                 | Branch and campus   | Branch and campus  | Branch and campus   |
| <b>Interface</b>             | 24/48× 1 GbE RJ45   | 24/48× 1 GbE RJ45  | 24/48× 1 GbE RJ45   |
| <b>Uplinks</b>               | 4× 1 GbE SFP<br>Fixed   | 4× 10 GbE SFP+<br>Fixed  | 4× 10 GbE SFP+<br>Fixed   |
| <b>PoE capabilities</b>      | 370 W (P, LP models)<br>740 W (FP models)   | 370 W (P, LP models)<br>740 W (FP models)  | 370 W (P, LP models)<br>740 W (FP models)   |
| <b>Power configuration</b>   | Internal<br>Optional RPS  | Internal<br>Optional RPS   | Modular<br>Redundant PSU optional   |
| <b>Stacking capabilities</b> | Compatible with MS225<br>80G physical + virtual                                   | Compatible with MS210<br>80G physical + virtual                                    | 80G physical + virtual  |
| <b>Routing capabilities</b>  | Static only<br>DHCP relay   | Static only<br>DHCP relay  | Static + dynamic <sup>1</sup><br>DHCP server + relay<br>Warm spare (VRRP)           |
| <b>Models</b>                | MS210-24-HW<br>MS210-24P-HW<br>MS210-48-HW<br>MS210-48LP-HW<br>MS210-48FP-HW      | MS225-24-HW<br>MS225-24P-HW<br>MS225-48-HW<br>MS225-48LP-HW<br>MS225-48FP-HW       | MS250-24-HW<br>MS250-24P-HW<br>MS250-48-HW<br>MS250-48LP-HW<br>MS250-48FP-HW        |

<sup>1</sup> Detailed routing specifications are available in series datasheets

## Stackable access switching portfolio



|                              | MS350  | MS355  | MS390  |
|------------------------------|--|--|--|
|                              |             |  |   |
| <b>Usage</b>                 | Campus and multigigabit  | Branch and campus  | High-performance campus and branch   |
| <b>Interface</b>             | 24/48× 1 GbE RJ45 <sup>1</sup><br>8× mGig RJ45 (24 port only)                                | 24/48× 1 GbE RJ45<br>8× mGig RJ45 (24 port only)                                   | 24/48× 1 GbE RJ45<br>24/48× mGig RJ45 (in select models)   |
| <b>Uplinks</b>               | 4× 10 GbE SFP+<br>Fixed  | 2× 40G QSFP+<br>Fixed  | 4/8× 10 GbE SFP+<br>2× 40 GbE QSFP+<br>Modular   |
| <b>PoE capabilities</b>      | 370 W (P, LP models)<br>740 W (24 port, FP models)   | 740 W (24 port, X2 models)<br>740 W (48 port, X2 models)                           | 830 W (24 port models)<br>822 W (48 port models)   |
| <b>Power configuration</b>   | Modular<br>Redundant PSU optional  | Removable PSU  | Removable PSU<br>Modular 80 PLUS Platinum PSU  |
| <b>Stacking capabilities</b> | 160G physical + virtual  | 400G physical +virtual   | Compatible only with MS390<br>480G physical +virtual   |
| <b>Routing capabilities</b>  | Static + dynamic <sup>2</sup><br>DHCP server + relay<br>Warm spare (VRRP)                    | Static + dynamic<br>DHCP server + relay  | Static + dynamic<br>DHCP server + relay  |
| <b>Models</b>                | MS350-24-HW<br>MS350-24P-HW<br>MS350-24X-HW<br>MS350-48-HW<br>MS350-48LP-HW<br>MS350-48FP-HW | MS355-24X-HW<br>MS355-24X2-HW<br>MS355-48X-HW<br>MS355-48X2-HW                     | MS390-24-HW<br>MS390-24P-HW<br>MS390-24U-HW<br>MS390-24UX-HW<br>MS390-48-HW<br>MS390-48P-HW<br>MS390-48U-HW<br>MS390-48UX-HW<br>MS390-48UX2-HW |

<sup>1</sup> Interfaces do not support half-duplex on the MS350




<sup>2</sup> Detailed routing specifications are available in series datasheets



## Stackable access switching portfolio

|                              | Catalyst Meraki C9300 (Gigabit)  | Catalyst Meraki C9300 (mGig)  |
|------------------------------|--|---|
|                              |       |                  |
| <b>Usage</b>                 | High-performance campus  |   |
| <b>Interface</b>             | 24/48× 1 GbE RJ45  | C9300 24 UX: 24× 10G mGig<br>C9300 48 UXM: 36× 2.5 mGig and 12× 10G mGig<br>C9300 48UN: 48× 5G mGig |
| <b>Uplinks</b>               | 4× 10G/1G SFP<br>8× 1/10G SFP/SFP+<br>2× 100G/40G SFP/SFP+<br>2× 40G QSFP              |   |
| <b>PoE capabilities</b>      | Data only option<br>30 W PoE+ option<br>60 W UPoE option                               | 60 W UPoE option  |
| <b>Power configuration</b>   | Removable PSU<br>Modular 80 PLUS® Platinum PSU   |   |
| <b>Stacking capabilities</b> | 480G physical + virtual  |   |
| <b>Routing capabilities</b>  | Static + dynamic DHCP server + relay   |   |
| <b>Models</b>                | C9300-24T-M<br>C9300-24P-M<br>C9300-24U-M<br>C9300-48T-M<br>C9300-48P-M<br>C9300-48U-M | C9300-24UX-M<br>C9300-48UXM-M<br>C9300-48UN-M   |

## Aggregation switching portfolio

|                              | MS410   | MS425  | MS450   |
|------------------------------|---|--|---|
|                              |  |  |  |
| <b>Usage</b>                 | 1G fiber aggregation  | 10G fiber aggregation  | 40G fiber aggregation   |
| <b>Interface</b>             | 16/32× GbE SFP  | 16/32× 10 GbE SFP+   | 12× 40 GbE QSFP+  |
| <b>Uplinks</b>               | 2× 10 GbE SFP+ (MS410-16)<br>4× 10 GbE SFP+ (MS410-32)                            | 2× 40 GbE QSFP+  | 2× 100 GbE QSFP28   |
| <b>Power configuration</b>   | Modular<br>Redundant PSU optional<br>(sold separately)                            | Modular<br>Redundant PSU optional<br>(sold separately)                             | Modular<br>Redundant PSU optional<br>(sold separately)                              |
| <b>Stacking capabilities</b> | 160G physical + virtual   | 160G physical + virtual  | 2x dedicated stack ports<br>for up to 400G + virtual                                |
| <b>Routing capabilities</b>  | Static + dynamic<br>DHCP server + relay<br>Warm spare (VRRP)                      | Static + dynamic<br>DHCP server + relay<br>Warm spare (VRRP)                       | Static + dynamic<br>DHCP server + relay<br>Warm spare (VRRP)                        |
| <b>Models</b>                | MS410-16-HW<br>MS410-32-HW  | MS425-16-HW<br>MS425-32-HW   | MS450-12-HW   |

## Lifetime warranty with next-day advance replacement

All Cisco Meraki MS switches include a limited lifetime hardware warranty that provides next-day advance hardware replacement. The Meraki simplified software and support licensing model also combines software upgrades, centralized systems management, and phone support under a single, easy-to-understand model.


For complete details, please visit [meraki.cisco.com/support](https://meraki.cisco.com/support).

## Features and capabilities

Meraki switches include all of the traditional Ethernet features found in modern enterprise access switches, including:

### Intelligent campus and branch switching

With built-in monitoring, troubleshooting, and logging capabilities, Meraki switches provide a refreshing new approach to managing network infrastructure, regardless of deployment size. The virtual stacking technology eliminates the need for configuration scripts and commands, empowering administrators to make changes quickly and securely on one or all of the switches in a deployment at once.



Intelligent anomaly detection flags potential network events

### Wired security without compromise

Whether deployed in an office environment, hospital, or retail store, Meraki switches make enforcing security policies a breeze. Set up multiple policies and enable them at the port level or apply them across the entire network in a few clicks. Meraki switches also provide comprehensive security reporting, making it easy to proactively discover rogue DHCP servers and other malicious activity on the network.

Email alerts: Send an email if a new DHCP server is seen

Default DHCP server policy: Allow DHCP servers

Note: Switches with configured DHCP servers are always allowed.

Blocked DHCP servers: 02:31:3a:1c:c4:14


DHCP servers for the last day

| Description                  | VLAN | Subnet         | IP            | Last seen  | Recent packet | Policy  |
|------------------------------|------|----------------|---------------|------------|---------------|---------|
| CORE_1 (interface CORP_WIFI) | 132  | 10.92.132.0/22 | 10.92.135.254 | 13 seconds |               | allowed |
| CORE_1 (interface)           | 46   | 172.16.46.0/23 | 172.16.47.254 | 1 second   |               | allowed |
| SD-WAN_Retry_1               | 42   | 172.16.42.0/23 | 172.16.43.254 | 7 seconds  |               | blocked |

Rogue DHCP server detection across the entire network

## Troubleshooting the way it should be

Drastically reduce time to resolution with a variety of powerful troubleshooting tools, such as remote cable testing and packet captures, that help isolate and troubleshoot network issues. With the dynamic network topology of Meraki, automatically see how the entire network is interconnected and ensure the team receives alerts upon power loss, downtime, or configuration changes.



Remote cable test in the Meraki dashboard

## StackPower and improved physical stacking

StackPower pools power from each individual power supply unit (PSU) in a switch stack to form a larger, shared pool of power that provides additional redundancy and also helps reduce costs by managing the available PoE more efficiently. Improved physical stacking helps in faster-stack convergence in case of a failover, which is critical in large enterprise deployments.

## Industry-leading cloud management

The Meraki cloud-management architecture delivers true zero-touch switch provisioning. Configure switches before they arrive on-site or use Meraki templates to standardize an entire fleet of switches, no matter what size.

With Meraki virtual stacking, administrators can manage up to thousands of ports from a single dashboard, enabling rapid and streamlined configuration that could otherwise take weeks to complete.

| Switch / Port * | Switch      | Name          | Type   | VLAN           | Status | Tags | PDE      | Access policy            | CDR/LLDP      |
|-----------------|-------------|---------------|--------|----------------|--------|------|----------|--------------------------|---------------|
| CORE 1.18       | CORE 1      | StagfG Port   | access | 110            |        |      | Open     | -                        |               |
| CORE 1.17       | CORE 1      | To ALPHA-COR1 | access | 78             |        |      | Open     | stu12-00a-csr1.cisco.com |               |
| CORE 1.18       | CORE 1      | To ALPHA-COR2 | access | 78             |        |      | Open     | stu12-00a-csr2.cisco.com |               |
| Closet 1.12/1   | Closet 1.13 | Cisco Alpha   | access | 110, voice 110 |        |      | disabled | Open                     | SEP0000001101 |

Switch virtual stack for managing all switch ports at once

## Built-in application layer visibility


Meraki is the only switch to include integrated layer 7 fingerprinting. Identify hundreds of applications, from business apps to BitTorrent and YouTube. User fingerprinting with Google-like search allows administrators to easily identify and control individual users, PCs, iPads, Androids, and other devices. This unprecedented visibility allows optimization of network resources and maintenance of optimal network performance.



Granular network client visibility up to the application layer

## Beyond-the-network software architecture

Meraki switches run the same operation system used by all Meraki products. The use of a common operating system allows a consistent experience across all product lines, from security products to VoIP phones. Meraki switches automatically connect to the Meraki cloud, download the configuration, and join the appropriate network. If new firmware is required, this is retrieved by the switch and updated automatically. This ensures the network is kept up-to-date with bug fixes, security updates, and new features.



MERAKI CLOUD-MANAGEMENT ARCHITECTURE WITH ALL PRODUCTS

## Included in the box

|                                    |  |
|------------------------------------|--|
| <b>MS120-8 series</b>              | Integrated mounting brackets; external PSU (non-PoE and LP models); getting started insert   |
| <b>MS120 series</b>                | Getting started insert   |
| <b>MS130 series</b> <sup>1</sup>   | Power supply (1); getting started insert   |
| <b>MS210 series</b>                | Getting started insert   |
| <b>MS225 series</b>                | Getting started insert   |
| <b>MS250 series</b>                | Power supply (1); system fans (2); getting started insert                                    |
| <b>MS350 series</b>                | Stacking cable (1); power supply (1); system fans (2); getting started insert                |
| <b>MS355 series</b>                | Power supply (1); system fans (3); getting started insert                                    |
| <b>MS390 series</b>                | Power supply (1); system fans (3); getting started insert                                    |
| <b>MS410 series</b>                | Power supply (1); system fans (2); getting started insert                                    |
| <b>MS425 series</b>                | Power supply (1); system fans (3); getting started insert                                    |
| <b>MS450 series</b>                | Power supply (1); system fans (3); getting started insert                                    |
| <b>Catalyst Meraki 9300 series</b> | Power supply (1); system fans (3); rack mount brackets and screw kit; getting started insert |

<sup>1</sup> Rack-mount screws are not included in the box, but can be ordered separately. Meraki recommends sourcing rack-mount screws and nuts made for your specific rack.

## Licensing

Every MS license is available in 1-, 3-, 5-, 7-, and 10-year terms.

| Product | Model         | License           | Description                               |
|---------|---------------|-------------------|---|
| MS120   | MS120-8-HW    | LIC-MS120-8-xY    | MS120-8 Enterprise license and support    |
|         | MS120-8LP-HW  | LIC-MS120-8LP-xY  | MS120-8LP Enterprise license and support  |
|         | MS120-8FP-HW  | LIC-MS120-8FP-xY  | MS120-8FP Enterprise license and support  |
|         | MS120-24-HW   | LIC-MS120-24-xY   | MS120-24 Enterprise license and support   |
|         | MS120-24P-HW  | LIC-MS120-24P-xY  | MS120-24P Enterprise license and support  |
|         | MS120-48-HW   | LIC-MS120-48-xY   | MS120-48 Enterprise license and support   |
|         | MS120-48LP-HW | LIC-MS120-48LP-xY | MS120-48LP Enterprise license and support |
|         | MS120-48FP-HW | LIC-MS120-48FP-xY | MS120-48FP Enterprise license and support |
| MS125   | MS125-24-HW   | LIC-MS125-24-xY   | MS125-24 Enterprise license and support   |
|         | MS125-24P-HW  | LIC-MS125-24P-xY  | MS125-24P Enterprise license and support  |
|         | MS125-48-HW   | LIC-MS125-48-xY   | MS125-48 Enterprise license and support   |
|         | MS125-48LP-HW | LIC-MS125-48LP-xY | MS125-48LP Enterprise license and support |
|         | MS125-48FP-HW | LIC-MS125-48FP-xY | MS125-48FP Enterprise license and support |
| MS130   | MS130-8-HW    | LIC-MS130-CMPT-xY | MS130-8 Enterprise license and Support    |
|         | MS130-8P-HW   |                   | MS130-8P Enterprise License and Support   |
|         | MS130-8X-HW   |                   | MS130-8X Enterprise License and Support   |
|         | MS130-12X-HW  |                   | MS130-12X Enterprise License and Support  |
|         | MS130-24-HW   | LIC-MS130-24-xY   | MS130-24 Enterprise License and Support   |
|         | MS130-24P-HW  |                   | MS130-24P Enterprise License and Support  |
|         | MS130-24X-HW  |                   | MS130-24X Enterprise License and Support  |
|         | MS130-48-HW   | LIC-MS130-48-xY   | MS130-48 Enterprise License and Support   |
|         | MS130-48P-HW  |                   | MS130-48P Enterprise License and Support  |
|         | MS130-48X-HW  |                   | MS130-48X Enterprise License and Support  |
| MS210   | MS210-24-HW   | LIC-MS210-24-xY   | MS210-24 Enterprise license and support   |
|         | MS210-24P-HW  | LIC-MS210-24P-xY  | MS210-24P Enterprise license and support  |
|         | MS210-48-HW   | LIC-MS210-48-xY   | MS210-48 Enterprise license and support   |
|         | MS210-48LP-HW | LIC-MS210-48LP-xY | MS210-48LP Enterprise license and support |
|         | MS210-48FP-HW | LIC-MS210-48FP-xY | MS210-48FP Enterprise license and support |

## Licensing

Every MS license is available in 1-, 3-, 5-, 7-, and 10-year terms.

| Product                       | Model         | License          | Description  |
|-------------------------------|---------------|------------------|--|
| Catalyst Meraki 9300 24 ports | C9300-24T-M   | LIC-C9300-24E-xY | Catalyst Meraki 9300 24 ports Enterprise license and support |
|                               | C9300-24P-M   | LIC-C9300-24A-xY | Catalyst Meraki 9300 24 ports Advanced license and support   |
|                               | C9300-24U-M   |                  |  |
|                               | C9300-24UX-M  |                  |  |
| Catalyst Meraki 9300 48 ports | C9300-48T-M   | LIC-C9300-48E-xY | Catalyst Meraki 9300 48 ports Enterprise license and support |
|                               | C9300-48P-M   | LIC-C9300-48A-xY | Catalyst Meraki 9300 48 ports Advanced license and support   |
|                               | C9300-48U-M   |                  |  |
|                               | C9300-48UXM-M |                  |  |
|                               | C9300-48UN-M  |                  |  |



## Optional accessories

| Description                 | Accessory   | Supported models   |
|-----------------------------|---|--|
| Power cable                 | Region-specific power cords are not included in the box. Order the appropriate power cord separately:<br>MA-PWR-CORD-US      MA-PWR-CORD-BR<br>MA-PWR-CORD-EU      MA-PWR-CORD-TW<br>MA-PWR-CORD-UK      MA-PWR-CORD-AU<br>MA-PWR-CORD-CN      MA-PWR-CORD-AR<br>MA-PWR-CORD-IN | All models   |
| 150 W power adapter         | MA-PWR-150WAC-ADP   | MS130-8X and MS130-8P  |
| 300 W power adapter         | MA-PWR-300WAC-ADP   | MS130-12X  |
| 30 W power adapter          | MA-PWR-30WAC  | MS130-8  |
| External power supply       | DC 54 V/1.67 A, 90 W, MA-PWR-90WAC<br>DC 12 V/2.5 A, 30 W, MA-PWR-30WAC   | MS120-8, MS120-8-LP  |
| 250 W power supply          | MA-PWR-250WAC   | MS250-24, MS250-48, MS350-24, MS350-48, MS410, MS425         |
| 640 W power supply          | MA-PWR-640WAC   | MS250-24P, MS250-48LP, MS350-24P, MS350-48LP                 |
| 1,025 W power supply        | MA-PWR-1025WAC  | MS250-24P, MS250-48FP, MS350-24X, MS350-48FP                 |
| 350 W power supply          | MA-PWR-350WAC   | MS390-24HW, MS390-48HW                                       |
| 715 W power supply          | MA-PWR-715WAC   | All MS390 models   |
| 1,100 W power supply        | MA-PWR-1100WAC  | All MS390 models   |
| Stacking cable (.5 m)       | MA-CBL-40G-50CM   | MS210, MS225, MS250, MS350, MS410, MS425                     |
| Stacking cable (1 m)        | MA-CBL-40G-1M   | MS210, MS225, MS250, MS350, MS410, MS425                     |
| Stacking cable (3 m)        | MA-CBL-40G-3M   | MS210, MS225, MS250, MS350, all MS410 models, MS425          |
| 16K system fan              | MA-FAN-16K  | MS350-24, MS350-24P, MS350-48, MS350-48LP, MS350-48FP, MS410 |
| 18K system fan              | MA-FAN-18K  | MS350-24X, MS425 series                                      |
| StackPower cables           | MA-CBL-SPWR-30CM<br>MA-CBL-SPWR-150CM   | All MS390 models   |
| Stacking cables             | MA-CBL-120G-50CM<br>MA-CBL-120G-1M<br>MA-CBL-120G-3M  | All MS390 models   |
| 8× 1/10G SFP+ uplink module | MA-MOD-8×10G  | All MS390 models   |
| 4× 1/10G SFP+ uplink Module | MA-MOD-4×10G*   | All MS390 models   |
| 2× 40G QSFP+ uplink module  | MA-MOD-2×40G  | All MS390 models   |
| 16K2 system fan             | MA-FAN-16K2   | All MS390 models   |

\* MA-MOD-4× 10G reached end-of-sale on November 1, 2021. Please refer to its [end-of-sale announcement](#) for further details

Meraki MS switches support SFP/SFP+/QSFP+ optic accessories for high-speed connectivity. Meraki offers a variety of GbE, 10 GbE, and 40 GbE accessories. Full specifications and compatibility information is available in the [Meraki accessories datasheet](#).

## Optional accessories

| Description                                    | Accessory          | Supported models            |
|--|--------------------|-----------------------------|
| 350 W AC power supply                          | PWR-C1-350WAC-P-M  | Catalyst Meraki 9300 series |
| 715 W AC power supply                          | PWR-C1-715WAC-P-M  | Catalyst Meraki 9300 series |
| 1,100 W AC power supply                        | PWR-C1-1100WAC-P-M | Catalyst Meraki 9300 series |
| Catalyst Meraki C9300 30 cm StackPower cable   | CAB-SPWR-30CM-M    | Catalyst Meraki 9300 series |
| Catalyst Meraki C9300 150 cm StackPower cable  | CAB-SPWR-150CM-M   | Catalyst Meraki 9300 series |
| Catalyst Meraki 120G stacking cable, 0.5 meter | STACK-T1-50CM-M    | Catalyst Meraki 9300 series |
| Catalyst Meraki 120G stacking cable, 1 meter   | STACK-T1-1M-M      | Catalyst Meraki 9300 series |
| Catalyst Meraki 120G stacking cable, 3 meter   | STACK-T1-3M-M      | Catalyst Meraki 9300 series |
| System fan                                     | FAN-T2-M           | Catalyst Meraki 9300 series |
| Catalyst Meraki C9300 rack mount kit           | 4PT-KIT-T1-M       | Catalyst Meraki 9300 series |
| 2× 40G uplink module                           | C9300-NM-2Q-M      | Catalyst Meraki 9300 series |
| 2× 10G/1G uplink module                        | C9300-NM-2Y-M      | Catalyst Meraki 9300 series |
| 8× 10G/1G uplink module                        | C9300-NM-8X-M      | Catalyst Meraki 9300 series |

## Additional resources

[Meraki MS120 series datasheet](#)

[Meraki MS125 series datasheet](#)

[Meraki MS130 series datasheet](#)

[Meraki MS210 series datasheet](#)

[Meraki MS225 series datasheet](#)

[Meraki MS250 series datasheet](#)

[Meraki MS350 series datasheet](#)

[Meraki MS355 series datasheet](#)

[Meraki MS390 series datasheet](#)

[Meraki MS410 series datasheet](#)

[Meraki MS425 series datasheet](#)

[Meraki MS450 series datasheet](#)

[Catalyst Meraki 9300 series datasheet](#)