

Product datasheet

Specifications



InRow 30kW Condensing Unit, 400V, Single feed

ACCU302

Main

Main Input Voltage	415 V AC 3 phases
Provided Equipment	Installation guide Integrated network management Network management card User manual

General

Compressor Type	Scroll
Air Discharge Option	Upflow
Intake Air Option	Top return
Tube Material	Copper

Physical

Height	155.4 cm
Width	100.1 cm
Depth	100.1 cm
Net Weight	266.98 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Usb Compatible	No

Input

Number Of Feeders	1
Network Frequency	50/60 Hz

Conformance

Product Certifications	cUL listed UL listed
------------------------	-------------------------

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more >](#)

Eu Rohs Directive

Under investigation

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
