

Product data sheet

Specifications



Network Management Card, UPS Network Management Cards, for Easy UPS 3 Series, 3-Phase, remotely monitor and manage the UPS

AP9547

Overview

Presentation

The Network Management Card for Easy UPS 3 Series (AP9547) enables secure remote monitoring and control of one Easy UPS 3S, Easy UPS 3M or Easy UPS 3L through the easy-to-use web browser interface, via EcoStruxure™ IT Software or another SNMP-enabled system. A 12-month support contract, that allows the customer to access future firmware updates, is included with purchase of the card. Upon expiration of the provided support contract the purchase of a new support contract license is required to access future firmware updates and gain the additional benefits of fast access to new features, priority support and rapid cybersecurity updates. Choose "License" under "This product is compatible with" to learn more about the Support Contract Licenses available.

Lead time

Usually in Stock

Main

Product or Component Type

Network Interface

Provided Equipment

User Manual
USB cable

Physical

Height

1.73 in (4.4 cm)

Width

2.05 in (5.2 cm)

Depth

3.15 in (8.0 cm)

Net Weight

0.11 lb(US) (0.05 kg)

Mounting preference

No preference

Mounting Mode

Not rack-mountable

Conformance

Standards

CISPR 32
EN 55024
EN 61000-4-2
EN 61000-4-3
EN 61000-4-4
EN 61000-4-5
EN 61000-4-6
EN 61000-4-8
EN 61000-6-2
EN/IEC 62040-2

Product Certifications

FCC Class A
ICES-003
VCCI Class A
AS/NZS

Environmental

Ambient air temperature for operation	23...113 °F (-5...45 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Communications & Management

Communication network type	10/100/1000BASE-T
----------------------------	-------------------

Ordering and shipping details

GTIN	731304422495
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	6.69 in (17.0 cm)
Package 1 Length	9.45 in (24 cm)
Package 1 Weight	10.58 oz (300 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	44
Package 2 Height	19.29 in (49 cm)
Package 2 Width	13.78 in (35 cm)
Package 2 Length	24.41 in (62 cm)
Package 2 Weight	33.25 lb(US) (15.08 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	352
Package 3 Height	45.24 in (114.9 cm)
Package 3 Width	38.19 in (97 cm)
Package 3 Length	38.19 in (97 cm)
Package 3 Weight	276.90 lb(US) (125.6 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes

Recommended replacement(s)