## TRIPP-LITE

1000 Eaton Boulevard Cleveland, OH 44122 United States

### Isobar 4-Outlet 230V Surge Protector, Detachable 6 ft. (1.83 m) Cord, 680 Joules, Metal Housing

#### MODEL NUMBER: EURO-4



Premium protection for valuable electronics against dangerous surges, spikes and line noise that can damage equipment or destroy data. Recommended for home, corporate, retail, telecom and industrial applications.

#### Description

Premium protection for home, corporate, retail, telecom and industrial applications, the EURO-4 Isobar® 4-Outlet 230V Surge Protector features a surge protection rating of 680 joules to defend your sensitive electronics against surges and spikes.

The EURO-R features four widely spaced C13 outlets, which are arranged in two exclusive isolated filter banks that prevent equipment connected to one bank from interacting with equipment connected to the other. These internal barriers also prevent disruptive line noise from causing A/V distortion, computer lock-ups, data errors and similar problems. Large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors remove EMI/RFI interference and prevent system crashes, reboots and performance problems.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the EURO-4 protects all three, covering two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

An integrated 9A circuit breaker protects all outlets and shuts down connected equipment in the event of an overload. A lighted on/off switch provides one-touch control over connected components. A C14 inlet accepts a variety of detachable power cords, such as the included 6-ft. (1.83 m) C13 cable. An all-metal housing ensures long life and durability.

#### Features

**680-Joule Surge Protection for Home or Office Electronics**Protects your A/V components, network hardware, retail displays, appliances, power tools and other electronics against surges and spikesRecommended for home, corporate, retail, telecom and industrial applications requiring AC line protectionFull normal mode (H-N) and common mode (N-G/H-G) line surge suppressionExceeds IEEE 587 Category A and B surge suppression specifications

4 Outlets Accept Wide Range of Electronic Devices 4 C13 outletsOutlets accommodate up to 2 transformers without blocking other outlets

**Isolated Filter Banks Provide Extra Protection**Outlets arranged in exclusive isolated filter banks to limit noise interaction among connected equipmentBlocks disruptive EMI/RFI line noise that can cause equipment damage or data lossCombines large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and metal oxide varistors to block interference

#### Highlights

- 4 C13 outlets in exclusive isolated filter banks
- 680-joule surge protection rating
- Durable metal housing designed for tough environments
- 9A resettable circuit breaker prevents dangerous overloads
- Detachable 6-ft. (1.83 m) C13to-C14 power cord

#### **Package Includes**

- EURO-4 Isobar 4-Outlet 230V Surge Protector, Metal Housing
- Detachable C13-to-C14 power cord, 6-ft. (1.83 m)
- Owner's manual

# TRIPP-LITE

1000 Eaton Boulevard Cleveland, OH 44122 United States

**Premium Safety Features**Lighted on/off switch provides one-touch control over connected equipmentAutomatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Fits Effortlessly Into Your WorkstationDetachable 6-ft. (1.83 m) C13 power cord reaches nearby outletsC14 inlet accepts wide variety of power cords to match country or site-specific wall outletsKeyhole slots on bottom panel provide convenient wall or desk mounting optionsMetal housing designed for long life

### **Specifications**

| OVERVIEW                           |  |  |
|------------------------------------|--|--|
| UPC Code                           | 037332010049   |  |
|                                    |  |  |
| INPUT                              |  |  |
| Nominal Input Voltage(s) Supported | 230V AC  |  |
| Recommended Electrical Service     | 230V (220-250V)  |  |
| Voltage Compatibility (VAC)        | 220-250  |  |
| Maximum Surge Amps                 | 15000  |  |
| Input Plug Type                    | IEC-320-C13  |  |
| Input Cord Length (ft.)            | 6  |  |
| Right-Angle Plug                   | No   |  |
| Input Cord Length (m)              | 1.83   |  |
| Integrated Cord Clip               | No   |  |
| OUTPUT                             |  |  |
| Frequency Compatibility            | 50 / 60 Hz   |  |
| Output Receptacles                 | (4) C13  |  |
| Circuit Breaker (amps)             | 9  |  |
| Transformer Accommodation          | (2) Yes  |  |
| Right-Angle Outlets                | No   |  |
| USER INTERFACE, ALERTS & CONTROLS  |  |  |
| Diagnostic LED(s)                  | No   |  |
| Switches                           | Two position orange illuminated on/off power switch                          |  |
| SURGE / NOISE SUPPRESSION          |  |  |
| AC Suppression Joule Rating        | 680  |  |
| AC Suppression Response Time       | NM = 0 ns. CM = <1 ns  |  |
| Protection Modes                   | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |  |

## TRIPP-LITE

|  | 1   |
|--|---|
| AC Suppression Components Used                       | Metal oxide varistors, toroidal balanced chokes, ferrite rod-core inductors and VHF capacitors. |
| EMI / RFI Filtering                                  | Yes   |
| Isolated Filter Banks                                | Yes   |
| Immunity   | Conforms to IEE 587 / ANSI C62.41   |
| Automatic Shut-Off                                   | Yes   |
| DATALINE SURGE SUPPRESSION                           | -   |
| Cable (Coax) Protection                              | No  |
| Network (Ethernet) Protection                        | No  |
| Telephone/DSL Protection                             | No  |
| PHYSICAL   |   |
| Material of Construction                             | Metal   |
| Power Cord Color                                     | Light Gray  |
| Housing Color  | Light Gray  |
| Mounting Holes or Slots                              | Yes   |
| Slot or Hole Mount Measurement<br>(Center to Center) | Distance between horizont tabs = 162.13 mm; Distance between vertical tabs = 58.17 mm           |
| Outlets Measurement (Center to Center)               | Distance between horizontal outlets = 53mm; Distance between vertical outlets = 38.10mm         |
| Receptacle Color                                     | Black   |
| Shipping Dimensions (hwd / in.)                      | 9.50 x 2.60 x 5.80  |
| Shipping Dimensions (hwd / cm)                       | 24.13 x 6.60 x 14.73  |
| Shipping Weight (lbs.)                               | 2.00  |
| Shipping Weight (kg)                                 | 0.91  |
| Unit Dimensions (hwd / in.)                          | 2.500 x 7.000 x 3.500   |
| Unit Dimensions (hwd / cm)                           | 8.9 x 17.8 x 6.4  |
| Unit Weight (lbs.)                                   | 2   |
| Unit Weight (kg)                                     | 0.91  |
| FEATURES & SPECIFICATIONS                            |   |
| Rotatable Outlets                                    | No  |
| Antimicrobial  | No  |
| STANDARDS & COMPLIANCE                               |   |
| Product Certifications                               | UL 1449   |
| Product Compliance                                   | RoHS; CE (Europe)   |



1000 Eaton Boulevard Cleveland, OH 44122 United States

#### WARRANTY & SUPPORT

Product Warranty Period (Worldwide)

Lifetime limited warranty



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.