



Release Notes for Cisco Catalyst IE9300 Rugged Series Switches, and Cisco Catalyst ESS9300 Embedded Series Switch, Cisco IOS XE Dublin 17.12.x

First Published: 2023-07-28

Last Modified: 2023-07-28

Cisco Catalyst IE9300 Rugged Series Switches and Cisco Catalyst ESS9300 Embedded Series Switch

This document provides release information for the following Catalyst IE switches:

- Cisco Catalyst IE9310 GE Fiber switch
- Cisco Catalyst IE9320 GE Fiber switch
- Cisco Catalyst IE9320 Fiber switch with 10 Gigabit uplinks
- Cisco Catalyst ESS9300 Embedded Series Switch

Cisco Catalyst IE9300 Rugged Series Switches provide rugged and secure switching infrastructure for harsh environments. It is suitable for industrial Ethernet applications, including manufacturing, utility substations, intelligent transportation systems (ITSs), rail transportation, and other similar deployments.

The switch fulfills the need for a high-density SFP, rack-, or wall-mount switch that can function as a software-defined (SD)-Access fabric edge. It provides end-to-end architectural uniformity in the Cisco Digital Network Architecture (DNA) for Internet of Things (IoT) connected communities and extended enterprises.

In industrial environments, the switch can be connected to any Ethernet-enabled industrial communication devices. These devices include programmable logic controllers (PLCs), human-machine interfaces (HMIs), drives, sensors, and input and output (I/O) devices.

The Cisco Catalyst ESS9300 Embedded Series Switch is a Small Form Factor (SFF) Ruggedized 10 GgE Embedded platform for tactical, outdoor, and mobile environments. The compact design simplifies integration and offers the system integrator the ability to use the ESS9300 in a wide variety of applications. The Cisco ESS 9300 consists of one switch card. There are no cooling plates sold with it. It is up to the system integrator to design a thermal solution. The ESS-9300-10X-E board supports up to 10 ports of 10 GE fiber. Thermal power is 35 Watts.



Note The documentation set for this product strives to use bias-free language. For purposes of this documentation set, bias-free is defined as language that does not imply discrimination based on age, disability, gender, racial identity, ethnic identity, sexual orientation, socioeconomic status, and intersectionality. Exceptions may be present in the documentation due to language that is hard coded in the user interfaces of the product software, language used based on standards documentation, or language that is used by a referenced third-party product.

New Features for Cisco Catalyst IE9300 Rugged Series Switches and Cisco Catalyst ESS9300 Embedded Series Switch

The features in the following table are new in this release for the supported switches.

Table 1: New Features for Cisco Catalyst IE9300 Rugged Series Switches

Feature Name	License Level	Description	Supported Switches
MODBUS TCP	<ul style="list-style-type: none"> Network Essentials Network Advantage 	<p>Beginning in this release, you can use MODBUS TCP on Cisco Catalyst IE9300 Rugged Series Switches. The feature enables you to connect the switch over an Ethernet network to a variety of devices.</p> <p>Note This feature is supported only on standalone systems..</p>	<ul style="list-style-type: none"> IE-9310-26S2C-E IE-9310-26S2C-A IE-9320-26S2C-E IE-9320-26S2C-A IE-9320-22S2C4X-E IE-9320-22S2C4X-A
SNMP MIB support for PTP	<ul style="list-style-type: none"> Network Essentials Network Advantage 	<p>Beginning with this release, SNMP management information bases (MIBs) are supported on Cisco Catalyst IE9300 Rugged Series Switches for Precision Time Protocol (PTP). The feature enables you to get PTP-related information from a switch remotely.</p>	<ul style="list-style-type: none"> IE-9310-26S2C-E IE-9310-26S2C-A IE-9320-26S2C-E IE-9320-26S2C-A IE-9320-22S2C4X-E IE-9320-22S2C4X-A

Table 2: New Features for the Cisco Catalyst ESS9300 Embedded Series Switch

Feature Name	License Level	Description	Supported Switches
Full Network Advantage features support	Network Advantage	Advantage License support on the Cisco Catalyst ESS9300 Embedded Series Switch	ESS-9300-10X-E with ESS9300-NW-A=

Switch Model Numbers

Cisco Catalyst IE9300 Rugged Series Switches

The following table lists the supported IE9300 series hardware models and the default license levels that they are delivered with.

Model Number	Default License Level	Stacking Support	Description
IE-9310-26S2C-A	Network Advantage	No	<ul style="list-style-type: none"> • <i>Total ports:</i> 28 • <i>SFP uplinks:</i> 4x 1000M SFP • <i>SFP downlinks:</i> 22x 100M/1000M SFP, 2x 100M/1000M dual-media • <i>Power supplies:</i> Support for field-replaceable, redundant AC or DC power supplies
IE-9310-26S2C-E	Network Essentials		

Model Number	Default License Level	Stacking Support	Description
IE-9320-26S2C-A	Network Advantage	Yes	<ul style="list-style-type: none"> • <i>Total ports:</i> 28 • <i>SFP uplinks:</i> 4x 100/1000M SFP • <i>SFP downlinks:</i> 22x 100M/1000M SFP, 2x 100M/1000M dual-media • <i>Power supplies:</i> Support for field-replaceable, redundant AC or DC power supplies
IE-9320-26S2C-E	Network Essentials		
IE-9320-22S2C4X-A	Network Advantage	Yes	<ul style="list-style-type: none"> • <i>Total ports:</i> 28 • <i>SFP uplinks:</i> 4x 1/10Gb SFP+ • <i>SFP downlinks:</i> 22x 100M/1000M SFP, 2x 100M/1000M dual-media • <i>Power supplies:</i> Support for field-replaceable, redundant AC or DC power supplies
IE-9320-22S2C4X-E	Network Essentials		

All Cisco Catalyst IE9300 Rugged Series Switches have 4 GB of DRAM, four alarm inputs, and one alarm output. Other I/O include the following:

- SD-cards socket
- Power input
- RJ-45 (RS-232) console
- Micro-USB console
- USB-A host port



Note This document uses the following terms:

- IE9310 GE Fiber when referring to both IE-9310-26S2C-A and IE-9310-26S2C-E switches.
- IE9320 GE Fiber when referring to both IE-9320-26S2C-A and IE-9320-26S2C-E switches.
- IE9320 Fiber switch with 10G uplinks when referring to both IE-9320-22S2C4X-A and IE-9320-22S2C4X-E switches.

Cisco Catalyst ESS9300 Embedded Series Switch

The ESS9300 is a ruggedized 10G embedded platform that is designed for embedded applications for tactical, outdoor, and mobile installations requiring low power, small size, and ruggedization. Its features include:

- Single board
- Small form-factor board size (110 x 85 mm; 4.3 x 3.3 in.)
- 10 ports of 10G: Enhanced Small Form-Factor Pluggable (SFP+)
- Ethernet management port (optional)
- RS-232 and USB console
- Common +3.3VDC and +5VDC power inputs
- Low power—35W (typical)
- 4 GB DDR4 DRAM
- 8 GB onboard eMMC flash storage (2.5 GB usable space)

Starting with release 17.10.1, both the Network Essentials license and the Network Advantage license are available. The features available in the two licenses follow the IE9300 series, with the exception of MACsec-256.

Table 3: Ordering Information

Product ID	Product Description
ESS-9300-10X-E	ESS9300 board, no cooling plate, Network Essentials software.
ESS9300-NW-A=	Cisco Network Advantage license for ESS9300 Series Spare.

Network Advantage License	Description
Security	MACsec-256
Routing	Layer 3 routing support

Upgrading the Switch Software

This section covers the various aspects of upgrading or downgrading the device software.



Note See the [Cisco IOS XE Migration Guide for IIoT Switches](#) for the latest information about upgrading and downgrading switch software.

Finding the Software Version

The package files for the Cisco IOS XE software can be found on the system board flash device flash (flash:) or external SDFlash (sdflash:).

You can use the **show version** privileged EXEC command to see the software version that is running on your switch.



Note Although the **show version** output always shows the software image running on the switch, the model name shown at the end of this display is the factory configuration and does not change if you upgrade the software license.

You can also use the **dir filesystem:** privileged EXEC command to see the names and versions of other software images that you might have stored in flash memory.

Software Images for Cisco IOS XE Dublin 17.12.x

The following table provides the filenames for the IOS XE 17.12.x software image for Cisco Catalyst IE9300 Rugged Series Switches and the Cisco Catalyst ESS9300 Embedded Series Switch.

Release	Image Type	Filename	Switch Model
Cisco IOS XE.17.12.1	Universal	ie9k_iosxe.17.12.01.SPA.bin	<ul style="list-style-type: none"> • IE9300 • ESS9300

Software Installation Options

The following table lists the options for the **install** command for Cisco Catalyst IE9300 Rugged Series Switches and the Cisco Catalyst ESS9300 Embedded Series Switch.

To install and activate the specified file, and to commit changes to be persistent across reloads, enter the following command: **install add file filename [activate commit]**

Option	Description
abort	Abort the current install operation.
activate	Activate an installed package.

Option	Description
add	Install a package file to the system.
auto-abort-timer	Install auto-abort-timer.
autoupgrade	Initiate software auto-upgrade on all incompatible switches.
commit	Commit the changes to the load path.
deactivate	Deactivate an install package.
label	Add a label name to any installation point.
remove	Remove installed packages.
rollback	Rollback to a previous installation point.

Licensing

This section provides information about the licensing packages for features available on Cisco Catalyst IE9300 Rugged Series Switches and the Cisco Catalyst ESS9300 Embedded Series Switch.

License Levels

The software features available on Cisco Catalyst IE9300 Rugged Series Switches fall under these base or add-on license levels.

Base Licenses

- Network Essentials
- Network Advantage: Includes features available with the Network Essentials license and more.

Add-on Licenses

Add-on licenses require a Network Essentials or Network Advantage as a prerequisite. The features available with add-on license levels provide Cisco innovations on the switch, and on the Cisco Digital Network Architecture Center (Cisco DNA Center).

- DNA Essentials
- DNA Advantage: Includes features available with the DNA Essentials license and more.

To find information about platform support and to know which license levels a feature is available with, use Cisco Feature Navigator. To access Cisco Feature Navigator, go to <https://cfng.cisco.com>. An account on Cisco.com is not required.

Cisco Catalyst ESS9300 Embedded Series Switch

The software features available for the Cisco Catalyst ESS9300 Embedded Series Switch fall under these base license levels.

Base Licenses

- Network Essentials
- Network Advantage: Includes features available with the Network Essentials license and more.

To find information about platform support and to know which license levels a feature is available with, use Cisco Feature Navigator. To access Cisco Feature Navigator, go to <https://cfmng.cisco.com>. An account on Cisco.com is not required.

Smart Licensing Using Policy

Smart Licensing Using Policy, which is an enhanced version of Smart Licensing, is the default and the only supported method to manage licenses.

Smart Licensing using Policy provides a licensing solution that does not interrupt the operations of your network. Instead, it enables a compliance relationship to account for the hardware and software licenses you purchase and use.

With this licensing model, you do not have to complete any licensing-specific operations, such as registering or generating keys before you start using the software and the licenses that are tied to it. Only export-controlled and enforced licenses require Cisco authorization *before* use. License usage is recorded on your device with timestamps, and the required workflows can be completed later.

Multiple options are available for license usage reporting – this depends on the topology you implement. You can use the Cisco Smart Licensing Utility (CSLU) Windows application, or report usage information directly to Cisco Smart Software Manager (CSSM). A provision for offline reporting for air-gapped networks, where you download usage information and upload to CSSM, is also available.

Starting with this release, Smart Licensing Using Policy is automatically enabled on the device. This is also the case when you upgrade to this release.

By default, your Smart Account and Virtual Account in CSSM is enabled for Smart Licensing Using Policy.

Caveats

Caveats describe unexpected behavior in Cisco IOS XE releases.

Open Caveats

Identifier	Description
CSCwf41579	"logging alarm informational" command causes the generation of irrelevant information from PTP logs.

Resolved Caveats

Identifier	Description
CSCwd78599	IE9300: Dying gasp messages are not received on power loss to switch

Troubleshooting

For the most up-to-date, detailed troubleshooting information, see the Cisco TAC website at this URL:

<https://www.cisco.com/en/US/support/index.html>

Go to **Product Support** and select your product from the list or enter the name of your product. Look under Troubleshoot and Alerts, to find information for the problem that you are experiencing.

Related Documentation

Information about Cisco IOS XE at this URL: <https://www.cisco.com/c/en/us/products/ios-nx-os-software/ios-xe/index.html>.

Information about Cisco Catalyst IE9300 Rugged Series Switches is at this URL: <https://www.cisco.com/c/en/us/products/ios-nx-os-software/ios-xe/index.html>

Information about the Cisco Catalyst ESS9300 Embedded Series Switch is at this URL: <https://www.cisco.com/c/en/us/support/switches/catalyst-ess-9300-10x-embedded-switch/model.html>

Cisco Validated Designs documents at this URL: <https://www.cisco.com/go/designzone>

To locate and download MIBs for selected platforms, Cisco IOS releases, and feature sets, use Cisco MIB Locator found at the following URL: <http://www.cisco.com/go/mibs>