

XEROX®

Technology | Document Management | Consulting Services

Phaser® 6360



color laser printer

Office color performance redefined





Phaser® 6360

Color Laser Printer

Setting the standard for high-performance color laser printers, the Xerox Phaser 6360 leads the industry with best-in-class print speed and exceptional color performance. Easy to operate and engineered to meet the exacting demands of high-volume office environments, the Phaser 6360 laser printer isn't just an obvious choice — it's the only choice.

Unrivaled performance

In the race for print speed supremacy, the Phaser 6360 printer sets the pace.

- Get unparalleled, professional-quality color at a blazing print speed of up to 42 ppm — so fast, jobs you used to outsource can be printed in-house.
- Stay efficient in a busy environment with a first-page-out time as fast as 9 seconds.
- A print resolution of 2400 dpi and Adobe® PostScript® 3™ page description language combine to give your work vibrant, true-to-life colors and crisp text and image definition.
- As the industry's only letter-size color printer with a built-in 1 GHz processor, the Phaser 6360 has the muscle to handle even the most complex print jobs.
- The Phaser 6360DN, DT and DX configurations feature standard onboard duplexing for fast, automatic, two-sided printing.

Printing simplified

With ultra-fast setup and seamless operation, the Phaser 6360 printer delivers unbeatable ease-of-use.

- User-friendly installation software gets the Phaser 6360 out of the box and running smoothly on your network in minutes.
- PhaserSMART™ online troubleshooting saves you time by providing 24/7 access to the Xerox Knowledge Base system.
- Check print job status from the comfort of your chair with Xerox CentreWare® IS Embedded Web Server which works seamlessly with your browser.
- The built-in PrintingScout™ function tracks print jobs and provides immediate print-issue alerts and timely correction suggestions.
- Smart Trays alleviate guesswork by showing all available media types and sizes at print time.
- Convenient email alerts notify network administrators of common hang-ups, such as low toner levels, to help maintain an uninterrupted workflow.



Printer management made simple. Easily manage, configure and monitor the Phaser 6360 with intuitive, built-in software.



Real-time paper and supply-level status lets you take action before the printer runs out.

Built for sharing

High-capacity paper volumes, powerful performance features and seamless network integration make the Phaser 6360 the ultimate multiuser printing solution.

- A maximum paper input of 2,350 pages and high-capacity toner cartridges keep the Phaser 6360 poised to handle a steady stream of print jobs.
- Up to 5 paper trays allow the Phaser 6360 to easily adapt to the size of your office.
- A 100,000-page-per-month duty cycle provides reliable operation for high-demand office environments.
- A variety of printing possibilities — from booklet to banner to a full range of custom sizes — lets your creativity run wild.
- Administrators can easily collect, organize and analyze print job accounting data from multiple printers via the Usage Analysis Tool.



Spectacular results. Bring everyday office print jobs to life with attention-grabbing color quality.



Not only is the Phaser 6360 printer ultra-fast and easy to use, it's also designed to provide the utmost flexibility. As the number of users increases, so can the print-volume capability.

- 1 The standard 150-sheet multipurpose tray supports a wide range of media, from executive to banner, card stock to envelopes.
- 2 The standard 550-sheet tray boosts capacity for extended printing.
- 3 An optional 550-sheet paper tray provides added convenience and no-hassle media loading.
- 4 5 Add the 1,100-sheet, high-capacity feeder and turn the Phaser 6360 into a convenient floor-standing printer with a total paper capacity of 2,350 sheets.

Phaser® 6360

Call today. For more information, call **1-877-362-6567** or visit us at **www.xerox.com/office**



	Phaser 6360N	Phaser 6360DN	Phaser 6360DT	Phaser 6360DX
Speed	Up to 42 ppm color / 42 ppm black-and-white			
Duty Cycle	100,000 pages / month*			
Paper Handling	Tray 1 (MPT): 150 sheets; Selectable sizes: 3.5 x 5.5 in. to 8.5 x 36 in. / 89 x 140 mm to 216 x 914 mm Tray 2: 550 sheets; Selectable sizes: Up to Legal / A4			
Paper input	Standard			
Additional 550-sheet Feeder	Optional		Standard	Optional
Additional 1100-sheet Feeder	Optional			Standard
Paper output	250 sheets			
Two-sided output	Optional	Standard		
Print				
First-page-out time	As fast as 9 seconds color			
Resolution (max)	2400 x 600 dpi			
Processor	1 GHz			
Memory (std / max)	256 MB / 1 GB		512 MB / 1 GB	
Connectivity	10/100Base-TX Ethernet, USB 2.0			
Page Description Languages	Adobe® PostScript® 3™, PCL® 5c emulation			
Print features	Booklet printing, Poster printing, Negative image, Mirror image, Scaling, Watermarks, Custom-size pages, Run Black, Covers, Separators, RAM collation, Remote Printing, N-up			
Productivity kit	Optional			Hard drive: Secure/Proof/Personal/Shared Saved/Personal Saved Print, Print With, Hard disk collation, PDF-direct print, Extended font/form storage
Warranty	One-year on-site warranty, Xerox Total Satisfaction Guarantee			

*Print volume uniformly distributed over 30 days.

Device Management

CentreWare® IS Embedded Web Server, CentreWare Web, Xerox NDPS Gateway, Xerox Usage Analysis Tool, Xerox Support Centre, Configuration card, PrintingScout™, MailInX email alerts, PhaserSMART®

Print Drivers

Windows® 2000/XP/2003 Server, Vista™, Mac OS® 9.x/X version 10.2 and higher, Novell NetWare® 5.x/6.5 (NPDS only), Linux Red Hat®, Fedora™ Core 5, SUSE™ Linux 10.0, UNIX: Sun Solaris™ 9/10, IBM AIX® 5.1, HP/UX® 11.0/11i, Xerox Walk-Up® Printer Drivers with Windows 2000 or higher

Security

802.1x protocol (EAP-MD5, EAP-TLS, EAP-PEAPv0-MSCHAPv2)

Font Support

PostScript® Fonts: 139; PCL® Fonts: 81

Media Handling

Tray 1 (MPT): 17–40 lb. bond to 50–80 lb. cover / 65–216 gsm
 Trays 2–5: 17–40 lb. bond to 50–60 lb. cover / 65–163 gsm
 Two-sided output: 17–60 lb. bond / 65–163 gsm
 Media types: Plain paper, glossy, envelopes, labels, transparencies, card stock

Color Standards

PANTONE® Color approved solid-color simulations, Adobe® PostScript® device-independent color, CIE International color standards, Color options, ICC Profile, Apple ColorSync®

Operating Environment

Temperature: Storage: 32° to 95° F / 0° to 35° C, Operating: 50° to 90°F / 10° to 32°C
 Humidity: 15% to 85%
 Sound pressure levels: Printing: 58.0 dB(A), Standby: 34.4 dB(A)
 Sound power levels: Printing: 7.26 B, Standby: 5.0 B
 Warm-up time (from sleep mode): 49 seconds

Electrical

Power: 110–127 VAC, 50/60 Hz or 220–240 VAC, 50/60 Hz
 Power consumption: 110–127 VAC: Standby: less than 105 W, Printing: less than 750 W, Power save: less than 20 W, 220–240 VAC: Standby: less than 95 W, Printing: less than 750 W, Power save: less than 22 W, 6360DN/DT/DX: ENERGY STAR® qualified

Dimensions (WxDxH)

6360N/DN: 17.2 x 22.8 x 20.2 in. / 429 x 580 x 513 mm
 6360DT: 17.2 x 22.8 x 25.4 in. / 429 x 580 x 643 mm
 6360DX: 22.5 x 27.5 x 33.8 in. / 572 x 698 x 854 mm
 Weight: 6360N/DN: 77.4 lb. / 35.2 kg, 6360DT: 92.4 lb. / 42 kg, 6360DX: 123.6 lb. / 56.2 kg

Certifications

FCC Part 15, Class A, Listed UL 60950-1/CSA 60950-1-03, CE Mark applicable to Directives 73/23/EEC, 89/336/EEC, and 1999/5/EC, Section 508 ADA

Supplies

Standard-capacity toner cartridge:
 Black: 9,000 pages¹ 106R01217
 Cyan: 5,000 pages¹ 106R01214
 Magenta: 5,000 pages¹ 106R01215
 Yellow: 5,000 pages¹ 106R01216
 High-capacity toner cartridge:
 Black: 18,000 pages¹ 106R01221
 Cyan: 12,000 pages¹ 106R01218
 Magenta: 12,000 pages¹ 106R01219
 Yellow: 12,000 pages¹ 106R01220

Routine Maintenance Items

Imaging unit: 35,000 pages² 108R00645
 110V Fuser: 100,000 pages³ 115R00055
 220V Fuser: 100,000 pages³ 115R00056
 Transfer roller: 35,000 pages 108R00646

Options

N to DN Upgrade 097S03791
 Productivity kit 097S03747
 550-sheet feeder 097S03378
 1100-sheet feeder 097S03379
 256 MB Phaser memory 097S03381
 512 MB Phaser memory 097S03382
 Wireless network adapter
 - N. American power converter 097S03740
 - Euro power converter 097S03741
 - UK power converter 097S03742



¹Average standard pages. Declared Yield based on 5% area coverage on letter/A4-size page. Yield will vary based on image, area coverage and print mode.

²Approximate pages. Declared yield based on an average job size of 4 A4-letter-size pages. Yield will vary depending on job run length and media size and orientation.

³Approximate pages. Declared yield based on A4-letter-size 20 lb. / 75 gsm pages. Yield will vary depending on media type, size, weight, orientation and usage patterns.

Copyright © 2007 XEROX CORPORATION. All rights reserved. Contents of this publication may not be reproduced in any form without permission of XEROX CORPORATION. XEROX®, Phaser®, PhaserSmart®, CentreWare® and PrintingScout™ are trademarks of XEROX CORPORATION in the U.S. and/or other countries. Total Satisfaction Services is a service mark of XEROX CORPORATION. All other trademarks are the property of their respective manufacturers. PANTONE Colors generated may not match PANTONE-identified standards. Consult current PANTONE publications for accurate color. PANTONE and other Pantone, Inc. trademarks are the property of Pantone, Inc. PCL® is a registered trademark of Hewlett-Packard. As an ENERGY STAR partner, XEROX CORPORATION has determined that these products (Phaser 6360DN / DT / DX) meet the ENERGY STAR guidelines for energy efficiency. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. The information in this brochure is subject to change without notice. 2/07 610P727150 6360R-01UA