



G2016wa2

Cabinet Color	Black
Panel	TFT Active Matrix LCD VIS: 20" (51.1cm) Widescreen, Diagonal Hard Coating (3H), Anti-glare Treatment
Pixel Pitch	0.258mm x 0.258mm
Display Area	433.44mm x 270.90mm
Brightness	300 cd/m2 (typ)
Contrast Ratio	1000:1 (typ)
Response Time	5ms (typ)
Viewing Angle	Horizontal: 160 Degrees Vertical: 160 Degrees
Compatibility	VESA, WSXGA, SXGA, XGA, SVGA, VGA Mac® Equipped With VGA Port
Scanning Frequency	Horizontal: 31K~81KHz Vertical: 56~75 Hz
Pixel Frequency	146MHz
Maximum Resolution	1680x1050x60Hz
Recommended Resolution	1680x1050@60Hz
Resolutions Supported	720x400@70Hz, 640x480@60, 72, 75Hz 800x600@56, 60, 72, 75Hz, 832x624@75Hz 1024x768@60, 70, 72, 75Hz, 1280x1024@60, 70, 72, 75Hz, 1280x960@60Hz, 1680x1050@60Hz
Color	16.7M
Signal Input	Video: 0.7Vp-p, RGB Analog Separate Sync: TTL Level H/V Sync: Positive / Negative
Digital Input	DVI-D (TMDS) with HDCP*
Connectors	Analog RGB Signal: 15-pin D-sub Male Digital Signal: 24-pin DVI-D Power: (3-Pin Plug CEE22) Audio: 3.5m Stereo
Power Source	Universal 110~240VAC, 50/60Hz
Power Consumption	50Watts (Max)
Plug & Play	DDC2B
EPA ENERGY STAR®	Yes
User Control	Auto Adjust Key/ Exit, Decrease</ Audio, Increase>/ Audio, MENU, Power
OSD Function	Contrast, Brightness, H-Position, V-Position, Clock, Phase, Color Management(9300k/ 6500k, 1 user mode, sRGB), OSD Language, OSD Position, System Status/Frequency Info. Auto Adjust, Volume, Mute
OSD Languages	English, French, Spanish
Regulations	cULus, FCC, CE, ISO 13406-2, Windows® Vista Premium Logo,
Built-in Speakers	1W x 2
Other Features	720p/1080i HD Compatible, VESA 100mm Wall Mount Compliant**, Kensington Security Slot
Dimensions (WxHxD mm)	Monitor: 473x398x215; Carton 528x460x148
Dimensions (WxHxD inches)	Monitor: 18.6x15.7x8.5; Carton 20.8x18.1x5.8
Monitor Dimensions w/o Base (WxHxD)	473x310.23x73mm; 18.6x12.2x2.9 inches
Weight	11.9 lbs (5.4 kgs) Net 15.0 lbs (6.8 kgs) Gross
Loading Qty w/pallet	20' = 608 pcs.; 40' Std = 1368 pcs.
UPC Code	685417103881