TRIPP-LITE

1000 Eaton Boulevard Cleveland, OH 44122 United States

Protect It! 7-Outlet Surge Protector, 6 ft. (1.83 m) Cord, 1080 Joules, Fax/Modem Protection, RJ11

MODEL NUMBER: SUPER6TEL





Description

SUPER6TEL surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. High-grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modern lines, fax machines, cordless phones and more. SUPER6TEL offers seven total outlets, six-foot cord with a space-saving right-angle plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy-grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs and three designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories.

Features

- 1080 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6-ft. (1.83 m) phone cable)
- 6-ft. (1.83 m) cord with space-saving right-angle plug
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- UL1449 3rd Edition Rated (400V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$50,000 Ultimate Lifetime connected equipment insurance (U.S., Canada, and Puerto Rico only)

Specifications

Highlights

- 7 outlets / 6-ft. cord
- 1080 joule rating
- Modem/fax surge protection

Package Includes

- SUPER6TEL Surge Suppressor
- 6-ft. (1.83 m) telephone cord
- Instruciton manual with warranty information



1000 Eaton Boulevard Cleveland, OH 44122 United States

NPUT Nominal Input Voltage(s) Supported 12	037332095428 120V AC 120V (110-125V) Right Angle
NPUT Nominal Input Voltage(s) Supported 12	20V AC 20V (110-125V)
Nominal Input Voltage(s) Supported 12	20V (110-125V)
	20V (110-125V)
Pacammandad Electrical Service	
	Right Angle
nput Plug Features Ri	יופויע אונאיס
nput Cord Gauge Type 14	4 gauge; SJT
nput Cord Gauge (AWG) 14	4
Voltage Compatibility (VAC) 12	20
Maximum Surge Amps 72	72000
nput Plug Type N	NEMA 5-15P
nput Cord Details S.	SJT
nput Cord Length (ft.) 6	3
Right-Angle Plug Ye	/es
input Cord Length (m) 1.	.83
Integrated Cord Clip No	No
OUTPUT	
Frequency Compatibility 50	50 / 60 Hz
Output Receptacles (7	7) 5-15R
Circuit Breaker (amps) 15	5
Transformer Accommodation (4	4) Yes
Outlet Orientation Si	Single row of 5, plus 2 side mounted outlets
Right-Angle Outlets No	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	/es
Switches Tv	Two position on/off power switch
Diagnostic LED Details But	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating 10	080
AC Suppression Response Time <	< 1 ns
Protection Modes In	ncludes full normal mode (H-N) and common mode (N-G / H-G) line suppression
JL1449 Let Through Rating 40	100V

TRIPP-LITE

EMI / RFI Filtering	Up to 20 dB	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	Yes	
PHYSICAL		
Material of Construction	Plastic	
Power Cord Color	Gray	
Housing Color	Light Gray	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 70 mm; Distance between slot height = 24 mm	
Outlets Measurement (Center to Center)	Between Standard Outlets = 29mm; Between Transformer Outlets = 48mm	
Receptacle Color	Gray	
Shipping Dimensions (hwd / in.)	12.90 x 2.30 x 6.00	
Shipping Dimensions (hwd / cm)	32.77 x 5.84 x 15.24	
Shipping Weight (lbs.)	1.50	
Shipping Weight (kg)	0.68	
Unit Dimensions (hwd / in.)	1.540 x 2.720 x 10.300	
Unit Dimensions (hwd / cm)	3.91 x 6.91 x 26.16	
Unit Weight (lbs.)	1.39	
Unit Weight (kg)	0.63	
Input Cord Color	White	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed	
Product Compliance	FCC Part 68; RoHS	
WARRANTY & SUPPORT		



1000 Eaton Boulevard Cleveland, OH 44122 United States

Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance	\$50,000 Ultimate Lifetime
(U.S., Canada & Puerto Rico)	Insurance



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.