

VX1962wm

19" WIDESCREEN LCD
WITH 6000:1 DYNAMIC CONTRAST

The amazing lifestyle display.

ViewSonic's 19" VX1962wm widescreen LCD offers the perfect balance of performance and style. With its elegant lines, the VX1962wm fits beautifully into your office décor and its high performance features BLEND EFFORTLESSLY INTO YOUR TECHNOLOGY LIFESTYLE. Images leap from the screen with Super-HD 1680x1050 resolution, video response as fast as 2ms and 6000:1 DYNAMIC CONTRAST RATIO (typ). Scrolling text, Internet pages and spreadsheet applications are displayed in crisp, blur-free detail with precise color. The SRS WOW HD speakers powerfully complement your games, movies and other multimedia applications. Demanding designers, professionals and gamers will love the sophisticated performance of the 19" VX1962wm.



SOPHISTICATION AND PERFORMANCE.

- > **Full 19" viewable widescreen with 1680x1050 resolution**
High resolution panel with 36% more clarity than a regular 19" wide monitor.
- > **Fast ClearMotiv® video response**
Video response as fast as 2ms enables digital HD broadcast-quality video.
- > **6000:1 dynamic contrast ratio (typ)**
Provides for darker black levels and better overall front-of-screen performance.
- > **Stylish slim-bezel design**
The thin bezel lets you see more without taking up valuable desktop real estate.
- > **OptiSync® digital/analog inputs expand your connectivity**
Multi-mode input technology supports both digital (DVI) and analog (VGA) signals for ultimate compatibility and configuration flexibility.
- > **OnView® controls for superior screen adjustability**
Screen adjustments are precisely made via an easy-to-use on-screen menu.
- > **SRS WOW HD sound and high quality stereo speakers**
- > **Windows Vista® certified**
- > **PC and Mac compatible**
- > **TCO'03 and ENERGY STAR® qualified**

1680x1050
SUPER HD

6000:1
Dynamic Contrast Ratio

SRS
WOW HD



VIEWSONIC
PRODUCTS, PROGRAMS,
AND SERVICES

ViewSonic®
See the difference®

VX1962wm

19" WIDESCREEN LCD WITH 6000:1 DYNAMIC CONTRAST



LCD	Type	19" Wide Color TFT Active Matrix LCD
	Display Area	16.1" horizontal x 10.0" vertical; 19.0" diagonal
	Optimum Resolution	1680x1050
	Contrast Ratio	1000:1 static (typ), 6000:1 dynamic (typ)
	Viewing Angles	170° horizontal, 150° vertical @ contrast ratio > 10:1
	Response Time	up to 2ms (gray-to-gray); 5ms black-to-white (typ)
	Light Source	Long life, 40,000 hrs. (typ)
	Brightness	300 cd/m ² (typ)
Panel Surface	Anti-glare	
VIDEO INPUT	Analog/Digital	RGB analog (75 ohms, 0.7 Vp-p)/DVI-D
	Frequency	F _H : 24~82kHz, F _V : 50~75Hz
	Sync	H/V separated (TTL), composite, sync-on-green
COMPATIBILITY	PC	VGA up to 1680x1050 non-interlaced
	Mac [®] *	G3/G4/G5 up to 1680x1050
CONNECTOR	Analog/Digital	15-pin mini D-sub/DVI-D
	Power	3-pin AC plug (CEE22)
AUDIO	Speaker	2x3-watt SRS WOW HD**
POWER	Voltage	AC 100~240V, 50~60Hz (auto switch)
	Consumption	44W (typ)
ERGONOMICS	Tilt	-5/+20°
CONTROLS	Basic	Power, 1, down, up, 2
	OnView [®]	Auto image adjust, brightness, contrast, input select (analog, digital), ViewMatch [®] color adjust (sRGB, 9300K, 7500K, 6500K-default, 5400K, user color-RGB), information (resolution, H. frequency, V. frequency, pixel clock, model number, serial number), manual image adjust (H. size, H. position, V. position, fine tune, sharpness, dynamic contrast aspect ratio), setup menu (language, resolution notice, OSD position, OSD timeout, OSD background), memory recall
OPERATING CONDITIONS	Temperature	32~104°F (0~40°C)
	Humidity	10~90% (non-condensing)
DIMENSIONS (W x H x D)	Physical with stand	17.6" x 15.7" x 6.9" (447mm x 399mm x 175mm)
	Physical without stand	17.6" x 12.5" x 2.0" (447mm x 317mm x 51mm)
WEIGHT	Net with stand	8.61 lb. (3.9 kg)
	Net without stand	6.8 lb. (3.1 kg)
	Gross with stand	11.5 lb. (5.2 kg)
REGULATIONS		UL, cUL, FCC-B, CB, CE, ENERGY STAR [®] , NOM, NEMKO/GS (covers TUV/GS), NEMKO ERGO (covers TUV/ERGO, ISO 13406-2 & MPR II), TCO'03, GOST-R + 20 original copies hygienic, SASO, PCBC, VCCI, BSMI, CCC, PSB, C-TICK, Argentina-S, Green Mark, RoHS, EPEAT-Silver
RECYCLE/DISPOSAL		The lamp in this product contains mercury. Please dispose of in accordance with local, state or federal laws.
POWER MANAGEMENT		Meets MPRII and ENERGY STAR [®] standards
PACKAGE CONTENTS		LCD display, power cable, 15-pin VGA video cable, DVI cable, Quick Start Guide, ViewSonic Wizard CD
WARRANTY		Three-year limited warranty on LCD, parts and labor



ViewSonic Corporation's QMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by the British Standards Institution.

Sales: (888) 881-8781 • SalesInfo@ViewSonic.com • ViewSonic.com

*Adapter may be required. Analog adapter available from ViewSonic. **Requires SRS Audio Sandbox Software to be installed. Specifications subject to change without notice. Selection, offers and programs may vary by country; see your ViewSonic representative for complete details. Windows Vista and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. Corporate names, trademarks stated herein are the property of their respective companies. Copyright © 2008 ViewSonic Corporation. All rights reserved. [13838-00B-01/08] VX1962wm-1

ViewSonic[®]
See the difference[®] 

For more product information, visit us on the web at ViewSonic.com