

DataShield Serial In-Line Surge Protector, DB9

MODEL NUMBER: DB9



Is your DB9 serial connection protected? If not, your equipment is vulnerable to damage and performance problems. Surges and line noise don't just affect the power line; they can enter your equipment on any connection. So protect your DB9 serial equipment with the DataShield™ DB9 In-Line Surge Suppressor. It's the ideal choice for protecting PCs, printers, modems and anything with a DB9 connection.

Description

Tripp Lite's DB9 offers dataline surge suppression for DB9 serial ports of data terminal and data communications equipment, including PCs, printers, modems and more. User configurable for use with male or female captive DB9 ports. Offers protection on all 9 lines, plus D shell chassis. Convenient DB9 input and output connects directly to the protected port, obtaining a ground outlet from the computer chassis. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges away from network interface connections. Tripp Lite network surge suppressors reduce blown interface cards, garbled transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground.

SUPPRESSION: Reversible DB9 m/f jacks, protects pins 1-9 and chassis, 18V clamping

Features

- DB9 protects 9 pin serial connections for dataline surge suppression of data terminal, data communications equipment and PCs, printers, modems and more
- Reversible for use with male or female captive DB9 ports
- Offers protection on all 9 data lines, plus D shell chassis
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground

Specifications

OVERVIEW

UPC Code

037332010834

Highlights

- Complete serial port (DB9) surge protection
- Protects against the effects of electrostatic discharge

Package Includes

- 1 DB9 Surge Suppressor



INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V, 230V
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(1) Network
Circuit Breaker (amps)	340
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Clamping Voltage (RMS)	18
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Additional Dataline Protection	1-9 & Chassis
PHYSICAL	
Color	Light Gray
Antimicrobial Coating	No
Integrated Keyhole Mounting Slots	No
Shipping Dimensions (hwd / cm)	12.70 x 7.62 x 5.08
Shipping Dimensions (hwd / in.)	5.00 x 3.00 x 2.00
Shipping Weight (kg)	0.07
Shipping Weight (lbs.)	0.16
SPECIAL FEATURES	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Rotatable Outlets	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>