

# VA2626wm

## 26" (25.5" VIEWABLE) VALUE SERIES WIDESCREEN LCD

WITH 5MS VIDEO RESPONSE

## Feature-rich big screen.

ViewSonic's 26" (25.5" viewable) VA2626wm LCD brings high-performance, widescreen displays to home office users, students and others who want a great desktop display. In addition to Super-HD 1920x1200 resolution, this big 26-inch LCD also features EXTREME CLARITY, AMAZING COLOR and FAST 5MS CLEARMOTIV® VIDEO RESPONSE. Enjoy beautiful graphics and view spreadsheets in unbelievable clarity. Enhance your desktop with the stylish, slim-bezel design and enhance your productivity with the ability to VIEW TWO FULL-SIZE DOCUMENTS SIDE-BY-SIDE or work in multiple applications simultaneously on the widescreen display. Only 3.6" deep without the stand this display's VESA® wall-mount compliance allows the VA2626wm to fit beautifully into any office décor. Desktop users can enjoy panoramic performance without breaking their budgets.



### ENHANCE YOUR VIEW AND PRODUCTIVITY

- > OptiSync® digital/analog inputs expand your connectivity  
Multi-mode input technology supports digital (HDMI), digital (DVI) and analog (VGA) signals for ultimate compatibility and configuration flexibility.
- > Full HD (1080p) Support with in 1920x1200 High Resolution
- > 6000:1 dynamic contrast ratio  
Provides darker black levels and better overall front-of-screen performance.
- > Fast 5ms video response delivers superior picture clarity
- > SRS WOW HD sound  
Extends the speaker frequency range, delivering better response and sound performance.
- > Windows Vista certified
- > TCO'03 and ENERGY STAR® qualified



**VIEWSONIC**  
PRODUCTS, PROGRAMS,  
AND SERVICES

**ViewSonic®**  
See the difference™ 

# VA2626wm

26" (25.5" VIEWABLE) VALUE SERIES WIDESCREEN LCD WITH 5MS VIDEO RESPONSE

Model No.VS12068



<b>LCD</b>	Type	25.5" Wide Color a-Si TFT Active Matrix
	Display Area	593mm (H) × 371mm(V) / 23.36" (H) × 14.6" (V)
	Optimum Resolution	1920x1200@60Hz
	Brightness	450 cd/m <sup>2</sup> (Typ)
	Contrast Ratio	800:1(Typ.) / 6000:1(Dynamic Contrast Ratio)
	Viewing Angles	170° (H), 160° (V) (CR≥10)
	Response Time	5ms
	Panel Surface	Anti-Glare, Hard coating(3H)
	Light Source	40,000 hrs (Min.)
<b>VIDEO INPUT</b>	Analog	RGB Analog (75 ohms, 0.7 / 1.0 Vp-p)
	Digital	DVI (TMDS, 100 ohms), HDMI (TMDS, 100 ohms)
	Sync	Separate, composite, SOG
	Frequency	Fh:24-82kHz, Fv:50-85Hz
<b>COMPATIBILITY</b>	PC	VGA up to 1920×1200 Non Interlaced
	Mac	Power Mac up to 1920×1200
<b>CONNECTOR</b>	Analog	15 pin mini D-sub×1
	Digital	DVI-D, HDMI (support HDCP and DDC/CI) (Cable option)
	Audio-in	3.5 mm Audio line-in
	Power	Built-in power Adapter, 3-Pin plug
<b>ERGONOMICS</b>	Tilt	Down 5°, Up 20°
<b>MULTIMEDIA</b>	Speaker	2.5Wx2
		SRS WOW HD Surround
<b>POWER</b>	Voltage	AC 100-240V (Universal); 50/60Hz(Switch)
	Consumption	80W (Typ.) / 64W (for Energy Star -II)
<b>CONTROLS</b>	Basic	[1], [2], Power, Down[▼], Up[▲]
	OnView	Auto Image Adjust, Contrast / Brightness, Input Select (D-Sub, DVI-D, HDMI), Audio Adjust (Volume, Mute), Color Adjust (sRGB, 9300K, 6500K, 5000K, User Color [R, G, B]), Information (Resolution / Video Format, H Frequency, V Frequency, Pixel Clock, Serial Number)
<b>OPERATING CONDITIONS</b>	Temperature	5°C - 35°C (41°F - 95°F)
	Humidity	20 - 80%(Non condensed)
<b>DIMENSIONS (WXHxD)</b>	Physical (mm)	596mm × 479mm × 255mm (With Base)
<b>WEIGHT</b>	Net	7.39kg (16.29lb)
<b>REGULATIONS</b>		CB, TCO'03, WEEE, ROHS, UL/cUL, FCC-B, IRAM, NOM, Energy Star, NEMKO/ERGO, CE, UkrSEPRO, GOST-R+Hygienic, SASO, BSMI, PSB, C-TICK, VCCI, CCC
<b>Wall Mount</b>		Meet VESA ( 100mm X 100mm ) Standards

Rev.1d



ISO 9001:2000  
FM 40187

ISO 14001:1996  
FM 40968

ViewSonic Corporation's QMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by the British Standards Institution.

#### Headquarters:

381 Brea Canyon Road,  
Walnut, CA 97189, U.S.A.  
salesinfo@viewsonic.com  
www.viewsonic.com

#### Asia Pacific:

9F, No. 1 92 Lien Chien Road,  
Chung Ho, Taipei, R.O.C.  
www.viewsonic.com.tw

#### ViewSonic Singapore:

Marine Parade Road #09-02  
Parkway Parade  
Singapore 449269  
www.viewsonic.com.sg

#### ViewSonic Australia:

Unit 4, 44 Dickson Ave, Artarmon  
NSW 2064, Australia  
www.viewsonic.com.au

#### ViewSonic Korea:

#2110, 21F, Renaissance Tower Bldg.,  
456 Gongdeok-dong, Mapo-gu, Seoul,  
121-020, Korea  
www.kr.viewsonic.com

#### ViewSonic India:

Unit No.2, 3 & 4 (Ground Floor),  
Tribhuvan Complex,  
Ishwar Nagar, Mathura Road,  
New Delhi - 110065  
in.viewsonic.com

**ViewSonic®**  
See the difference™ 

For more product information, visit us on the web at [ViewSonic.com](http://ViewSonic.com)

20080807