


# Protect It! 8-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 2160 Joules, Tel/Fax/Modem/Coax Protection, RJ11

# MODEL NUMBER: TLP808TELTV











## Description

Tripp Lite's TLP808TELTV surge suppressor has 8 outlets, an 8-ft. (2.43 m) cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

#### Features

- 8 outlets with integrated child safety covers; charcoal gray housing
- 8-ft. (2.43 m) cord with space-saving right-angle plug
- Built-in RJ11 jacks (1 in/2 out) prevent surges from damaging your modem/fax/phone equipment; 6-ft. (1.83 m) telephone cord included
- Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment; 6-ft. (1.83 m) gold coax cable included
- Surge suppression rating: 2160 joules
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Diagnostic LEDs indicate protection present & ground present
- Audible alarm notifies user when the unit is damaged and needs to be replaced
- Keyhole supports for wall mounting
- Lighted power switch
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing

### Highlights

- 8 outlets / 8-ft. (2.43 m) cord
- 2160 joule rating
- 2.2GHz gold coaxial surge

protection

Modem/fax surge protection

#### Package Includes

- TLP808TELTV
- 6-ft. (1.83 m) telephone cord
- 6-ft. (1.83 m) gold coax cable
- Instruction manual with warranty information



equipment damage and indicating replacement is required

# **Specifications**

OVERVIEW	
UPC Code	037332095343
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(6) Yes
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CON	TROLS
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Audible Alarm	Audible alarm
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2160
	·



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line
SPECIAL FEATURES	
Unit Weight (Ibs.)	1.9
Unit Weight (kg)	0.86
Unit Dimensions (hwd / in.)	4.86 x 9.55 x 1.51
Unit Dimensions (hwd / cm)	12.34 x 24.26 x 3.84
Shipping Weight (lbs.)	2.40
Shipping Weight (kg)	1.09
Shipping Dimensions (hwd / in.)	11.50 x 2.40 x 8.70
Shipping Dimensions (hwd / cm)	29.21 x 6.10 x 22.10
Receptacle Color	Gray
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm
Material of Construction	Plastic
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 75mm; Distance between vertical tabs = 41.6mm
Integrated Keyhole Mounting Slots	Yes
Housing Color	Dark Gray
Color (AC Line Cord)	Black
Antimicrobial Coating	No
Color	Black
PHYSICAL	
Network (Ethernet) Protection	No
Cable (Coax) Protection Details	1 line
Cable (Coax) Protection	Yes
Telephone/DSL Protection Details	1 line
Telephone/DSL Protection	Yes
DATALINE SURGE SUPPRESSION	
Automatic Shut-Off	Yes
EMI / RFI Filtering	Up to 40 dB
UL1449 Let Through Rating	330/400/400
Clamping Voltage (RMS)	150
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression



Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
Industry Canada (Communications)	Industry Canada
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies