

1000 Mbps Gigabit Single-Mode Fiber Ethernet Media Converter SC 15km

Product ID: MCMGBSC15



The MCMGBSC15 Ethernet Media Converter converts transparently to/from 1000Base-T Ethernet signals and 1000Base-LH optical signals, providing a cost-effective Ethernet-fiber/copper-fiber link. - Perfect for extending an Ethernet network connection over a Single Mode fiber backbone.

Supporting a Single Mode fiber optic cable distance of up to 15-kilometers (9.32-miles), this Fiber Media Converter delivers a simple solution for connecting Gigabit Ethernet networks to remote locations using SC-terminated SM fiber, while ensuring solid network performance and scalability.

Certifications, Reports and Compatibility



Applications

- Extending an Ethernet connection by up to 15km (9.32 miles) using a fiber backbone
- Creates an economical Ethernet-fiber/copper-fiber link for connecting remote sub-networks to larger fiber optic networks/backbones
- Converts Ethernet to fiber, fiber to copper/Ethernet, ensuring optimum network scalability for connecting two or more Ethernet network nodes (e.g. connecting two buildings on the same campus)

Features

- Auto detects half/full duplex transfer mode from the TX port
- Auto negotiation MDI/MDI-X (Crossover for TX port)
- Compact design
- LED Indicators for simple Ethernet/Fiber network link monitoring
- Simple installation
- Supports forced full duplex or auto-negotiation modes on the fiber link
- Supports 802.3ab 1000Base-TX, and 1000Base-LX/LH industry standards
- Supports a maximum Single-mode fiber optic cable distance of 15km
- Supports IEEE 802.1q Tag VLAN pass through
- Supports transparent Q-in-Q double tagged frames
- 1310nm Wavelength

Hardware	Warranty	2 Years
	Industry Standards	IEEE 802.3z 1000BASE-LX/LH
	PoE	No
	WDM	No
Performance	Fiber Operating Mode	Half/Full-Duplex
	Max Transfer Distance	15 km (9.3 mi)
	Maximum Data Transfer Rate	1000 Mbps (1 Gbps)
	Type	Single Mode
	Wavelength	1310nm
Connector(s)	Local Unit Connectors	1 - RJ-45 Female
	Remote Unit Connectors	1 - Fiber Optic SC Duplex Female
Indicators	LED Indicators	1 - FX Link: On - Valid Fiber Link 1 - Power Indicator 1 - TP Link: On - Valid Ethernet Link 1 - TP RX: On - Receiving Data on the Ethernet Link
Power	Center Tip Polarity	Positive
	Input Current	0.3 A
	Input Voltage	110V-240V AC
	Output Current	0.6A
	Output Voltage	9 DC
	Plug Type	M
	Power Consumption (In Watts)	5.4
	Power Source	AC Adapter Included
Environmental	Humidity	90% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Color	Black
	Product Height	1.1 in [2.7 cm]
	Product Length	3.9 in [99 mm]
	Product Width	2.9 in [73 mm]
	Weight of Product	8.4 oz [238 g]

Packaging Information	Package Height	2.6 in [65 mm]
	Package Length	8.1 in [20.5 cm]
	Package Width	6.6 in [16.8 cm]
	Shipping (Package) Weight	15.1 oz [428 g]
What's in the Box	Included in Package	
	1 - Media Converter	
	1 - Power Adapter	
	1 - Instruction Manual	

Product appearance and specifications are subject to change without notice.