



ioSafe Solo

+ Data Recovery Service

The world's first affordable high capacity disaster-proof hard drive.



FIREPROOF

Protects against data loss in fire up to 1550°F,
1/2 hour Per ASTM E119



WATERPROOF

Protects data from flood, full submersion, 10' depth,
72 hours fresh or salt water



PC/MAC COMPATIBILITY

USB 2.0 provides full support for
Windows XP, Vista, Windows 7 and Mac



DATA RECOVERY SERVICES

Up to \$1000 for forensic data recovery,



USB 2.0

USB 2.0 up to 480 mb/s transfer rate



THEFTPROOF

Physical theft protection cable lock
or floor mount option

ioSafe Solo External Hard Drive

Product Specifications

Operational Details

- Single disk. 1TB to 2TB capacities.
- Quiet forced air cooling.
- Multi-platform compatibility: Windows XP, Vista, Windows 7 and Mac. (Not supported in a Windows Server Environment)
- USB 2.0, up to 480Mb/s

Disaster & Security Specifications

- Fire protection - 1550F, 1/2 hour per ASTM E119
- Tested per UL, FCC and CE Standards
- Flood / submersion protection - to 10 feet water depth, 3 days.
- Proven data protection and recovery. Tested to ASTM E119 standards for fire exposure.
- Physical theft protection
- Cable lock or floor mount optional

Support

- \$1,000 Data Recovery Service. One time, no questions asked policy. See website for details.
- 3 Year standard manufacturer's warranty for defects

Inside The Box

- ioSafe Solo External Hard Drive
- USB Cable
- Power Supply
- Owners Manual and Warranty

Electrical

- Electrical - AC input
- Voltage: 80 ~ 264 VAC at 50/60 HZ
- Typical Power Consumption: < 25W

System Requirements

- Intel Pentium II 350 Mhz-compatible or Mac G3 processor & greater
- Microsoft Windows XP/Vista/Windows 7 or Mac OS 8.6 & greater (Not supported in a Windows Server Environment)
- USB equipped system
- For USB 2.0 speeds, the system must support USB 2.0 specifications

Operating Environment

- Operating: 0-35° C (95°F)
- Non-operating: 0-1550°F, 1/2 hr per ASTM E119
- Operating Humidity: 20% - 80% (non-condensing)
- Non-operating Humidity: 100%, Full water immersion, 10 feet, 3 days.

Physical

- Size: 5.0"W x 7.1"H x 11.0"L
- Weight: 15 lbs