

## The ultimate in quiet versatility

It is actually possible to get a case that combines versatility, capacity, quietness and 80 PLUS® Certified power. The NSK6580 combines ease-of-use features like a removable 3.5" HDD cage that holds 5 removable trays with Quiet Computing™ technology and a 80 PLUS® Certified EarthWatts 430 Watt power supply with universal input and active PFC. Indirect front bezel vents and silicone grommets for the hard drives minimize noise while the crisp, understated styling makes the NSK6580 an attractive addition to your office.



UCC13# 0761345-96580-4 US  
 UCC13# 0761345-00680-4 EC  
 UCC13# 0761345-00681-1 UK

### Special Features:

- **Quiet and highly efficient 80 PLUS® Certified EarthWatts 430 Watt power supply**
  - Universal input
  - Active PFC and high-efficiency design for superior environmentally-friendly operation
  - 80PLUS® Certification means you'll save money on your power bills
- **Advanced cooling system:**
  - 1 Rear 120mm TriCool™ 3-speed fan
  - 2 Front mounts for optional 92mm fans
  - 1 Advanced Chassis Air Guide, with mount for optional 80mm fan
  - VGA vent
- **9 Drive Bays**
  - Front Accessible: 4 x 5.25" (with one 5.25" to 3.5" adapter)
  - Internal: 5 x 3.5" removable HDD trays with silicone grommets in a removable HDD cage to isolate drive vibrations
- **7 Expansion Slots**
- **Front-mounted ports for easy multimedia connections**
  - 2 x USB 2.0
  - 1 x IEEE 1394 (FireWire®, i.Link®)
  - Audio In and Out
- **0.8mm cold-rolled steel construction**
- **Motherboard:** Fits micro and standard ATX
- **Dimensions:**
  - 18.3" (H) x 8.25" (W) x 18.6" (D)
  - 46.5cm (H) x 21cm (W) x 47.2cm (D)



www.antec.com • 1-800-22ANTEC (US) / +31 (0) 10 462-2060 (EU)  
 More information on 80Plus® financial advantages for SI's/VAR's  
 in North America under [www.antec.com/us/80Plus.html](http://www.antec.com/us/80Plus.html)

**Antec**  
 The Power of You