

you can
Canon

Black & White printers for
medium-sized workgroups

iR1020/1024 Series

iR1020, iR1024A, iR1024F,
iR1024i, iR1024iF

iR2018/2030 Series

iR2018/i, iR2022/i
iR2025/i, iR2030/i

**PRINT
SCAN
COPY
SEND**



Business never looked better in black & white

Big impact, small size. Now you can ensure your business communications create a big impression – with only a little effort. Both the Canon iR1020/1024 and iR2018/2030 Series combine the skills of many devices into small space-saving multifunctional units, giving you high quality printing, scanning, copying and sending.

COPY SCAN PRINT SEND

DO MORE FOR LESS

By connecting these intelligent all-in-one devices to your network, you can add powerful communication tools to your business. From entry-level everyday black & white A4 printers to more sophisticated document and publishing capabilities up to A3, you'll find what you're looking for with these two great ranges.

ENVIRONMENTALLY FRIENDLY

These highly energy efficient products have a stand-by power consumption as low as 3.5w

ENHANCE YOUR PRODUCTIVITY WITH COLOUR I-SEND

Colour i-Send scans and converts hardcopies into electronic files for distribution across public telephone lines, the Internet, or a local area network.

WHY USE COLOUR I-SEND?

- Time saving: send to multi-destinations and destination types in one go.
- Enhanced quality: documents can be sent in colour, an improvement over traditional fax transmission.
- Increased flexibility as documents can be emailed directly from the device.
- Quick and reliable: both internet and traditional phone lines can be used.
- Cost & space efficient.
- Internet faxes incur no extra charge and there is no need for additional fax/scanner purchase.
- Cost effective: no more high courier bills.



Canon iR1020/1024 – Communicate with incredible speed

Entry level pricing high quality A4 printing

Sitting comfortably on your desk, Canon iR1020/24 printers will help you print, copy and fax desktop communications quickly in black and white, plus you can scan and send in glorious colour too.



FAST, EFFECTIVE, PRODUCTIVE

Canon iR1020/24 printers meet the specific requirements of small business or workgroups needing compact, cost-effective power. You can print 20-24 pages per minute and also scan and send information directly from the device in a variety of formats.

PLUG AND PLAY

To save you time and increase productivity, all these devices come network ready*.

WHY CHOOSE A4?

- Ideal when space is at a premium.
- When you need the versatility of an A3 device e.g.
 - Scan and send
 - Fax
 - iFax
 - Collate and staple

* The iR1020, iR1024A & iR1024F come with UFRII and require a network adaptor. The iR1024i & iR1024iF come with UFRII & PCL and network adaptor as standard.

SAVE SPACE, AND THE ENVIRONMENT TOO

A compact footprint means you don't have to use valuable floor space for different devices, you get everything you need in one small desktop model. As part of Canon's commitment to reducing environmental impact, these models automatically go into energy-saving sleep mode when the device is not in use - and can power back up in seconds as soon as they are needed.

SLEEP MODE LESS THAN 5W

WHY BUY CANON GENUINE CONSUMABLES?

Only Canon genuine consumables can guarantee optimal device performance and the highest quality output.

COPY SCAN PRINT SEND



C-EXV18 Toner

Business has never looked better in black & white - especially with our genuine toner.



iR1020

- Print/copy at up to 20ppm
- Sits comfortably on your desk



iR1024A

- Print/copy at up to 24ppm
- Automatic Document Feeder (ADF)



iR1024F

- Print/copy/fax at up to 24ppm
- Automatic Document Feeder (ADF)
- Built-in modem for speedy faxing
- Store up to 200 fax numbers



iR1024i

- Print/copy/scan/send at up to 24ppm
- Automatic Document Feeder (ADF)
- Scan colour documents
- Email scanned documents directly to recipient
- PCL Printing



iR1024iF

- Print/copy/scan/fax/send at up to 24ppm
- Automatic Document Feeder (ADF)
- Scan colour documents
- Email scanned documents directly to recipient
- PCL Printing

COPY SCAN PRINT SEND



C-EXV14 Toner

Business has never looked better in black & white – especially with our genuine toner.



Picture shown is i-model



Picture shown is i-model

iR 2018/i

- Print/copy/fax/send at up to 18ppm
- Print up to A3
- Simple network integration

iR 2022/i

- Remote fleet control with iWMC and RUI
- Additional finishing and paper capacity options

		COPY	PRINT	ADF	FAX	SCAN	SEND
iR 2018	18ppm	●	●	○	○	●	
iR 2018i	18ppm	●	●	●	○	●	●
iR 2022	22ppm	●	●	○	○	●	
iR 2022i	22ppm	●	●	●	○	●	●
iR 2025	25ppm	●	●	○	○	●	○
iR 2025i	25ppm	●	●	●	○	●	●
iR 2030	30ppm	●	●	○	○	●	○
iR 2030i	30ppm	●	●	●	○	●	●

● STANDARD ○ OPTIONAL



iR 2025/i

- Print/copy/fax/send at up to 25ppm
- Remote fleet control with iWMC and RUI
- Additional finishing and paper capacity options
- Easy-to-use interface and touch-screen



iR 2030/i

- Print/copy/fax/send at up to 30ppm
- Additional finishing and paper capacity options
- Remote fleet control with iWMC and RUI
- Easy-to-use interface and touch-screen
- Optional Card Reader for secure access control

COPY SCAN PRINT SEND

Canon iR2018/2030 – Get your message across in style

Add a little sophistication to your – black & white A3 documents

The Canon iR2018/30 series has been created to deliver fantastic value printing, scanning and copying for up to A3, and publishing capabilities if you require them. All of which enables you to manage cost, productivity, quality of output and your impact on the environment.



SIMPLE, PROFESSIONAL, VERSATILE

Create high quality professional-looking black & white documents with ease, at up to 1,200 dpi (with URFinI lite), with simple finishing options such as double-sided printing and stapling.

PLUG AND PLAY

To save you time and increase productivity, all these devices come network ready.

WHY BUY A3?

- Ideal for printing large excel spreadsheets
- Ideal for copying large documents
- Ideal for scanning large documents and converting them to PDF for electronic storage
- Ideal for increased productivity with the staple and sort functions

EASY ADMINISTRATION WITH CENTRAL MANAGEMENT

All devices in this range can be easily connected to your IT network, enabling you to take advantage of intelligent software solutions. For example, iW Management Console (iWMC), helps you manage, monitor and control multiple networked devices from a single point of control. Plus, Remote User Interface (RUI), gives users easy access and management of any print device connected to your network, direct from all connected PCs.

**STAND-BY POWER
CONSUMPTION: 3.5W**

COPY SCAN PRINT SEND

Specifications iR1020/iR1024 Series

<p>Maximum Original Size Copy Sizes Resolution</p> <p>Copy/Print Speed Magnification First copy time Warm-Up Time</p> <p>Multiple Copies/Prints Double-Sided Paper weight</p> <p>Cassette Paper Capacity (80g/m²) Standard Optional CPU Memory</p>	Desktop A4 Cassette: A4, Stack Bypass: A5 - A4, Envelopes Copying: 600dpi x 600dpi, 1200dpi equivalent x 600dpi Printing: 1200dpi equivalent x 600dpi (PCL, UFRII LT) 256 Gradations A4: 20cpm (1020), 24cpm (iR1024A/24F/24i/24iF) Zoom: 50-200%, Fixed: 50%, 70%, 100%, 141%, 200% 8.0 sec or less (1020), 12.0 sec or less (iR1024A/24F/24i/24iF) less than 16 sec. for iR1020/24A/24F/20/24A/24F less than 19 sec. for iR1024/24iF	<p>UFRII LT (Standard for iR1020/24A/24F/24i/24iF), PCL 5e/6 (Standard for iR1024/24iF)</p> <p>1200dpi equivalent x 600dpi (PCL, UFRII LT)</p> <p>128MB (iR1020/24A/24F), 256MB (iR1024/24iF)</p> <p>Canon Custom Processor, 192MHz (Uses Main Unit CPU)</p> <p>Roman113 (including Barcode Fonts)</p> <p>PCL:Windows2000/XP/Server 2003/Server 2008/Vista UFR II:Windows 2000/XP/Server 2003/Server 2008/Vista/ Mac OSX 10.2.8 or later</p> <p>Interface (Standard) Network Protocol</p>
	1 to 99 sheets Automatic stackless Cassette: 64 to 90g/m ² , Stack Bypass: 56 to 128g/m ² Double-Sided: 64 to 80g/m ² A4	
	500 sheets x 1 cassette, Stack Bypass: 100 sheets 500 sheets x 1 cassette, Max. Total paper capacity: 1,100 sheets Canon Custom Processor, 192MHz 128MB (iR1020/24A/24F), 256MB (iR1024/24i/24iF)	
	Interface Power Supply Power Consumption (W) Dimensions (WxDxH)	iR1020/24A/24F iR1024/iF 220V AC to 240V AC ±10% (50/60Hz) 1023W max. 520 x 457 x 378 mm (20) 520 x 457 x 453 mm (iR1024A/24F/24i/24iF) Approx. 22.0kg (20) Approx. 24.1kg (iR1024A/24F/24i/24iF)
	Scan Speed with DADF Scan Resolution	BW: 20ipm A4 300dpi, Colour: 6ipm A4 300dpi BW: 200x100dpi, 200dpi, 200x400dpi, 300dpi, 400dpi, 600dpi Colour: 100dpi, 150dpi, 200dpi, 300dpi (JPEG) 300dpi (High compression PDF)
	Destinations Address book File Format	E-Mail/Internet FAX (SMTP), PC (SMB,FTP), iWDM Gateway Local (Max.200) Single: (BW) TIFF, PDF - (Colour) JPEG, High compression PDF Multi: (BW) TIFF, PDF - (Colour) High compression PDF
	SEND FUNCTION¹	
	Scan Speed with DADF Scan Resolution	
	Destinations Address book File Format Pull Scan	

<p>PRINTER FUNCTION</p> <p>PDL</p> <p>Resolution Memory</p> <p>CPU</p> <p>PCL Fonts</p> <p>Supported OS</p> <p>Interface (Standard)</p> <p>Network Protocol</p>	UFRII LT (Standard for iR1020/24A/24F/24i/24iF), PCL 5e/6 (Standard for iR1024/24iF)
	1200dpi equivalent x 600dpi (PCL, UFRII LT)
	128MB (iR1020/24A/24F), 256MB (iR1024/24iF)
	Canon Custom Processor, 192MHz (Uses Main Unit CPU)
	Roman113 (including Barcode Fonts)
	PCL:Windows2000/XP/Server 2003/Server 2008/Vista UFR II:Windows 2000/XP/Server 2003/Server 2008/Vista/ Mac OSX 10.2.8 or later
	Interface (Standard)
	iR1020/24A/24F iR1024/iF
	Ethernet (100Base-TX/10Base-T) optional, USB2.0 Ethernet (100Base-TX/10Base-T), USB2.0
	TCP/IP (LPD/Raw/ Port 9100)

<p>DADF²</p> <p>Paper size</p> <p>Paper weight</p> <p>Max. Number of originals</p> <p>Document Scanning speed (max.)</p> <p>Copy Scan</p>	A4R, A5R, A5 50 g/m ² to 105 g/m ² A5R to A4: 50 sheets (80 g/m ²)
	iR1024A/1024F/1024i/1024iF: A4 20 ipm BW: 20ipm A4 300dpi, Colour: 6ipm A4 300dpi

<p>OTHER ACCESSORIES</p>	IR1020/24 Plain Pedestal, Cassette Feeding Module-N2, Cassette-AD1, Card Reader-E1, Card Reader Attachment-D2, NW IF ADAPTER IN-E11 (Standard for iR1024i/24iF), PCL PRINT KIT-AB1 (Standard for iR1024i/24iF)

Specifications iR2018/2030 Series

<p>Maximum Original Size Copy Sizes Resolution</p> <p>Copy/Print Speed Magnification First copy time Warm-Up Time</p> <p>Multiple Copies/Prints Double-Sided Paper weight</p> <p>Cassette Paper Capacity Standard</p> <p>Multi Stack Bypass Optional</p> <p>Max.Total paper capacity CPU Memory Interface Power Supply Dimensions (WxDxH)</p> <p>Weight</p>	Desktop A3, 297 x 432mm Cassette: A5 - A3, Stack Bypass: A5R-A3, Envelopes Copying: 600dpi x 600dpi, 1200dpi equivalent x 600dpi Printing: 1200dpi equivalent x 600dpi (PCL, UFRII LT), 1200dpi x 1200dpi (UFRII LT), 256 Gradations A4: 18cpm (iR2018/i), 22cpm (iR2022/i), 25cpm (iR2025/i) 30cpm (iR2030/i), A3: 15cpm for iR2018/18/22/22i/25/30/i Zoom: 50-200%, Fixed: 50%, 70%, 100%, 141%, 200% 6.9 sec Approx. 26 seconds (Approx 14 seconds for iR2018/22) 1 to 99 sheets Optional Automatic stackless (Standard for iR2025/30/i) Cassette: 64 to 90g/m ² , Stack Bypass: 64 to 128g/m ² Double-Sided: 64 to 90g/m ² Universal: A5 to A3 Standard 250 sheets x 2 cassettes (80g/m ² , 500 sheets) for iR2022/22i/25/30/i 250 sheets x 1 cassettes (80g/m ² , 250 sheets) for iR2018/i 80 sheets (80g/m ²) for A5R to A4, 50 sheets for A3 (80g/m ²) 250 sheets x 2 cassettes (500 sheets) for iR2022/25/30/i 250 sheets x 3 cassettes (750 sheets) for iR2018/i 250 sheets x 1 cassette for iR2018/i 1,080 sheets Canon Custom Processor, 192MHz 256MB (128MB for iR2018/22) Ethernet (100Base-TX/10Base-T), USB2.0 220V AC to 240V AC ±10% (50/60Hz) 1.5KW max. 622 x 638 x 665.4mm (iR2022), 622 x 676 x 757 mm (iR2022/25/30/i), 622 x 638 x 665.4 mm (iR2025/30) 622 x 638 x 580.4mm (iR2018), 622 x 676 x 672 mm (iR2018/i) Approx. 53.0 kg (iR2022/25/30), Approx. 47.0 kg (iR2025/30) Approx. 47.0 kg (iR2018/i), Approx. 41.0 kg (iR2018)	<p>A3-A5R 52 g/m² to 105 g/m² A5R to A4: 50 sheets (80 g/m²) A3: 25 sheets (80 g/m²)</p> <p>A4 20 ipm BW: 20ipm A4 300dpi, Colour: 6ipm A4 300dpi 565 x 489.4 x 122 mm Approx. 7.0kg</p> <p>Front-loading adjustable drawers 64 to 90g/m² P1: 250 sheets (80 g/m²) x 1 cassettes for iR2018/i Q1: 250 sheets (80 g/m²) x 2 cassettes for iR2022/25/30/i P1 and Q1: 250 sheets (80 g/m²) x 3 cassettes for iR2018/i P1: 580.3 x 569.3 x 116.8 mm Q1: 580.3 x 569.3 x 201.8 mm P1: Approx. 6.0kg, Q1: Approx. 12.0kg</p> <p>One stack tray + Optional Tray (Inner) Standard: A4/A5/A5R : 770 sheets or 100mm A4R/A3: 380 sheets or 50mm Tray A: A4/A5/A5R 200 sheets, A4R/A3: 150 sheets Tray B: A4/A5/A5R 200 sheets, A4R/A3: 150 sheets Corner A4: 50 sheets, A3/A4R: 30 sheets Approx.10.0kg</p> <p>Tray A: A4 100 sheets, Other 50 sheets, Tray B: A4 250 sheets Other 100 sheets Approx. 1.5kg</p> <p>PCL Printer Kit-W1, Fax Panel-B1 (Optional for iR2018/22, standard on other models), Barcode Printing Kit-B1, Colour Send Kit-1 (Not for iR2018/22), Super G3 FAX Board-AA1, Duplex Unit-B1, iR2016/20 Plain Pedestal High (for 2cassettes configuration), iR2016/20 Plain Pedestal Low (for 4cassettes configuration), FL Cassette-AC1, PLATEN COVER Type J, Staple Cartridge-J1, Staple Ink Cartridge-C1, Additional Finisher Tray-C1 (Optional for Finisher-U2), Card Reader-E1, Card Reader Attachment-D1, Power Supply Kit-Q1 (Required for Finisher-U2 and Cassette Feeding Module-Q1), Signal Converter For NEXUS</p>
---	---	---

you can
Canon

Canon Inc.
www.canon.com

Canon (UK) Ltd
Woodhatch, Reigate
Surrey RH2 8BF
Telephone No. 0800 353535
Fax No. 01737 220 022
www.canon.co.uk

Canon Europa N.V.
www.canon-europe.com

English-UK Edition 0116W148
© Canon Europa N.V., 2008 (1008)

Canon Ireland
Aren Road
Sandyford Industrial Estate
Dublin 18, Ireland
Telephone No. 01-205 2400
Fax No. 01-295 8141
www.canon.ie



Canon's GENUINE logo means
quality all-round performance