

# VA926

**19" VALUE SERIES LCD**  
**WITH 5MS VIDEO RESPONSE**

## Budget savvy desktop space saver.

ViewSonic's 19" VA926 LCD is a brilliant choice for upgrading your home or small office. This ultra-slim, Vista-certified LCD DELIVERS AN IMPRESSIVE ARRAY OF FEATURES that will enhance your productivity while helping you stay within your budget. With OptiSync® digital and analog inputs, 2000:1 DYNAMIC CONTRAST RATIO (typ) and fast ClearMotiv® 5ms video response, you'll enjoy crystal-clear graphics, video and text. The latest OSD/power lock and AutoTune® functions MAXIMIZE AND MAINTAIN YOUR DISPLAY SETTINGS. The VA926 displays excellent taste while enhancing your home or small office desktop.



**2000:1**  
Dynamic Contrast Ratio

### ATTRACTIVE STYLING. ATTRACTIVE PRICE.

- > **Fast 5ms video response** delivers superior picture clarity
- > **Full 19" viewable screen**  
Displays a full, flat 19" viewable area with crisp detail and fully saturated color.
- > **1280x1024 native resolution**  
Incredible image detail for sharp text and graphics.
- > **2000:1 dynamic contrast ratio (typ)**  
Provides for darker black levels and better overall front-of-screen performance.
- > **Stylish slim-bezel design**  
An ultra-thin bezel lets you see more without taking up valuable desktop real estate.
- > **OptiSync® digital/analog inputs expand your connectivity**  
Multi-mode input technology supports both digital (DVI) and analog (VGA) signals for ultimate compatibility and configuration flexibility.
- > **OSD/power lock secures your settings**  
Prevents changes to monitor settings and maintains an optimized image.
- > **OnView® controls for superior screen adjustability**  
Screen adjustments are precisely made via an easy-to-use on-screen menu.
- > **Windows Vista approved**
- > **ViewSonic Wizard included**  
User-friendly Wizard software automates the setup process to deliver optimized screen performance.
- > **PC and Mac® compatible**
- > **TCO'03 and ENERGY STAR® qualified**



**VIEWSONIC**  
PRODUCTS, PROGRAMS,  
AND SERVICES

**ViewSonic®**  
See the difference® 

# VA926

## 19" VALUE SERIES LCD WITH 5MS VIDEO RESPONSE



ViewSonic Corporation's QMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by the British Standards Institution.

ViewSonic Corporation • 381 Brea Canyon Road, Walnut, CA 91789

Customer Service and Technical Support: (800) 688-6688 • Sales: (888) 881-8781 • SalesInfo@ViewSonic.com • ViewSonic.com

\*Adapter may be required. Analog adapter available from ViewSonic. Specifications subject to change without notice. Selection, offers and programs may vary by country; see your ViewSonic representative for complete details. Windows Vista and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. Corporate names, trademarks stated herein are the property of their respective companies. Copyright © 2007 ViewSonic Corporation. All rights reserved. [13627-00B-08/07] VA926-1

<b>LCD</b>	Type	19" color TFT active matrix SXGA LCD
	Display Area	14.8" horizontal x 11.9" vertical; 19.0" diagonal
	Optimum Resolution	1280x1024
	Contrast Ratio	1000:1 static (typ), 2000:1 dynamic (typ)
	Viewing Angles	170° horizontal, 160° vertical
	Response Time	5ms (typ)
	Light Source	Long life, 40,000 hrs. (typ)
<b>VIDEO INPUT</b>	Brightness	300 cd/m2 (typ)
	Panel Surface	Anti-glare
	Analog/Digital	RGB analog (75 ohms, 0.7 Vp-p)/DVI-D
<b>COMPATIBILITY</b>	Frequency	F <sub>H</sub> : 30~82kHz, F <sub>V</sub> : 50~75Hz
	Sync	H/V separated (TTL)
<b>CONNECTOR</b>	PC	VGA up to 1280x1024 non-interlaced
	Mac**	Power Mac™ G3/G4/G5 up to 1280x1024
<b>POWER</b>	Analog/Digital	15-pin mini D-sub/Digital
	Power	3-pin AC plug (CEE22)
<b>POWER</b>	Voltage	AC 100~240V (universal), 50/60Hz (auto switch)
	Consumption	32W (typ)
<b>CONTROLS</b>	Basic	Power, 1, down, up, 2
	OnView®	Auto image adjust, contrast, brightness, input select, ViewMatch® color adjust (sRGB, 9300K, 6500K – default, 5400K, RGB), information, manual image adjust (H. size, H. position, V. position, fine tune, sharpness), setup menu (language, resolution notice, OSD position, OSD timeout, OSD background), memory recall
<b>ERGONOMICS</b>	Tilt	-5°/+20°
<b>OPERATING CONDITIONS</b>	Temperature	32~104°F (0~40°C)
	Humidity	10~90% (non-condensing)
<b>DIMENSIONS (W x H x D)</b>	Physical with stand	16.2" x 17.1" x 7.7" (412mm x 434mm x 194mm)
	Physical without stand	16.2" x 14.0" x 2.5" (412mm x 355mm x 64mm)
<b>WEIGHT</b>	Net with stand	8.4 lb. (3.8 kg)
	Net without stand	7.3 lb. (3.3 kg)
	Gross with stand	11.1 lb. (5.0 kg)
<b>REGULATIONS</b>		UL, cUL, FCC-B, CB, CE, NOM, TUV-S, TUV/GS, TUV/ERGO (covers ISO13406-2), MPR II, BSMI, CCC, ENERGY STAR®, PSB, C-TICK, RoHS, WEEE, VCCI, GOST-R, SASO, TCO'03, EPEAT-Silver
<b>RECYCLE/DISPOSAL</b>		The lamp in this product contains mercury. Please dispose of in accordance with local, state and federal laws.
<b>POWER MANAGEMENT</b>		Meets TCO'03 and ENERGY STAR® standards
<b>PACKAGE CONTENTS</b>		LCD display, video cable, power cable, Quick Start Guide, ViewSonic Wizard (DVI cable not included)
<b>WARRANTY</b>		Three-year limited warranty on parts, labor and backlight

**ViewSonic®**  
See the difference® 

For more product information, visit us on the web at [ViewSonic.com](http://ViewSonic.com)