


Isobar 6-Outlet Surge Protector, 6 ft. Cord with Right-Angle Plug, 3300 Joules, Diagnostic LEDs, Metal Housing

MODEL NUMBER: ISOBAR6



Premium protection for valuable electronics against dangerous surges, spikes and line noise that can damage equipment or destroy data. Recommended for home, corporate, retail, telecom and industrial applications.

Description

Premium protection for essential network workstations, telecom systems, point-of-sale equipment and audio/video systems, the ISOBAR6 Isobar® 6-Outlet Surge Protector features a network-grade surge protection rating of 3300 joules to defend your sensitive electronics against even the strongest surges and spikes. In fact, Tripp Lite will repair or replace any connected equipment damaged by surges up to \$50,000 for life (valid in the U.S., Canada and Puerto Rico only).

The ISOBAR6 features six NEMA 5-15R outlets, which are arranged in three exclusive isolated filter banks that prevent equipment connected to one bank from interacting with equipment connected to the other. These internal barriers also prevent disruptive line noise from causing A/V distortion, computer lock-ups, data errors and similar problems. Large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors remove EMI/RFI interference and prevent system crashes, reboots and performance problems.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the ISOBAR6 protects all three, covering two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

Included safety covers protect against dust while blocking accidental contact with unused outlets. An integrated 12A circuit breaker protects all outlets and shuts down connected equipment in the event of an overload. A lighted on/off switch provides one-touch control over connected component. Diagnostic LEDs show power, protection and line fault status at a glance. A six-foot (1.8-meter) AC power cord with right-angle 5-15P plug reaches nearby outlets and allows furniture to be placed flush against the wall. An all-metal stands up to rugged environments.

Features

Network-Grade 3300-Joule Surge Protection for Home or Office Electronics Protects your essential network workstations, telecom systems, point-of-sale equipment, audio/video systems and other expensive electronics against surges and spikes
Recommended for home, corporate, retail, telecom and industrial applications requiring AC line protection Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Exceeds IEEE 587 Category A and B surge suppression specifications

Highlights

- 6 NEMA 5-15R outlets in exclusive isolated filter banks
- Network-grade 3300-joule surge protection rating
- Durable metal housing designed for tough environments
- 12A resettable circuit breaker prevents dangerous overloads
- 6 ft. AC power cord with right-angle NEMA 5-15P plug

Package Includes

- ISOBAR6 Isobar 6-Outlet Surge Protector, Metal Housing
- (4) Outlet safety covers
- Owner's manual



6 Outlets Accept Wide Range of Electronic Devices 6 NEMA 5-15R AC outlets accept most computer equipment, electronics, appliances and power tools Outlets accommodate up to 3 bulky transformers without blocking other outlets Included safety covers block accidental contact with unused outlets

Isolated Filter Banks Provide Extra Protection Outlets arranged in 3 exclusive isolated filter banks to limit noise interaction among connected equipment Block disruptive EMI/RFI line noise up to 80 dB that can cause equipment damage or data loss Combine large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and metal oxide varistors to block interference

Premium Safety Features Lighted on/off switch provides one-touch control over connected equipment Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required Diagnostic LEDs confirm power, protection and line fault status at a glance Conforms to current UL 1449 3rd Edition safety standards

Fits Effortlessly Into Your Workstation 6 ft. AC power cord reaches nearby outlets Space-saving right-angle NEMA 5-15P plug allows furniture and equipment to move flush against the wall Keyhole slots on bottom panel provide convenient wall or desk mounting options Metal housing designed for long life

Backed by Tripp Lite's Ultimate Lifetime Insurance \$50,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332010117
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge
Voltage Compatibility (VAC)	120
Maximum Surge Amps	135000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	12
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	



Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and two position red illuminated on/off power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3330
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
AC Suppression Surge Current Rating	97,000 amps (36,000 NM / 61,000 CM)
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes, ferrite rod-core inductors and VHF capacitors.
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended over-voltages and catastrophic occurrences
UL1449 Let Through Rating	330V
IEEE587 Cat. A Ringwave Let-Through	Less than 35 volts
EMI / RFI Filtering	40-80 dB
Isolated Filter Banks	3
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Light Gray
Antimicrobial Coating	No
Color (AC Line Cord)	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 171.34mm; Distance between vertical tabs = 58.17mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 39.45mm; Distance between vertical outlets = 39.30mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	29.21 x 8.13 x 18.29



Shipping Dimensions (hwd / in.)	11.50 x 3.20 x 7.20
Shipping Weight (kg)	1.32
Shipping Weight (lbs.)	2.90
Unit Dimensions (hwd / cm)	6.35 x 15.24 x 8.89
Unit Dimensions (hwd / in.)	2.5 x 6 x 3.5
Unit Weight (kg)	1.09
Unit Weight (lbs.)	2.4
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition requirements by ETL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>