



## Wireless 150N Access Point

150 Mbps, Bridge, Repeater, Multiple SSIDs and VLANs

Part No.: **524704**

Wireless networking with three times the speed and five times the flexibility.

The INTELLINET NETWORK SOLUTIONS Wireless 150N Access Point is the latest in wireless networking. Taking advantage of new technology, a wireless network can now see greatly enhanced network speeds.

### Multiple Solutions in One Device

The INTELLINET NETWORK SOLUTIONS Wireless 150N Access Point serves multiple purposes — an access point for your wireless network supporting multiple SSIDs and tagged VLANs, a wireless bridge for point-to-point connections or WDS setups, and a RADIUS authentication server — and brings it all together so that the devices can access a high-speed Internet connection.

### Flexibility

This access point can be configured in any one of five modes: 1) Access Point (AP), 2) Point-to-Point (PtP), 3) Point-to-Multi-Point (PtMP), 4) Universal Repeater or 5) AP Client (Station Infrastructure). Add support for multiple ESSIDs and VLANs to that and it becomes clear that whatever your requirements are the 150N Access Point provides the solution.

### Secure Communications

The Wireless 150N Access Point provides maximum wireless security by supporting 802.1x user authentication for external RADIUS servers and, thanks to its internal RADIUS server, the access point can be used as the authentication server in smaller networks. Other security features included in this access point are MAC address filtering, disable SSID broadcast and support for the latest wireless encryption mechanisms.

### Features:

- Up to 150 Mbps network link speed
- Complies with 2.4 GHz IEEE 802.11n standard and is backward compatible with IEEE 802.11g/b standards
- Supports WMM function to meet the multimedia data bandwidth requirement
- Supports Wi-Fi Protected Setup (WPS)
- Supports WEP and WPA/WPA2 (TKIP and AES) data encryption
- Integrated RADIUS authentication server for 16 wireless clients
- DHCP server assigns IP addresses for all LAN users

*For more information on Intellinet products, consult your local dealer or visit [www.intellinet-network.com](http://www.intellinet-network.com).*

*All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.*

- Supported modes: Access Point, Bridge Point-to-Point, Bridge Point-to-Multi-Point, WDS and Universal Repeater
- Supports multiple ESSIDs with individual security settings
- Multiple ESSIDs support VLAN tagging
- Easy installation through Web-based user interface
- Firmware upgradeable
- Use INTELLINET NETWORK SOLUTIONS Wireless N adapters for the best compatibility and performance
- Three-Year Warranty

## Specifications:

### Standards

- IEEE 802.1d (Spanning Tree Protocol)
- IEEE 802.11b (11 Mbps Wireless LAN)
- IEEE 802.11g (54 Mbps Wireless LAN)
- IEEE 802.11n (150 Mbps Wireless LAN)
- IEEE 802.1x (Network Access Control)
- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3u (100Base-TX Fast Ethernet)

### General

- LAN port: RJ45 10/100 Mbps data port
- LAN port with Auto MDI/MDI-X
- Flash: 4 MB
- Memory: 16 MB SDRAM
- Certifications: FCC Class B, CE Mark

### Wireless

- Chipset: Ralink RT3050
- Wireless frequency range: 2.400 – 2.483 GHz
- Modulation technologies:
  - 802.11b: Direct Sequence Spread Spectrum (DSSS): DBPSK, DQPSK, CCK
  - 802.11g: Orthogonal Frequency Division Multiplexing (OFDM): BPSK, QPSK, 16QAM, 64QAM
  - 802.11n: Orthogonal Frequency Division Multiplexing (OFDM): BPSK, QPSK, 16QAM, 64QAM
- Data rates:
  - IEEE 802.11b (11 Mbps, 5.5 Mbps, 2 Mbps, 1 Mbps)
  - IEEE 802.11g (54 Mbps, 48 Mbps, 36 Mbps, 24 Mbps, 18 Mbps, 12 Mbps, 9 Mbps, 6 Mbps)
  - IEEE 802.11n (MCS0-7: up to 150 Mbps)
- Output power:
  - OFDM: 14 dBm +/- 1.5 dBm (150 Mbps, 40 mW max.)
  - OFDM: 15 dBm +/- 1.5 dBm (54 Mbps, 40 mW max.)
  - CCK: 17 dBm +/- 1.5 dBm (11 Mbps, 63 mW max.)
- Receiver sensitivity:

- 11n (150 Mbps) MCS0-7: 20 MHz: -73 dBm; 40MHz: -68 dBm
- 11g (54 Mbps) OFDM: -78 dBm
- 11b (11 Mbps) CCK: -91 dBm
- Wireless operation modes:
  - Access Point
  - Station Infrastructure (AP Client)
  - Point-to-Point Bridge
  - Point-to-Multi-Point Bridge
  - WDS Bridge
  - Universal Repeater
- Wireless security:
  - WEP encryption (64/128 bit)
  - WPA TKIP
  - WPA2 AES
  - WPA2 mixed
  - WPA RADIUS
  - 802.1x Authentication
  - Internal MD5/PEAP RADIUS server
  - Client access control through media access control (MAC) filter
- Antennas:
  - 1 detachable dipole antenna with 3 dBi gain

#### LEDs

- Power
- WLAN Link/Act
- LAN Link/Act

#### Environmental

- Dimensions: 160 (W) x 127 (L) x 35 (H) mm (6.3 x 5.0 x 1.4 in.)
- Weight: 0.8 kg (1.7 lbs.)
- Operating temperature: 0 – 40°C (32 – 104°F)
- Operating humidity: 10 – 90% RH, non-condensing
- Storage temperature: -20 – 60°C (4 – 149°F)

#### Power

- External power adapter: 5 V DC, 1.0 A
- Power consumption: 4 Watts max.

#### Package Contents

- Wireless 150N Access Point
- User manual
- 1 detachable antenna
- Power adapter
- Ethernet Cat5 RJ45 cable: 1.0 m (3 ft.)

